

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931095

Luminaire Tested: DFN2DS-SQ4F0-070DS935-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931095
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ4F0-070DS935-FLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5959.8 lumens
Efficiency: N/A
Efficacy: 86.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.92' x L: 3.92' x H: 0')
CIE Type: Direct

Input Watts (W): 69.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931095

CATALOG NUMBER: DFN2DS-SQ4F0-070DS935-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931095

CATALOG NUMBER: DFN2DS-SQ4F0-070DS935-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1644	1644	1644
5°	1650	1626	1636
10°	1640	1610	1618
15°	1620	1589	1587
20°	1591	1557	1556
25°	1563	1519	1519
30°	1526	1484	1471
35°	1491	1441	1420
40°	1448	1399	1372
45°	1406	1357	1323
50°	1360	1313	1266
55°	1312	1262	1215
60°	1258	1201	1157
65°	1201	1141	1088
70°	1128	1067	1017
75°	1026	983	959
80°	910	883	837
85°	743	708	635

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1406 cd/sqm

TEST NUMBER: P931095

CATALOG NUMBER: DFN2DS-SQ4F0-070DS935-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	220.5	3.7
10°-20°	620.3	10.4
20°-30°	911.6	15.3
30°-40°	1058.8	17.8
40°-50°	1057.5	17.7
50°-60°	922.1	15.5
60°-70°	681.6	11.4
70°-80°	385.7	6.5
80°-90°	101.8	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1752.4	29.4
0°-40°	2811.2	47.2
0°-60°	4790.7	80.4
0°-90°	5959.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5959.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2342	2342	2342	2342	2342	
5°	2342	2334	2309	2327	2322	222
15°	2230	2216	2187	2196	2185	628
25°	2018	2000	1962	1966	1962	929
35°	1741	1719	1683	1669	1658	1087
45°	1417	1401	1367	1342	1333	1093
55°	1072	1059	1032	1005	993	959
65°	723	710	687	667	656	715
75°	378	374	362	349	354	404
85°	92	90	88	81	79	108
90°	0	0	0	0	0	

TEST NUMBER: P931095

CATALOG NUMBER: DFN2DS-SQ4F0-070DS935-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2342.4	2342.4	2342.4	2342.4	2342.4
2.5°	2356.1	2344.8	2319.9	2342.4	2338.1
5°	2342.4	2333.6	2308.8	2326.6	2322.3
7.5°	2326.6	2313.2	2288.4	2306.6	2302.0
10°	2302.0	2286.2	2259.2	2277.2	2270.5
12.5°	2268.1	2254.7	2227.7	2238.9	2234.4
15°	2229.9	2216.5	2187.1	2196.2	2184.9
17.5°	2182.5	2169.2	2139.8	2151.0	2139.8
20°	2130.6	2117.3	2085.8	2092.5	2083.6
22.5°	2079.0	2058.8	2029.3	2029.3	2024.8
25°	2018.2	2000.2	1962.0	1966.3	1962.0
27.5°	1950.5	1934.7	1905.6	1898.9	1887.6
30°	1883.1	1864.9	1831.3	1824.6	1815.5
32.5°	1810.9	1797.6	1761.5	1747.9	1738.7
35°	1741.2	1718.7	1682.6	1669.0	1657.7
37.5°	1662.3	1642.0	1605.9	1590.1	1578.9
40°	1581.3	1563.1	1527.0	1507.0	1497.9
42.5°	1502.4	1484.3	1448.4	1425.7	1412.3
45°	1416.8	1401.1	1367.1	1342.5	1333.4
47.5°	1333.4	1317.7	1281.6	1256.7	1243.4
50°	1245.5	1234.3	1202.7	1171.2	1160.0
52.5°	1160.0	1144.2	1115.1	1090.2	1074.4
55°	1072.2	1058.7	1031.7	1004.7	993.4
57.5°	984.4	973.1	943.7	916.7	907.6
60°	896.4	887.5	856.0	831.2	824.5
62.5°	810.8	795.1	772.6	750.2	741.1
65°	723.2	709.5	687.1	666.8	655.5
67.5°	633.0	621.6	601.5	585.7	576.6
70°	549.6	540.6	520.2	504.5	495.6
72.5°	464.1	455.0	443.8	428.0	421.3
75°	378.3	374.0	362.5	349.2	353.7
77.5°	301.9	292.7	288.2	281.5	274.9
80°	225.3	223.0	218.4	211.7	207.2
82.5°	153.2	153.2	151.0	142.0	142.0
85°	92.3	90.1	88.0	81.0	78.9
87.5°	40.6	36.1	31.6	24.9	22.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931095

CATALOG NUMBER: DFN2DS-SQ4F0-070DS935-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.01	14.62	13.37	14.93	15.25	12.56	14.18	12.93	14.49	14.80
	3H	14.76	16.21	15.14	16.54	16.90	14.27	15.72	14.64	16.05	16.41
	4H	15.41	16.77	15.80	17.12	17.50	14.91	16.28	15.31	16.63	17.00
	6H	15.87	17.14	16.29	17.51	17.90	15.37	16.64	15.78	17.01	17.40
	8H	16.02	17.23	16.44	17.62	18.02	15.51	16.73	15.94	17.11	17.51
	12H	16.11	17.27	16.54	17.65	18.08	15.60	16.76	16.03	17.14	17.57
4H	2H	13.57	14.94	13.97	15.29	15.66	13.22	14.59	13.61	14.93	15.31
	3H	15.54	16.69	15.95	17.09	17.49	15.14	16.28	15.55	16.68	17.08
	4H	16.32	17.36	16.75	17.77	18.21	15.90	16.93	16.33	17.35	17.78
	6H	16.92	17.82	17.37	18.26	18.72	16.49	17.39	16.94	17.83	18.29
	8H	17.11	17.95	17.57	18.40	18.86	16.67	17.52	17.13	17.96	18.42
	12H	17.24	18.00	17.72	18.47	18.94	16.79	17.55	17.27	18.02	18.49
8H	4H	16.59	17.44	17.06	17.88	18.35	16.22	17.07	16.68	17.51	17.97
	6H	17.31	18.01	17.80	18.50	18.98	16.93	17.63	17.42	18.12	18.59
	8H	17.57	18.20	18.08	18.71	19.19	17.18	17.81	17.69	18.31	18.80
	12H	17.77	18.33	18.27	18.82	19.38	17.35	17.91	17.86	18.40	18.96
12H	4H	16.62	17.38	17.10	17.86	18.33	16.26	17.02	16.74	17.49	17.96
	6H	17.35	17.99	17.86	18.49	18.98	16.99	17.62	17.50	18.12	18.61
	8H	17.67	18.23	18.18	18.72	19.28	17.29	17.85	17.80	18.34	18.90