

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930623

Luminaire Tested: DFN2DS-PN3F0-090DS927-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930623
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN3F0-090DS927-FLL
Description: 3 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7056.8 lumens
Efficiency: N/A
Efficacy: 72.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.11' x L: 2.96' x H: 0')
CIE Type: Direct

Input Watts (W): 97.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930623

CATALOG NUMBER: DFN2DS-PN3F0-090DS927-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930623

CATALOG NUMBER: DFN2DS-PN3F0-090DS927-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3242	3242	3242
5°	3255	3208	3227
10°	3235	3175	3191
15°	3195	3134	3131
20°	3138	3072	3069
25°	3082	2996	2996
30°	3010	2927	2902
35°	2942	2843	2801
40°	2857	2759	2707
45°	2773	2676	2610
50°	2682	2590	2498
55°	2588	2489	2397
60°	2482	2370	2282
65°	2368	2250	2147
70°	2224	2105	2006
75°	2023	1939	1892
80°	1796	1741	1652
85°	1465	1396	1253

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2773 cd/sqm

TEST NUMBER: P930623

CATALOG NUMBER: DFN2DS-PN3F0-090DS927-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	261.0	3.7
10°-20°	734.5	10.4
20°-30°	1079.4	15.3
30°-40°	1253.7	17.8
40°-50°	1252.1	17.7
50°-60°	1091.8	15.5
60°-70°	807.1	11.4
70°-80°	456.6	6.5
80°-90°	120.5	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2074.9	29.4
0°-40°	3328.6	47.2
0°-60°	5672.5	80.4
0°-90°	7056.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7056.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2774	2774	2774	2774	2774	
5°	2774	2763	2734	2755	2750	263
15°	2640	2624	2590	2600	2587	744
25°	2390	2368	2323	2328	2323	1100
35°	2062	2035	1992	1976	1963	1287
45°	1678	1659	1619	1590	1579	1295
55°	1270	1254	1222	1190	1176	1135
65°	856	840	814	790	776	847
75°	448	443	429	413	419	478
85°	109	107	104	96	93	128
90°	0	0	0	0	0	

TEST NUMBER: P930623

CATALOG NUMBER: DFN2DS-PN3F0-090DS927-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2773.5	2773.5	2773.5	2773.5	2773.5
2.5°	2789.7	2776.4	2747.0	2773.5	2768.4
5°	2773.5	2763.1	2733.7	2754.9	2749.7
7.5°	2754.9	2739.1	2709.6	2731.1	2725.7
10°	2725.7	2707.1	2675.1	2696.3	2688.4
12.5°	2685.5	2669.7	2637.8	2651.0	2645.7
15°	2640.3	2624.5	2589.6	2600.4	2587.1
17.5°	2584.2	2568.4	2533.6	2546.9	2533.6
20°	2522.8	2507.0	2469.6	2477.5	2467.1
22.5°	2461.7	2437.7	2402.8	2402.8	2397.5
25°	2389.5	2368.3	2323.1	2328.2	2323.1
27.5°	2309.5	2290.8	2256.3	2248.4	2235.1
30°	2229.7	2208.2	2168.3	2160.3	2149.6
32.5°	2144.3	2128.4	2085.7	2069.6	2058.8
35°	2061.7	2035.0	1992.3	1976.2	1962.9
37.5°	1968.3	1944.2	1901.4	1882.8	1869.5
40°	1872.3	1850.8	1808.1	1784.3	1773.6
42.5°	1778.9	1757.4	1715.0	1688.1	1672.3
45°	1677.6	1659.0	1618.8	1589.6	1578.9
47.5°	1578.9	1560.2	1517.5	1488.1	1472.2
50°	1474.8	1461.5	1424.1	1386.8	1373.5
52.5°	1373.5	1354.8	1320.3	1290.9	1272.2
55°	1269.7	1253.5	1221.5	1189.6	1176.3
57.5°	1165.5	1152.2	1117.4	1085.4	1074.7
60°	1061.4	1050.9	1013.5	984.1	976.2
62.5°	960.1	941.4	914.8	888.2	877.5
65°	856.2	840.1	813.5	789.5	776.2
67.5°	749.5	736.0	712.2	693.6	682.8
70°	650.8	640.0	616.0	597.3	586.9
72.5°	549.5	538.7	525.4	506.8	498.9
75°	448.0	442.8	429.3	413.4	418.8
77.5°	357.4	346.7	341.3	333.4	325.4
80°	266.8	264.0	258.6	250.7	245.4
82.5°	181.4	181.4	178.8	168.1	168.1
85°	109.2	106.7	104.1	95.9	93.4
87.5°	48.1	42.7	37.4	29.5	26.6
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930623

CATALOG NUMBER: DFN2DS-PN3F0-090DS927-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.37	16.98	15.73	17.29	17.61	14.92	16.54	15.29	16.85	17.16
	3H	17.12	18.57	17.50	18.90	19.26	16.63	18.08	17.01	18.41	18.77
	4H	17.77	19.13	18.16	19.48	19.86	17.27	18.64	17.67	18.99	19.36
	6H	18.23	19.50	18.65	19.87	20.26	17.73	19.00	18.14	19.37	19.76
	8H	18.38	19.59	18.80	19.98	20.38	17.88	19.09	18.30	19.48	19.87
	12H	18.47	19.63	18.90	20.01	20.44	17.96	19.12	18.39	19.50	19.93
4H	2H	15.93	17.30	16.33	17.65	18.02	15.58	16.95	15.98	17.29	17.67
	3H	17.90	19.05	18.31	19.45	19.85	17.50	18.64	17.91	19.04	19.44
	4H	18.68	19.72	19.11	20.13	20.57	18.26	19.29	18.69	19.71	20.14
	6H	19.28	20.18	19.73	20.62	21.08	18.85	19.75	19.30	20.19	20.65
	8H	19.47	20.31	19.93	20.76	21.22	19.03	19.88	19.49	20.32	20.78
	12H	19.60	20.36	20.08	20.84	21.30	19.15	19.91	19.63	20.38	20.85
8H	4H	18.95	19.80	19.42	20.24	20.71	18.58	19.43	19.04	19.87	20.33
	6H	19.67	20.37	20.16	20.86	21.34	19.29	19.99	19.78	20.48	20.95
	8H	19.93	20.56	20.44	21.07	21.55	19.54	20.17	20.05	20.67	21.16
	12H	20.13	20.69	20.64	21.18	21.74	19.72	20.27	20.22	20.76	21.32
12H	4H	18.98	19.74	19.46	20.22	20.69	18.62	19.38	19.10	19.85	20.32
	6H	19.71	20.35	20.22	20.85	21.34	19.35	19.98	19.86	20.48	20.97
	8H	20.03	20.59	20.54	21.08	21.64	19.65	20.21	20.16	20.70	21.26