

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930554

Luminaire Tested: DFN2DS-PN3F0-050DS930-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930554
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN3F0-050DS930-RLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3463.8 lumens
Efficiency: N/A
Efficacy: 70.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.11' x L: 2.96' x H: 0')
CIE Type: Direct

Input Watts (W): 49.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930554

CATALOG NUMBER: DFN2DS-PN3F0-050DS930-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930554

CATALOG NUMBER: DFN2DS-PN3F0-050DS930-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1969	1969	1969
5°	1976	1944	1955
10°	1961	1912	1896
15°	1939	1856	1802
20°	1907	1775	1686
25°	1875	1683	1573
30°	1831	1588	1428
35°	1788	1486	1301
40°	1744	1379	1154
45°	1693	1260	1020
50°	1641	1139	890
55°	1587	1009	764
60°	1525	873	634
65°	1454	734	578
70°	1370	604	531
75°	1266	551	496
80°	1118	492	452
85°	879	388	388

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1693 cd/sqm

TEST NUMBER: P930554

CATALOG NUMBER: DFN2DS-PN3F0-050DS930-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.8	4.6
10°-20°	433.3	12.5
20°-30°	608.4	17.6
30°-40°	663.2	19.1
40°-50°	609.5	17.6
50°-60°	478.7	13.8
60°-70°	311.6	9.0
70°-80°	160.4	4.6
80°-90°	40.9	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1199.5	34.6
0°-40°	1862.7	53.8
0°-60°	2950.9	85.2
0°-90°	3463.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3463.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1684	1684	1684	1684	1684	
5°	1684	1677	1657	1670	1666	160
15°	1602	1585	1533	1504	1489	451
25°	1454	1405	1305	1242	1219	669
35°	1253	1175	1041	945	911	784
45°	1024	922	762	654	617	791
55°	779	660	495	404	375	696
65°	526	402	265	213	209	521
75°	280	174	122	111	110	297
85°	66	34	29	29	29	79
90°	0	0	0	0	0	

TEST NUMBER: P930554

CATALOG NUMBER: DFN2DS-PN3F0-050DS930-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1684.2	1684.2	1684.2	1684.2	1684.2
2.5°	1691.8	1684.2	1667.4	1682.7	1679.6
5°	1684.2	1676.6	1656.7	1670.4	1665.9
7.5°	1670.4	1661.4	1640.0	1646.1	1638.4
10°	1652.2	1641.5	1611.1	1606.4	1597.3
12.5°	1629.3	1615.7	1574.4	1565.4	1548.5
15°	1601.9	1585.1	1533.3	1504.4	1489.2
17.5°	1569.9	1545.5	1481.4	1447.9	1423.5
20°	1533.3	1502.8	1426.6	1388.6	1354.9
22.5°	1493.7	1458.6	1370.2	1318.4	1295.6
25°	1454.0	1405.2	1304.7	1242.2	1219.2
27.5°	1406.9	1354.9	1243.7	1172.1	1137.0
30°	1356.6	1298.5	1176.6	1098.9	1057.7
32.5°	1307.7	1237.6	1112.7	1021.2	983.1
35°	1252.9	1175.1	1041.1	945.0	911.4
37.5°	1199.5	1115.7	974.0	868.7	830.7
40°	1143.1	1051.8	903.8	795.6	756.0
42.5°	1085.3	987.7	833.7	720.9	682.9
45°	1024.3	922.1	762.1	653.8	617.2
47.5°	966.3	858.2	693.6	585.3	551.8
50°	902.4	794.1	626.5	521.2	489.3
52.5°	839.8	725.4	562.4	461.9	432.9
55°	778.8	659.9	495.3	403.9	375.0
57.5°	716.4	594.5	435.9	350.6	326.2
60°	652.3	530.4	373.4	295.8	271.3
62.5°	589.9	468.0	320.1	246.9	234.8
65°	525.8	402.4	265.2	213.4	208.8
67.5°	464.9	341.4	213.4	187.4	182.9
70°	400.9	282.0	176.8	161.5	155.4
72.5°	339.9	227.1	147.8	135.7	132.6
75°	280.4	173.7	121.9	111.2	109.8
77.5°	221.0	123.4	96.1	89.9	86.8
80°	166.1	88.4	73.1	67.1	67.1
82.5°	115.8	59.5	50.3	47.2	47.2
85°	65.5	33.5	28.9	28.9	28.9
87.5°	24.4	12.1	12.1	10.7	10.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930554

CATALOG NUMBER: DFN2DS-PN3F0-050DS930-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.59	15.11	13.95	15.42	15.74	9.55	11.07	9.91	11.38	11.70
	3H	15.35	16.72	15.73	17.05	17.41	10.81	12.18	11.19	12.51	12.87
	4H	16.02	17.30	16.42	17.65	18.03	11.32	12.60	11.72	12.95	13.32
	6H	16.51	17.69	16.92	18.06	18.45	11.70	12.88	12.11	13.25	13.64
	8H	16.67	17.80	17.10	18.19	18.59	11.82	12.95	12.25	13.34	13.74
	12H	16.78	17.86	17.21	18.24	18.67	11.90	12.98	12.33	13.36	13.79
4H	2H	13.69	14.97	14.09	15.32	15.70	10.24	11.53	10.64	11.87	12.25
	3H	15.63	16.69	16.04	17.09	17.49	11.69	12.75	12.10	13.15	13.55
	4H	16.38	17.33	16.81	17.75	18.19	12.29	13.24	12.72	13.66	14.10
	6H	16.97	17.80	17.42	18.24	18.70	12.77	13.61	13.23	14.05	14.51
	8H	17.18	17.96	17.64	18.40	18.87	12.94	13.71	13.40	14.16	14.63
	12H	17.33	18.03	17.82	18.51	18.98	13.05	13.75	13.54	14.23	14.70
8H	4H	16.40	17.18	16.86	17.62	18.09	12.64	13.42	13.10	13.86	14.33
	6H	17.04	17.68	17.53	18.17	18.65	13.23	13.87	13.72	14.36	14.84
	8H	17.29	17.86	17.80	18.37	18.86	13.45	14.02	13.96	14.53	15.02
	12H	17.49	18.00	18.00	18.49	19.06	13.63	14.14	14.14	14.63	15.19
12H	4H	16.38	17.08	16.87	17.56	18.03	12.68	13.38	13.17	13.86	14.33
	6H	17.02	17.60	17.53	18.10	18.59	13.29	13.87	13.80	14.38	14.87
	8H	17.30	17.81	17.81	18.30	18.87	13.56	14.07	14.07	14.57	15.13