

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931134

Luminaire Tested: DFN2DS-SQ4F0-090DS940-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931134
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ4F0-090DS940-RLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6823.8 lumens
Efficiency: N/A
Efficacy: 75.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.92' x L: 3.92' x H: 0')
CIE Type: Direct

Input Watts (W): 90.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931134

CATALOG NUMBER: DFN2DS-SQ4F0-090DS940-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931134

CATALOG NUMBER: DFN2DS-SQ4F0-090DS940-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2328	2328	2328
5°	2337	2299	2312
10°	2319	2261	2242
15°	2292	2194	2131
20°	2256	2099	1993
25°	2218	1990	1860
30°	2165	1878	1688
35°	2114	1757	1538
40°	2063	1631	1364
45°	2002	1490	1207
50°	1941	1347	1052
55°	1877	1194	904
60°	1803	1032	750
65°	1720	867	683
70°	1620	714	628
75°	1498	651	586
80°	1322	582	534
85°	1039	459	459

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2002 cd/sqm

TEST NUMBER: P931134

CATALOG NUMBER: DFN2DS-SQ4F0-090DS940-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	311.0	4.6
10°-20°	853.7	12.5
20°-30°	1198.5	17.6
30°-40°	1306.5	19.1
40°-50°	1200.8	17.6
50°-60°	943.0	13.8
60°-70°	613.8	9.0
70°-80°	316.0	4.6
80°-90°	80.7	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2363.1	34.6
0°-40°	3669.6	53.8
0°-60°	5813.4	85.2
0°-90°	6823.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6823.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3318	3318	3318	3318	3318	
5°	3318	3303	3264	3291	3282	315
15°	3156	3123	3021	2964	2934	889
25°	2865	2768	2570	2447	2402	1317
35°	2468	2315	2051	1862	1796	1545
45°	2018	1817	1501	1288	1216	1558
55°	1534	1300	976	796	739	1371
65°	1036	793	522	420	411	1027
75°	552	342	240	219	216	584
85°	129	66	57	57	57	155
90°	0	0	0	0	0	

TEST NUMBER: P931134

CATALOG NUMBER: DFN2DS-SQ4F0-090DS940-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3318.0	3318.0	3318.0	3318.0	3318.0
2.5°	3333.0	3318.0	3284.8	3315.1	3309.1
5°	3318.0	3303.0	3263.8	3290.9	3281.9
7.5°	3290.9	3273.0	3231.0	3242.8	3227.8
10°	3254.9	3233.9	3174.0	3164.7	3146.9
12.5°	3210.0	3182.9	3101.7	3083.8	3050.6
15°	3155.8	3122.7	3020.8	2963.7	2933.8
17.5°	3092.7	3044.7	2918.4	2852.5	2804.4
20°	3020.8	2960.5	2810.4	2735.6	2669.3
22.5°	2942.7	2873.6	2699.3	2597.3	2552.5
25°	2864.7	2768.4	2570.3	2447.3	2402.1
27.5°	2771.6	2669.3	2450.1	2309.0	2239.9
30°	2672.5	2558.2	2318.0	2165.1	2083.8
32.5°	2576.3	2438.0	2192.1	2011.8	1936.6
35°	2468.3	2315.1	2051.0	1861.8	1795.5
37.5°	2363.2	2197.9	1918.8	1711.4	1636.6
40°	2252.0	2072.0	1780.5	1567.4	1489.4
42.5°	2137.9	1945.9	1642.5	1420.2	1345.3
45°	2017.9	1816.6	1501.4	1288.0	1216.0
47.5°	1903.8	1690.7	1366.4	1152.9	1087.0
50°	1777.7	1564.5	1234.2	1026.8	964.0
52.5°	1654.4	1429.2	1108.0	909.8	852.8
55°	1534.2	1300.1	975.8	795.8	738.8
57.5°	1411.3	1171.1	858.9	690.7	642.6
60°	1285.1	1044.9	735.6	582.7	534.6
62.5°	1162.2	922.0	630.5	486.5	462.6
65°	1036.0	792.6	522.4	420.5	411.3
67.5°	915.9	672.5	420.5	369.2	360.3
70°	789.8	555.6	348.2	318.3	306.1
72.5°	669.6	447.2	291.1	267.2	261.3
75°	552.4	342.2	240.2	219.2	216.3
77.5°	435.5	243.1	189.2	177.2	171.1
80°	327.2	174.3	144.0	132.2	132.2
82.5°	228.1	117.2	99.1	93.0	93.0
85°	129.0	65.9	57.0	57.0	57.0
87.5°	48.1	23.9	23.9	21.1	21.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931134

CATALOG NUMBER: DFN2DS-SQ4F0-090DS940-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.17	15.69	14.54	16.01	16.32	10.13	11.65	10.50	11.97	12.28
	3H	15.94	17.30	16.31	17.63	17.99	11.40	12.76	11.77	13.09	13.45
	4H	16.60	17.88	17.00	18.23	18.61	11.90	13.18	12.30	13.53	13.91
	6H	17.09	18.27	17.50	18.64	19.03	12.28	13.46	12.69	13.83	14.22
	8H	17.26	18.38	17.68	18.77	19.17	12.40	13.53	12.83	13.92	14.32
	12H	17.36	18.44	17.79	18.82	19.25	12.48	13.56	12.92	13.95	14.37
4H	2H	14.27	15.56	14.67	15.90	16.28	10.83	12.11	11.23	12.46	12.83
	3H	16.21	17.27	16.62	17.67	18.07	12.27	13.33	12.68	13.73	14.13
	4H	16.96	17.91	17.39	18.33	18.77	12.87	13.83	13.30	14.24	14.68
	6H	17.55	18.38	18.01	18.82	19.28	13.36	14.19	13.81	14.63	15.09
	8H	17.76	18.54	18.23	18.99	19.45	13.52	14.30	13.98	14.74	15.21
	12H	17.92	18.61	18.40	19.09	19.56	13.64	14.33	14.12	14.81	15.28
8H	4H	16.98	17.76	17.44	18.20	18.67	13.22	14.00	13.69	14.44	14.91
	6H	17.62	18.26	18.12	18.75	19.23	13.81	14.45	14.31	14.94	15.42
	8H	17.87	18.45	18.38	18.96	19.44	14.03	14.61	14.54	15.12	15.61
	12H	18.07	18.58	18.58	19.08	19.64	14.21	14.72	14.72	15.21	15.78
12H	4H	16.97	17.66	17.45	18.14	18.61	13.27	13.96	13.75	14.44	14.91
	6H	17.60	18.18	18.11	18.69	19.18	13.87	14.45	14.39	14.96	15.45
	8H	17.88	18.39	18.39	18.89	19.45	14.15	14.66	14.66	15.15	15.71

END OF REPORT

FIELD PERFORMANCE MAY DIFFER FROM LABORATORY PERFORMANCE

7 of 7