

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930592

Luminaire Tested: DFN2DS-PN3F0-070DS935-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930592
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN3F0-070DS935-RLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5117.0 lumens
Efficiency: N/A
Efficacy: 69.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.11' x L: 2.96' x H: 0')
CIE Type: Direct

Input Watts (W): 73.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930592

CATALOG NUMBER: DFN2DS-PN3F0-070DS935-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930592

CATALOG NUMBER: DFN2DS-PN3F0-070DS935-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2909	2909	2909
5°	2920	2872	2888
10°	2897	2825	2801
15°	2864	2741	2662
20°	2818	2622	2490
25°	2771	2486	2323
30°	2705	2346	2109
35°	2641	2195	1921
40°	2577	2038	1704
45°	2502	1861	1508
50°	2424	1683	1315
55°	2345	1491	1129
60°	2253	1290	937
65°	2149	1084	853
70°	2024	892	784
75°	1871	813	733
80°	1652	727	668
85°	1298	573	573

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2502 cd/sqm

TEST NUMBER: P930592

CATALOG NUMBER: DFN2DS-PN3F0-070DS935-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	233.2	4.6
10°-20°	640.1	12.5
20°-30°	898.7	17.6
30°-40°	979.7	19.1
40°-50°	900.4	17.6
50°-60°	707.1	13.8
60°-70°	460.3	9.0
70°-80°	236.9	4.6
80°-90°	60.5	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1772.1	34.6
0°-40°	2751.7	53.8
0°-60°	4359.3	85.2
0°-90°	5117.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5117.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2488	2488	2488	2488	2488	
5°	2488	2477	2448	2468	2461	236
15°	2366	2342	2265	2222	2200	667
25°	2148	2076	1927	1835	1801	988
35°	1851	1736	1538	1396	1346	1158
45°	1513	1362	1126	966	912	1169
55°	1150	975	732	597	554	1028
65°	777	594	392	315	308	770
75°	414	256	180	164	162	438
85°	97	49	43	43	43	116
90°	0	0	0	0	0	

TEST NUMBER: P930592

CATALOG NUMBER: DFN2DS-PN3F0-070DS935-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2488.1	2488.1	2488.1	2488.1	2488.1
2.5°	2499.2	2488.1	2463.2	2485.9	2481.4
5°	2488.1	2476.8	2447.5	2467.8	2461.1
7.5°	2467.8	2454.4	2422.9	2431.6	2420.5
10°	2440.8	2425.0	2380.0	2373.2	2359.8
12.5°	2407.1	2386.8	2325.9	2312.5	2287.6
15°	2366.5	2341.6	2265.2	2222.4	2200.0
17.5°	2319.2	2283.1	2188.5	2139.0	2103.0
20°	2265.2	2220.0	2107.5	2051.4	2001.6
22.5°	2206.7	2154.8	2024.1	1947.6	1914.0
25°	2148.1	2076.0	1927.3	1835.2	1801.3
27.5°	2078.4	2001.6	1837.3	1731.5	1679.7
30°	2004.1	1918.3	1738.1	1623.5	1562.6
32.5°	1931.9	1828.3	1643.8	1508.6	1452.2
35°	1850.9	1736.0	1538.0	1396.1	1346.4
37.5°	1772.1	1648.1	1438.9	1283.3	1227.2
40°	1688.7	1553.8	1335.2	1175.4	1116.8
42.5°	1603.2	1459.2	1231.7	1064.9	1008.9
45°	1513.2	1362.2	1125.9	965.9	911.9
47.5°	1427.6	1267.8	1024.6	864.6	815.1
50°	1333.0	1173.2	925.4	770.0	722.9
52.5°	1240.6	1071.6	830.8	682.2	639.5
55°	1150.5	974.9	731.7	596.8	554.0
57.5°	1058.3	878.1	644.1	517.9	481.9
60°	963.7	783.5	551.6	437.0	400.8
62.5°	871.4	691.4	472.7	364.8	346.8
65°	776.8	594.3	391.8	315.4	308.4
67.5°	686.8	504.3	315.4	276.8	270.2
70°	592.2	416.6	261.1	238.6	229.5
72.5°	502.2	335.4	218.4	200.5	195.9
75°	414.3	256.5	180.1	164.3	162.2
77.5°	326.5	182.2	141.9	132.8	128.3
80°	245.4	130.6	108.0	99.2	99.2
82.5°	171.1	87.9	74.3	69.7	69.7
85°	96.8	49.4	42.7	42.7	42.7
87.5°	36.0	17.9	17.9	15.7	15.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930592

CATALOG NUMBER: DFN2DS-PN3F0-070DS935-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.94	16.47	15.31	16.78	17.09	10.90	12.43	11.27	12.74	13.05
	3H	16.71	18.07	17.09	18.40	18.76	12.17	13.53	12.55	13.86	14.22
	4H	17.38	18.66	17.78	19.00	19.38	12.67	13.95	13.07	14.30	14.68
	6H	17.86	19.05	18.28	19.41	19.81	13.05	14.24	13.46	14.60	14.99
	8H	18.03	19.16	18.46	19.55	19.95	13.18	14.30	13.60	14.69	15.09
	12H	18.13	19.21	18.56	19.59	20.02	13.26	14.34	13.69	14.72	15.15
4H	2H	15.05	16.33	15.45	16.68	17.06	11.60	12.88	12.00	13.23	13.61
	3H	16.98	18.04	17.39	18.44	18.84	13.04	14.11	13.45	14.51	14.91
	4H	17.73	18.69	18.16	19.10	19.54	13.64	14.60	14.07	15.01	15.45
	6H	18.32	19.15	18.78	19.60	20.06	14.13	14.96	14.59	15.41	15.87
	8H	18.54	19.31	19.00	19.76	20.23	14.29	15.07	14.76	15.51	15.98
	12H	18.69	19.38	19.17	19.86	20.33	14.41	15.10	14.89	15.58	16.05
8H	4H	17.75	18.53	18.22	18.98	19.44	14.00	14.77	14.46	15.22	15.68
	6H	18.39	19.03	18.89	19.53	20.00	14.58	15.23	15.08	15.72	16.19
	8H	18.64	19.22	19.16	19.73	20.22	14.80	15.38	15.32	15.89	16.38
	12H	18.85	19.36	19.36	19.85	20.41	14.98	15.49	15.49	15.98	16.55
12H	4H	17.74	18.43	18.22	18.91	19.38	14.04	14.73	14.52	15.21	15.68
	6H	18.37	18.95	18.89	19.46	19.95	14.65	15.22	15.16	15.73	16.22
	8H	18.66	19.17	19.17	19.66	20.22	14.92	15.43	15.43	15.92	16.49