

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930610

Luminaire Tested: DFN2DS-PN3F0-080DS935-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930610
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN3F0-080DS935-RLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5848.0 lumens
Efficiency: N/A
Efficacy: 69.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.11' x L: 2.96' x H: 0')
CIE Type: Direct

Input Watts (W): 84.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930610

CATALOG NUMBER: DFN2DS-PN3F0-080DS935-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930610

CATALOG NUMBER: DFN2DS-PN3F0-080DS935-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3324	3324	3324
5°	3337	3282	3300
10°	3311	3229	3201
15°	3273	3133	3043
20°	3220	2996	2846
25°	3167	2841	2655
30°	3092	2681	2411
35°	3019	2508	2196
40°	2945	2329	1948
45°	2859	2127	1723
50°	2770	1924	1502
55°	2680	1704	1290
60°	2575	1474	1071
65°	2456	1238	975
70°	2313	1020	897
75°	2138	930	837
80°	1888	831	763
85°	1483	655	655

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2859 cd/sqm

TEST NUMBER: P930610

CATALOG NUMBER: DFN2DS-PN3F0-080DS935-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	266.5	4.6
10°-20°	731.6	12.5
20°-30°	1027.1	17.6
30°-40°	1119.6	19.1
40°-50°	1029.1	17.6
50°-60°	808.2	13.8
60°-70°	526.0	9.0
70°-80°	270.8	4.6
80°-90°	69.1	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2025.2	34.6
0°-40°	3144.8	53.8
0°-60°	4982.0	85.2
0°-90°	5848.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5848.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2844	2844	2844	2844	2844	
5°	2844	2831	2797	2820	2813	270
15°	2704	2676	2589	2540	2514	762
25°	2455	2373	2203	2097	2059	1129
35°	2115	1984	1758	1596	1539	1324
45°	1729	1557	1287	1104	1042	1335
55°	1315	1114	836	682	633	1175
65°	888	679	448	360	352	880
75°	473	293	206	188	185	501
85°	111	56	49	49	49	133
90°	0	0	0	0	0	

TEST NUMBER: P930610

CATALOG NUMBER: DFN2DS-PN3F0-080DS935-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2843.5	2843.5	2843.5	2843.5	2843.5
2.5°	2856.3	2843.5	2815.1	2841.0	2835.8
5°	2843.5	2830.7	2797.1	2820.3	2812.6
7.5°	2820.3	2805.0	2768.9	2779.1	2766.2
10°	2789.4	2771.4	2720.1	2712.2	2696.9
12.5°	2751.0	2727.7	2658.1	2642.8	2614.4
15°	2704.5	2676.1	2588.8	2539.9	2514.2
17.5°	2650.4	2609.2	2501.1	2444.6	2403.4
20°	2588.8	2537.2	2408.6	2344.4	2287.6
22.5°	2521.9	2462.6	2313.3	2225.9	2187.4
25°	2455.0	2372.6	2202.7	2097.4	2058.6
27.5°	2375.2	2287.6	2099.8	1978.9	1919.6
30°	2290.4	2192.3	1986.5	1855.4	1785.8
32.5°	2207.9	2089.5	1878.7	1724.1	1659.7
35°	2115.3	1984.0	1757.7	1595.6	1538.7
37.5°	2025.2	1883.6	1644.4	1466.6	1402.5
40°	1930.0	1775.7	1525.9	1343.2	1276.3
42.5°	1832.2	1667.6	1407.6	1217.2	1152.9
45°	1729.3	1556.8	1286.7	1103.8	1042.1
47.5°	1631.6	1448.9	1171.0	988.1	931.6
50°	1523.4	1340.8	1057.7	880.0	826.1
52.5°	1417.8	1224.7	949.5	779.8	730.9
55°	1314.9	1114.2	836.3	682.0	633.1
57.5°	1209.5	1003.6	736.1	591.9	550.7
60°	1101.3	895.5	630.4	499.3	458.1
62.5°	996.0	790.1	540.3	416.9	396.5
65°	887.9	679.2	447.7	360.4	352.4
67.5°	784.9	576.4	360.4	316.4	308.8
70°	676.8	476.2	298.4	272.7	262.4
72.5°	573.9	383.3	249.6	229.1	223.9
75°	473.4	293.3	205.9	187.8	185.4
77.5°	373.2	208.3	162.2	151.8	146.6
80°	280.4	149.4	123.4	113.3	113.3
82.5°	195.5	100.4	84.9	79.7	79.7
85°	110.6	56.5	48.8	48.8	48.8
87.5°	41.2	20.5	20.5	18.1	18.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930610

CATALOG NUMBER: DFN2DS-PN3F0-080DS935-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.41	16.93	15.77	17.24	17.56	11.37	12.89	11.73	13.20	13.52
	3H	17.17	18.54	17.55	18.87	19.23	12.63	14.00	13.01	14.33	14.69
	4H	17.84	19.12	18.24	19.47	19.85	13.14	14.42	13.54	14.76	15.14
	6H	18.33	19.51	18.74	19.88	20.27	13.52	14.70	13.93	15.07	15.46
	8H	18.49	19.62	18.92	20.01	20.41	13.64	14.77	14.07	15.16	15.56
	12H	18.60	19.68	19.03	20.06	20.49	13.72	14.80	14.15	15.18	15.61
4H	2H	15.51	16.79	15.91	17.14	17.52	12.06	13.34	12.46	13.69	14.07
	3H	17.45	18.51	17.86	18.91	19.31	13.51	14.57	13.92	14.97	15.37
	4H	18.19	19.15	18.63	19.57	20.01	14.11	15.06	14.54	15.48	15.92
	6H	18.79	19.62	19.24	20.06	20.52	14.59	15.43	15.05	15.87	16.33
	8H	19.00	19.78	19.46	20.22	20.69	14.76	15.53	15.22	15.98	16.45
	12H	19.15	19.85	19.64	20.33	20.80	14.87	15.57	15.36	16.05	16.52
8H	4H	18.22	19.00	18.68	19.44	19.91	14.46	15.24	14.92	15.68	16.15
	6H	18.86	19.50	19.35	19.99	20.47	15.05	15.69	15.54	16.18	16.66
	8H	19.11	19.68	19.62	20.19	20.68	15.27	15.84	15.78	16.35	16.84
	12H	19.31	19.82	19.82	20.31	20.88	15.45	15.96	15.96	16.45	17.01
12H	4H	18.20	18.90	18.69	19.38	19.85	14.50	15.20	14.99	15.68	16.15
	6H	18.84	19.41	19.35	19.92	20.41	15.11	15.69	15.62	16.20	16.69
	8H	19.12	19.63	19.63	20.12	20.69	15.38	15.89	15.89	16.39	16.95