

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931100

Luminaire Tested: DFN2DS-SQ4F0-070DS950-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931100
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ4F0-070DS950-RLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5622.7 lumens
Efficiency: N/A
Efficacy: 81.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.92' x L: 3.92' x H: 0')
CIE Type: Direct

Input Watts (W): 69.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931100

CATALOG NUMBER: DFN2DS-SQ4F0-070DS950-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931100

CATALOG NUMBER: DFN2DS-SQ4F0-070DS950-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1918	1918	1918
5°	1926	1894	1905
10°	1911	1863	1848
15°	1889	1808	1756
20°	1859	1729	1642
25°	1827	1640	1532
30°	1784	1547	1391
35°	1742	1448	1267
40°	1700	1344	1124
45°	1650	1228	994
50°	1599	1110	867
55°	1547	984	745
60°	1486	851	618
65°	1417	715	563
70°	1335	589	517
75°	1234	537	483
80°	1089	480	440
85°	856	378	378

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1650 cd/sqm

TEST NUMBER: P931100

CATALOG NUMBER: DFN2DS-SQ4F0-070DS950-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	256.2	4.6
10°-20°	703.4	12.5
20°-30°	987.6	17.6
30°-40°	1076.5	19.1
40°-50°	989.4	17.6
50°-60°	777.0	13.8
60°-70°	505.8	9.0
70°-80°	260.3	4.6
80°-90°	66.5	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1947.2	34.6
0°-40°	3023.7	53.8
0°-60°	4790.2	85.2
0°-90°	5622.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5622.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2734	2734	2734	2734	2734	
5°	2734	2722	2689	2712	2704	259
15°	2600	2573	2489	2442	2417	733
25°	2360	2281	2118	2016	1979	1086
35°	2034	1908	1690	1534	1480	1273
45°	1663	1497	1237	1061	1002	1284
55°	1264	1071	804	656	609	1130
65°	854	653	430	346	339	846
75°	455	282	198	181	178	481
85°	106	54	47	47	47	127
90°	0	0	0	0	0	

TEST NUMBER: P931100

CATALOG NUMBER: DFN2DS-SQ4F0-070DS950-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2734.0	2734.0	2734.0	2734.0	2734.0
2.5°	2746.3	2734.0	2706.7	2731.6	2726.6
5°	2734.0	2721.6	2689.4	2711.7	2704.3
7.5°	2711.7	2696.9	2662.3	2672.0	2659.7
10°	2682.0	2664.7	2615.3	2607.7	2593.0
12.5°	2645.0	2622.7	2555.8	2541.0	2513.7
15°	2600.4	2573.0	2489.0	2442.1	2417.4
17.5°	2548.4	2508.8	2404.8	2350.4	2310.8
20°	2489.0	2439.4	2315.8	2254.1	2199.5
22.5°	2424.8	2367.8	2224.2	2140.1	2103.2
25°	2360.4	2281.1	2117.8	2016.5	1979.3
27.5°	2283.8	2199.5	2018.9	1902.7	1845.7
30°	2202.1	2107.9	1909.9	1784.0	1717.1
32.5°	2122.8	2009.0	1806.3	1657.7	1595.7
35°	2033.8	1907.6	1690.0	1534.1	1479.5
37.5°	1947.3	1811.0	1581.1	1410.1	1348.5
40°	1855.6	1707.3	1467.1	1291.5	1227.2
42.5°	1761.7	1603.4	1353.4	1170.2	1108.6
45°	1662.7	1496.8	1237.2	1061.3	1002.0
47.5°	1568.7	1393.1	1125.9	950.0	895.7
50°	1464.8	1289.2	1016.9	846.1	794.4
52.5°	1363.2	1177.6	913.0	749.7	702.7
55°	1264.2	1071.3	804.0	655.7	608.8
57.5°	1162.9	964.9	707.7	569.1	529.5
60°	1059.0	861.0	606.1	480.2	440.5
62.5°	957.6	759.7	519.5	400.9	381.1
65°	853.6	653.1	430.5	346.5	338.9
67.5°	754.7	554.1	346.5	304.2	296.9
70°	650.7	457.8	286.9	262.2	252.2
72.5°	551.8	368.5	239.9	220.3	215.3
75°	455.2	281.9	197.9	180.6	178.2
77.5°	358.8	200.2	155.9	145.9	141.0
80°	269.6	143.5	118.7	109.0	109.0
82.5°	188.0	96.6	81.6	76.6	76.6
85°	106.3	54.3	47.0	47.0	47.0
87.5°	39.6	19.7	19.7	17.3	17.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931100

CATALOG NUMBER: DFN2DS-SQ4F0-070DS950-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.50	15.02	13.86	15.33	15.65	9.46	10.98	9.82	11.29	11.61
	3H	15.26	16.63	15.64	16.96	17.32	10.72	12.09	11.10	12.42	12.78
	4H	15.93	17.21	16.33	17.56	17.94	11.23	12.51	11.63	12.85	13.23
	6H	16.42	17.60	16.83	17.97	18.36	11.61	12.79	12.02	13.16	13.55
	8H	16.58	17.71	17.01	18.10	18.50	11.73	12.86	12.16	13.25	13.65
	12H	16.69	17.77	17.12	18.15	18.58	11.81	12.89	12.24	13.27	13.70
4H	2H	13.60	14.88	14.00	15.23	15.61	10.15	11.43	10.55	11.78	12.16
	3H	15.54	16.60	15.95	17.00	17.40	11.60	12.66	12.01	13.06	13.46
	4H	16.28	17.24	16.72	17.66	18.10	12.20	13.15	12.63	13.57	14.01
	6H	16.88	17.71	17.33	18.15	18.61	12.69	13.52	13.14	13.96	14.42
	8H	17.09	17.87	17.55	18.31	18.78	12.85	13.62	13.31	14.07	14.54
	12H	17.24	17.94	17.73	18.42	18.89	12.96	13.66	13.45	14.14	14.61
8H	4H	16.31	17.09	16.77	17.53	18.00	12.55	13.33	13.01	13.77	14.24
	6H	16.95	17.59	17.44	18.08	18.56	13.14	13.78	13.63	14.27	14.75
	8H	17.20	17.77	17.71	18.28	18.77	13.36	13.93	13.87	14.44	14.93
	12H	17.40	17.91	17.91	18.40	18.97	13.54	14.05	14.05	14.54	15.10
12H	4H	16.29	16.99	16.78	17.47	17.94	12.59	13.29	13.08	13.77	14.24
	6H	16.93	17.50	17.44	18.01	18.50	13.20	13.78	13.71	14.29	14.78
	8H	17.21	17.72	17.72	18.21	18.78	13.47	13.98	13.98	14.48	15.04