

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930560

Luminaire Tested: DFN2DS-PN3F0-050DS950-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930560
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN3F0-050DS950-RLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4016.3 lumens
Efficiency: N/A
Efficacy: 81.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.11' x L: 2.96' x H: 0')
CIE Type: Direct

Input Watts (W): 49.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930560

CATALOG NUMBER: DFN2DS-PN3F0-050DS950-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930560

CATALOG NUMBER: DFN2DS-PN3F0-050DS950-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2283	2283	2283
5°	2292	2254	2267
10°	2274	2217	2198
15°	2248	2152	2090
20°	2212	2058	1954
25°	2175	1951	1823
30°	2123	1842	1655
35°	2073	1723	1508
40°	2023	1599	1338
45°	1963	1461	1183
50°	1903	1321	1032
55°	1840	1170	886
60°	1768	1012	736
65°	1686	851	670
70°	1589	701	616
75°	1469	639	575
80°	1297	571	524
85°	1019	449	449

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1963 cd/sqm

TEST NUMBER: P930560

CATALOG NUMBER: DFN2DS-PN3F0-050DS950-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.0	4.6
10°-20°	502.4	12.5
20°-30°	705.4	17.6
30°-40°	768.9	19.1
40°-50°	706.7	17.6
50°-60°	555.0	13.8
60°-70°	361.3	9.0
70°-80°	186.0	4.6
80°-90°	47.5	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1390.9	34.6
0°-40°	2159.8	53.8
0°-60°	3421.5	85.2
0°-90°	4016.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4016.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1953	1953	1953	1953	1953	
5°	1953	1944	1921	1937	1932	185
15°	1857	1838	1778	1744	1727	523
25°	1686	1629	1513	1440	1414	775
35°	1453	1363	1207	1096	1057	909
45°	1188	1069	884	758	716	917
55°	903	765	574	468	435	807
65°	610	466	308	248	242	604
75°	325	201	141	129	127	344
85°	76	39	34	34	34	91
90°	0	0	0	0	0	

TEST NUMBER: P930560

CATALOG NUMBER: DFN2DS-PN3F0-050DS950-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1952.8	1952.8	1952.8	1952.8	1952.8
2.5°	1961.6	1952.8	1933.4	1951.1	1947.6
5°	1952.8	1944.1	1921.0	1936.9	1931.7
7.5°	1936.9	1926.4	1901.6	1908.6	1899.7
10°	1915.7	1903.3	1868.1	1862.7	1852.1
12.5°	1889.2	1873.4	1825.6	1815.1	1795.5
15°	1857.4	1837.9	1777.9	1744.4	1726.7
17.5°	1820.3	1792.0	1717.7	1678.9	1650.5
20°	1777.9	1742.5	1654.1	1610.1	1571.1
22.5°	1732.0	1691.3	1588.7	1528.7	1502.3
25°	1686.0	1629.4	1512.8	1440.4	1413.7
27.5°	1631.3	1571.1	1442.1	1359.0	1318.4
30°	1573.0	1505.7	1364.3	1274.2	1226.4
32.5°	1516.3	1435.0	1290.2	1184.1	1139.9
35°	1452.7	1362.6	1207.1	1095.7	1056.8
37.5°	1390.9	1293.6	1129.4	1007.3	963.2
40°	1325.5	1219.5	1047.9	922.5	876.6
42.5°	1258.4	1145.2	966.7	835.9	791.8
45°	1187.7	1069.2	883.7	758.1	715.6
47.5°	1120.5	995.1	804.2	678.6	639.8
50°	1046.3	920.8	726.4	604.3	567.4
52.5°	973.7	841.1	652.1	535.5	502.0
55°	903.0	765.2	574.3	468.3	434.8
57.5°	830.7	689.3	505.5	406.5	378.2
60°	756.4	615.0	432.9	342.9	314.6
62.5°	684.0	542.6	371.1	286.3	272.3
65°	609.7	466.5	307.5	247.5	242.1
67.5°	539.0	395.9	247.5	217.4	212.1
70°	464.8	327.0	205.0	187.3	180.2
72.5°	394.2	263.3	171.4	157.3	153.8
75°	325.2	201.4	141.4	129.0	127.3
77.5°	256.3	143.1	111.4	104.2	100.6
80°	192.6	102.5	84.8	77.8	77.8
82.5°	134.3	69.0	58.3	54.7	54.7
85°	76.0	38.8	33.5	33.5	33.5
87.5°	28.4	14.1	14.1	12.4	12.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930560

CATALOG NUMBER: DFN2DS-PN3F0-050DS950-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.10	15.62	14.47	15.94	16.25	10.06	11.58	10.43	11.90	12.21
	3H	15.87	17.23	16.25	17.56	17.92	11.33	12.69	11.71	13.02	13.38
	4H	16.53	17.82	16.93	18.16	18.54	11.83	13.11	12.23	13.46	13.84
	6H	17.02	18.21	17.44	18.57	18.96	12.21	13.39	12.62	13.76	14.15
	8H	17.19	18.32	17.62	18.70	19.11	12.34	13.46	12.76	13.85	14.25
	12H	17.29	18.37	17.72	18.75	19.18	12.42	13.49	12.85	13.88	14.31
4H	2H	14.21	15.49	14.61	15.84	16.21	10.76	12.04	11.16	12.39	12.77
	3H	16.14	17.20	16.55	17.60	18.00	12.20	13.26	12.61	13.66	14.07
	4H	16.89	17.85	17.32	18.26	18.70	12.80	13.76	13.23	14.17	14.61
	6H	17.48	18.31	17.94	18.76	19.22	13.29	14.12	13.75	14.56	15.02
	8H	17.70	18.47	18.16	18.92	19.38	13.45	14.23	13.91	14.67	15.14
	12H	17.85	18.54	18.33	19.02	19.49	13.57	14.26	14.05	14.74	15.21
8H	4H	16.91	17.69	17.38	18.14	18.60	13.16	13.93	13.62	14.38	14.84
	6H	17.55	18.19	18.05	18.68	19.16	13.74	14.38	14.24	14.87	15.35
	8H	17.80	18.38	18.32	18.89	19.38	13.96	14.54	14.48	15.05	15.54
	12H	18.01	18.52	18.52	19.01	19.57	14.14	14.65	14.65	15.14	15.71
12H	4H	16.90	17.59	17.38	18.07	18.54	13.20	13.89	13.68	14.37	14.84
	6H	17.53	18.11	18.05	18.62	19.11	13.80	14.38	14.32	14.89	15.38
	8H	17.82	18.33	18.33	18.82	19.38	14.08	14.59	14.59	15.08	15.64