

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930724

Luminaire Tested: DFN2DS-PN4F0-090DS830-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930724
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN4F0-090DS830-RLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7206.4 lumens
Efficiency: N/A
Efficacy: 77.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.94' x L: 3.74' x H: 0')
CIE Type: Direct

Input Watts (W): 93.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930724

CATALOG NUMBER: DFN2DS-PN4F0-090DS830-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930724

CATALOG NUMBER: DFN2DS-PN4F0-090DS830-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2558	2558	2558
5°	2568	2526	2540
10°	2548	2484	2463
15°	2519	2411	2341
20°	2478	2306	2190
25°	2437	2186	2043
30°	2379	2063	1855
35°	2323	1930	1690
40°	2266	1792	1499
45°	2200	1637	1326
50°	2132	1480	1156
55°	2062	1311	993
60°	1981	1134	824
65°	1890	953	750
70°	1780	785	690
75°	1645	716	644
80°	1452	639	587
85°	1141	504	504

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2200 cd/sqm

TEST NUMBER: P930724

CATALOG NUMBER: DFN2DS-PN4F0-090DS830-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	328.4	4.6
10°-20°	901.5	12.5
20°-30°	1265.7	17.6
30°-40°	1379.7	19.1
40°-50°	1268.1	17.6
50°-60°	995.9	13.8
60°-70°	648.2	9.0
70°-80°	333.7	4.6
80°-90°	85.2	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2495.6	34.6
0°-40°	3875.3	53.8
0°-60°	6139.3	85.2
0°-90°	7206.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7206.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3504	3504	3504	3504	3504	
5°	3504	3488	3447	3475	3466	332
15°	3333	3298	3190	3130	3098	939
25°	3025	2924	2714	2584	2537	1391
35°	2607	2445	2166	1966	1896	1632
45°	2131	1918	1586	1360	1284	1646
55°	1620	1373	1030	840	780	1448
65°	1094	837	552	444	434	1085
75°	583	361	254	231	228	617
85°	136	70	60	60	60	163
90°	0	0	0	0	0	

TEST NUMBER: P930724

CATALOG NUMBER: DFN2DS-PN4F0-090DS830-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3504.0	3504.0	3504.0	3504.0	3504.0
2.5°	3519.8	3504.0	3468.9	3500.9	3494.5
5°	3504.0	3488.1	3446.8	3475.3	3465.9
7.5°	3475.3	3456.5	3412.1	3424.5	3408.7
10°	3437.4	3415.1	3351.9	3342.1	3323.3
12.5°	3389.9	3361.3	3275.5	3256.7	3221.6
15°	3332.7	3297.8	3190.1	3129.8	3098.2
17.5°	3266.1	3215.3	3082.0	3012.4	2961.6
20°	3190.1	3126.5	2968.0	2888.9	2818.9
22.5°	3107.7	3034.7	2850.6	2742.9	2695.5
25°	3025.2	2923.6	2714.4	2584.5	2536.7
27.5°	2927.0	2818.9	2587.5	2438.5	2365.5
30°	2822.3	2701.6	2447.9	2286.4	2200.6
32.5°	2720.7	2574.7	2315.0	2124.6	2045.2
35°	2606.7	2444.9	2165.9	1966.1	1896.2
37.5°	2495.6	2321.1	2026.3	1807.3	1728.3
40°	2378.3	2188.2	1880.3	1655.3	1572.9
42.5°	2257.8	2055.0	1734.6	1499.9	1420.7
45°	2131.0	1918.4	1585.6	1360.2	1284.1
47.5°	2010.5	1785.5	1443.0	1217.5	1147.9
50°	1877.3	1652.2	1303.4	1084.3	1018.0
52.5°	1747.1	1509.3	1170.2	960.8	900.6
55°	1620.2	1373.0	1030.5	840.5	780.2
57.5°	1490.4	1236.8	907.1	729.4	678.6
60°	1357.1	1103.5	776.9	615.3	564.5
62.5°	1227.3	973.7	665.8	513.8	488.5
65°	1094.0	837.1	551.7	444.1	434.4
67.5°	967.2	710.2	444.1	389.9	380.5
70°	834.0	586.8	367.8	336.1	323.3
72.5°	707.2	472.3	307.5	282.2	275.9
75°	583.4	361.4	253.7	231.4	228.4
77.5°	459.9	256.7	199.8	187.1	180.7
80°	345.5	184.1	152.0	139.6	139.6
82.5°	240.9	123.8	104.7	98.3	98.3
85°	136.2	69.6	60.2	60.2	60.2
87.5°	50.8	25.2	25.2	22.2	22.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930724

CATALOG NUMBER: DFN2DS-PN4F0-090DS830-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.50	16.02	14.86	16.33	16.65	10.46	11.98	10.82	12.29	12.61
	3H	16.26	17.63	16.64	17.96	18.32	11.72	13.09	12.10	13.42	13.78
	4H	16.93	18.21	17.33	18.56	18.94	12.22	13.51	12.62	13.85	14.23
	6H	17.42	18.60	17.83	18.97	19.36	12.61	13.79	13.02	14.16	14.55
	8H	17.58	18.71	18.01	19.10	19.50	12.73	13.86	13.16	14.25	14.65
	12H	17.69	18.76	18.12	19.15	19.58	12.81	13.89	13.24	14.27	14.70
4H	2H	14.60	15.88	15.00	16.23	16.61	11.15	12.43	11.55	12.78	13.16
	3H	16.53	17.60	16.95	18.00	18.40	12.60	13.66	13.01	14.06	14.46
	4H	17.28	18.24	17.72	18.66	19.10	13.20	14.15	13.63	14.57	15.01
	6H	17.88	18.71	18.33	19.15	19.61	13.68	14.52	14.14	14.96	15.42
	8H	18.09	18.87	18.55	19.31	19.78	13.85	14.62	14.31	15.07	15.54
	12H	18.24	18.94	18.73	19.42	19.89	13.96	14.66	14.45	15.14	15.61
8H	4H	17.31	18.09	17.77	18.53	19.00	13.55	14.33	14.01	14.77	15.24
	6H	17.95	18.59	18.44	19.08	19.56	14.14	14.78	14.63	15.27	15.75
	8H	18.20	18.77	18.71	19.28	19.77	14.36	14.93	14.87	15.44	15.93
	12H	18.40	18.91	18.91	19.40	19.97	14.54	15.05	15.05	15.54	16.10
12H	4H	17.29	17.99	17.78	18.47	18.94	13.59	14.29	14.08	14.77	15.24
	6H	17.93	18.50	18.44	19.01	19.50	14.20	14.78	14.71	15.29	15.78
	8H	18.21	18.72	18.72	19.21	19.78	14.47	14.98	14.98	15.48	16.04