

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931426

Luminaire Tested: DFN2DS-TR3F0-090DS830-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931426
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-090DS830-RLL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7206.4 lumens
Efficiency: N/A
Efficacy: 72.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 99.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931426

CATALOG NUMBER: DFN2DS-TR3F0-090DS830-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931426

CATALOG NUMBER: DFN2DS-TR3F0-090DS830-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4366	4366	4366
5°	4383	4311	4335
10°	4349	4241	4205
15°	4299	4115	3997
20°	4230	3936	3738
25°	4159	3732	3488
30°	4061	3522	3166
35°	3965	3295	2885
40°	3869	3059	2559
45°	3755	2794	2263
50°	3639	2527	1973
55°	3520	2239	1695
60°	3382	1936	1407
65°	3226	1627	1281
70°	3039	1340	1178
75°	2809	1221	1100
80°	2479	1091	1002
85°	1947	861	861

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3755 cd/sqm

TEST NUMBER: P931426

CATALOG NUMBER: DFN2DS-TR3F0-090DS830-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	328.4	4.6
10°-20°	901.5	12.5
20°-30°	1265.7	17.6
30°-40°	1379.7	19.1
40°-50°	1268.1	17.6
50°-60°	995.9	13.8
60°-70°	648.2	9.0
70°-80°	333.7	4.6
80°-90°	85.2	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2495.6	34.6
0°-40°	3875.3	53.8
0°-60°	6139.3	85.2
0°-90°	7206.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7206.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3504	3504	3504	3504	3504	
5°	3504	3488	3447	3475	3466	332
15°	3333	3298	3190	3130	3098	939
25°	3025	2924	2714	2584	2537	1391
35°	2607	2445	2166	1966	1896	1632
45°	2131	1918	1586	1360	1284	1646
55°	1620	1373	1030	840	780	1448
65°	1094	837	552	444	434	1085
75°	583	361	254	231	228	617
85°	136	70	60	60	60	163
90°	0	0	0	0	0	

TEST NUMBER: P931426

CATALOG NUMBER: DFN2DS-TR3F0-090DS830-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3504.0	3504.0	3504.0	3504.0	3504.0
2.5°	3519.8	3504.0	3468.9	3500.9	3494.5
5°	3504.0	3488.1	3446.8	3475.3	3465.9
7.5°	3475.3	3456.5	3412.1	3424.5	3408.7
10°	3437.4	3415.1	3351.9	3342.1	3323.3
12.5°	3389.9	3361.3	3275.5	3256.7	3221.6
15°	3332.7	3297.8	3190.1	3129.8	3098.2
17.5°	3266.1	3215.3	3082.0	3012.4	2961.6
20°	3190.1	3126.5	2968.0	2888.9	2818.9
22.5°	3107.7	3034.7	2850.6	2742.9	2695.5
25°	3025.2	2923.6	2714.4	2584.5	2536.7
27.5°	2927.0	2818.9	2587.5	2438.5	2365.5
30°	2822.3	2701.6	2447.9	2286.4	2200.6
32.5°	2720.7	2574.7	2315.0	2124.6	2045.2
35°	2606.7	2444.9	2165.9	1966.1	1896.2
37.5°	2495.6	2321.1	2026.3	1807.3	1728.3
40°	2378.3	2188.2	1880.3	1655.3	1572.9
42.5°	2257.8	2055.0	1734.6	1499.9	1420.7
45°	2131.0	1918.4	1585.6	1360.2	1284.1
47.5°	2010.5	1785.5	1443.0	1217.5	1147.9
50°	1877.3	1652.2	1303.4	1084.3	1018.0
52.5°	1747.1	1509.3	1170.2	960.8	900.6
55°	1620.2	1373.0	1030.5	840.5	780.2
57.5°	1490.4	1236.8	907.1	729.4	678.6
60°	1357.1	1103.5	776.9	615.3	564.5
62.5°	1227.3	973.7	665.8	513.8	488.5
65°	1094.0	837.1	551.7	444.1	434.4
67.5°	967.2	710.2	444.1	389.9	380.5
70°	834.0	586.8	367.8	336.1	323.3
72.5°	707.2	472.3	307.5	282.2	275.9
75°	583.4	361.4	253.7	231.4	228.4
77.5°	459.9	256.7	199.8	187.1	180.7
80°	345.5	184.1	152.0	139.6	139.6
82.5°	240.9	123.8	104.7	98.3	98.3
85°	136.2	69.6	60.2	60.2	60.2
87.5°	50.8	25.2	25.2	22.2	22.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931426

CATALOG NUMBER: DFN2DS-TR3F0-090DS830-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.36	17.88	16.72	18.19	18.51	12.32	13.84	12.68	14.15	14.47
	3H	18.12	19.49	18.50	19.81	20.18	13.58	14.95	13.96	15.27	15.64
	4H	18.79	20.07	19.19	20.42	20.80	14.08	15.36	14.48	15.71	16.09
	6H	19.28	20.46	19.69	20.83	21.22	14.46	15.65	14.88	16.01	16.41
	8H	19.44	20.57	19.87	20.96	21.36	14.59	15.72	15.02	16.10	16.51
	12H	19.54	20.62	19.98	21.01	21.43	14.67	15.75	15.10	16.13	16.56
4H	2H	16.46	17.74	16.86	18.09	18.47	13.01	14.29	13.41	14.64	15.02
	3H	18.39	19.46	18.80	19.86	20.26	14.45	15.52	14.87	15.92	16.32
	4H	19.14	20.10	19.58	20.51	20.95	15.05	16.01	15.49	16.43	16.86
	6H	19.73	20.57	20.19	21.01	21.47	15.54	16.37	16.00	16.82	17.28
	8H	19.95	20.73	20.41	21.17	21.64	15.70	16.48	16.17	16.93	17.39
	12H	20.10	20.80	20.58	21.28	21.75	15.82	16.52	16.30	16.99	17.47
8H	4H	19.17	19.94	19.63	20.39	20.86	15.41	16.19	15.87	16.63	17.10
	6H	19.80	20.45	20.30	20.94	21.42	15.99	16.64	16.49	17.13	17.61
	8H	20.05	20.63	20.57	21.14	21.63	16.22	16.79	16.73	17.30	17.79
	12H	20.26	20.77	20.77	21.26	21.83	16.39	16.90	16.90	17.40	17.96
12H	4H	19.15	19.85	19.63	20.32	20.80	15.45	16.15	15.93	16.62	17.10
	6H	19.78	20.36	20.30	20.87	21.36	16.06	16.64	16.57	17.15	17.63
	8H	20.07	20.58	20.58	21.07	21.64	16.33	16.84	16.84	17.33	17.90