

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931319

Luminaire Tested: DFN2DS-TR3F0-030DS835-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931319
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-030DS835-FLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2970.0 lumens
Efficiency: N/A
Efficacy: 105.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 28.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931319

CATALOG NUMBER: DFN2DS-TR3F0-030DS835-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931319

CATALOG NUMBER: DFN2DS-TR3F0-030DS835-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1455	1455	1455
5°	1460	1439	1448
10°	1452	1425	1432
15°	1434	1406	1405
20°	1408	1378	1377
25°	1383	1344	1344
30°	1350	1313	1302
35°	1320	1276	1257
40°	1282	1238	1214
45°	1244	1201	1171
50°	1203	1162	1121
55°	1161	1117	1076
60°	1113	1063	1024
65°	1063	1010	963
70°	998	945	900
75°	908	870	849
80°	806	781	741
85°	658	626	562

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1244 cd/sqm

TEST NUMBER: P931319

CATALOG NUMBER: DFN2DS-TR3F0-030DS835-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.9	3.7
10°-20°	309.1	10.4
20°-30°	454.3	15.3
30°-40°	527.6	17.8
40°-50°	527.0	17.7
50°-60°	459.5	15.5
60°-70°	339.7	11.4
70°-80°	192.2	6.5
80°-90°	50.7	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	873.3	29.4
0°-40°	1400.9	47.2
0°-60°	2387.4	80.4
0°-90°	2970.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2970.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1167	1167	1167	1167	1167	
5°	1167	1163	1150	1160	1157	111
15°	1111	1105	1090	1094	1089	313
25°	1006	997	978	980	978	463
35°	868	856	838	832	826	542
45°	706	698	681	669	664	545
55°	534	528	514	501	495	478
65°	360	354	342	332	327	356
75°	188	186	181	174	176	201
85°	46	45	44	40	39	54
90°	0	0	0	0	0	

TEST NUMBER: P931319

CATALOG NUMBER: DFN2DS-TR3F0-030DS835-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1167.3	1167.3	1167.3	1167.3	1167.3
2.5°	1174.1	1168.5	1156.1	1167.3	1165.2
5°	1167.3	1162.9	1150.5	1159.5	1157.3
7.5°	1159.5	1152.8	1140.4	1149.5	1147.2
10°	1147.2	1139.3	1125.9	1134.8	1131.5
12.5°	1130.3	1123.6	1110.2	1115.7	1113.5
15°	1111.2	1104.6	1089.9	1094.4	1088.8
17.5°	1087.6	1081.0	1066.3	1071.9	1066.3
20°	1061.8	1055.1	1039.4	1042.7	1038.3
22.5°	1036.1	1026.0	1011.3	1011.3	1009.0
25°	1005.7	996.8	977.7	979.9	977.7
27.5°	972.0	964.1	949.6	946.3	940.7
30°	938.4	929.4	912.6	909.2	904.7
32.5°	902.5	895.8	877.8	871.0	866.5
35°	867.7	856.5	838.5	831.7	826.1
37.5°	828.4	818.3	800.3	792.4	786.8
40°	788.0	779.0	761.0	751.0	746.5
42.5°	748.7	739.7	721.8	710.5	703.8
45°	706.1	698.2	681.3	669.0	664.5
47.5°	664.5	656.7	638.7	626.3	619.6
50°	620.7	615.1	599.4	583.7	578.1
52.5°	578.1	570.2	555.7	543.3	535.4
55°	534.4	527.6	514.1	500.7	495.1
57.5°	490.5	484.9	470.3	456.8	452.3
60°	446.7	442.3	426.6	414.2	410.9
62.5°	404.1	396.2	385.0	373.8	369.3
65°	360.4	353.6	342.4	332.3	326.7
67.5°	315.5	309.8	299.7	291.9	287.4
70°	273.9	269.4	259.3	251.4	247.0
72.5°	231.3	226.7	221.1	213.3	210.0
75°	188.5	186.4	180.7	174.0	176.3
77.5°	150.4	145.9	143.6	140.3	137.0
80°	112.3	111.1	108.8	105.5	103.3
82.5°	76.3	76.3	75.3	70.7	70.7
85°	46.0	44.9	43.8	40.4	39.3
87.5°	20.2	18.0	15.7	12.4	11.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931319

CATALOG NUMBER: DFN2DS-TR3F0-030DS835-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.58	14.19	12.95	14.51	14.82	12.14	13.75	12.50	14.06	14.38
	3H	14.33	15.79	14.71	16.12	16.48	13.84	15.30	14.22	15.62	15.99
	4H	14.98	16.35	15.38	16.70	17.07	14.49	15.86	14.88	16.20	16.58
	6H	15.45	16.72	15.86	17.08	17.47	14.95	16.22	15.36	16.58	16.97
	8H	15.59	16.80	16.02	17.19	17.59	15.09	16.30	15.52	16.69	17.09
	12H	15.68	16.84	16.11	17.22	17.65	15.17	16.33	15.60	16.71	17.14
4H	2H	13.14	14.51	13.54	14.86	15.24	12.79	14.16	13.19	14.51	14.88
	3H	15.12	16.27	15.53	16.66	17.06	14.71	15.86	15.12	16.26	16.66
	4H	15.90	16.93	16.33	17.35	17.78	15.47	16.51	15.90	16.92	17.36
	6H	16.49	17.40	16.95	17.84	18.29	16.06	16.97	16.52	17.41	17.86
	8H	16.68	17.53	17.14	17.97	18.44	16.24	17.09	16.71	17.53	18.00
	12H	16.81	17.57	17.29	18.05	18.52	16.36	17.12	16.84	17.60	18.07
8H	4H	16.17	17.02	16.63	17.46	17.92	15.80	16.64	16.26	17.08	17.55
	6H	16.88	17.59	17.38	18.08	18.55	16.50	17.21	17.00	17.69	18.17
	8H	17.14	17.77	17.65	18.28	18.77	16.75	17.38	17.26	17.89	18.38
	12H	17.34	17.90	17.85	18.39	18.95	16.93	17.49	17.44	17.98	18.54
12H	4H	16.20	16.96	16.68	17.43	17.90	15.83	16.59	16.31	17.07	17.54
	6H	16.93	17.56	17.44	18.07	18.55	16.56	17.19	17.07	17.70	18.19
	8H	17.24	17.80	17.75	18.29	18.85	16.87	17.42	17.37	17.91	18.48