

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931337

Luminaire Tested: DFN2DS-TR3F0-040DS835-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931337
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-040DS835-FLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3960.0 lumens
Efficiency: N/A
Efficacy: 101.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 39.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931337

CATALOG NUMBER: DFN2DS-TR3F0-040DS835-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931337

CATALOG NUMBER: DFN2DS-TR3F0-040DS835-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1939	1939	1939
5°	1947	1919	1930
10°	1935	1900	1909
15°	1911	1875	1873
20°	1877	1838	1836
25°	1844	1792	1792
30°	1800	1751	1736
35°	1760	1701	1676
40°	1709	1650	1619
45°	1659	1601	1561
50°	1604	1549	1494
55°	1548	1489	1434
60°	1484	1418	1365
65°	1417	1346	1284
70°	1331	1260	1200
75°	1210	1160	1131
80°	1074	1041	988
85°	876	835	749

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1659 cd/sqm

TEST NUMBER: P931337

CATALOG NUMBER: DFN2DS-TR3F0-040DS835-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.5	3.7
10°-20°	412.2	10.4
20°-30°	605.7	15.3
30°-40°	703.5	17.8
40°-50°	702.6	17.7
50°-60°	612.7	15.5
60°-70°	452.9	11.4
70°-80°	256.2	6.5
80°-90°	67.6	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1164.4	29.4
0°-40°	1867.9	47.2
0°-60°	3183.2	80.4
0°-90°	3960.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3960.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1556	1556	1556	1556	1556	
5°	1556	1550	1534	1546	1543	148
15°	1482	1473	1453	1459	1452	417
25°	1341	1329	1304	1306	1304	617
35°	1157	1142	1118	1109	1102	722
45°	941	931	908	892	886	727
55°	712	703	686	668	660	637
65°	480	471	456	443	436	475
75°	251	248	241	232	235	268
85°	61	60	58	54	52	72
90°	0	0	0	0	0	

TEST NUMBER: P931337

CATALOG NUMBER: DFN2DS-TR3F0-040DS835-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1556.4	1556.4	1556.4	1556.4	1556.4
2.5°	1565.5	1558.0	1541.5	1556.4	1553.6
5°	1556.4	1550.5	1534.0	1545.9	1543.1
7.5°	1545.9	1537.0	1520.5	1532.6	1529.6
10°	1529.6	1519.1	1501.2	1513.1	1508.6
12.5°	1507.0	1498.1	1480.2	1487.7	1484.6
15°	1481.6	1472.7	1453.2	1459.2	1451.8
17.5°	1450.2	1441.3	1421.8	1429.2	1421.8
20°	1415.7	1406.8	1385.9	1390.3	1384.5
22.5°	1381.4	1367.9	1348.4	1348.4	1345.4
25°	1340.9	1329.0	1303.6	1306.5	1303.6
27.5°	1296.0	1285.5	1266.2	1261.7	1254.3
30°	1251.2	1239.2	1216.8	1212.3	1206.3
32.5°	1203.3	1194.4	1170.4	1161.4	1155.3
35°	1156.9	1142.0	1118.0	1109.0	1101.5
37.5°	1104.5	1091.0	1067.0	1056.6	1049.1
40°	1050.7	1038.6	1014.6	1001.3	995.3
42.5°	998.3	986.2	962.4	947.3	938.4
45°	941.4	931.0	908.4	892.1	886.0
47.5°	886.0	875.5	851.6	835.1	826.2
50°	827.6	820.1	799.2	778.2	770.7
52.5°	770.7	760.3	740.9	724.4	713.9
55°	712.5	703.4	685.5	667.5	660.1
57.5°	654.0	646.6	627.0	609.1	603.1
60°	595.6	589.7	568.8	552.3	547.8
62.5°	538.8	528.3	513.4	498.4	492.4
65°	480.5	471.4	456.5	443.0	435.6
67.5°	420.6	413.0	399.7	389.2	383.2
70°	365.2	359.2	345.7	335.2	329.3
72.5°	308.4	302.3	294.9	284.4	279.9
75°	251.4	248.5	240.9	232.0	235.0
77.5°	200.5	194.5	191.5	187.0	182.6
80°	149.7	148.1	145.1	140.7	137.7
82.5°	101.8	101.8	100.4	94.3	94.3
85°	61.3	59.9	58.4	53.8	52.4
87.5°	27.0	24.0	21.0	16.5	14.9
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931337

CATALOG NUMBER: DFN2DS-TR3F0-040DS835-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.58	15.19	13.95	15.51	15.82	13.14	14.75	13.50	15.06	15.38
	3H	15.33	16.79	15.71	17.12	17.48	14.84	16.30	15.22	16.62	16.98
	4H	15.98	17.35	16.38	17.70	18.07	15.49	16.85	15.88	17.20	17.58
	6H	16.45	17.72	16.86	18.08	18.47	15.95	17.22	16.36	17.58	17.97
	8H	16.59	17.80	17.02	18.19	18.59	16.09	17.30	16.51	17.69	18.09
	12H	16.68	17.84	17.11	18.22	18.65	16.17	17.33	16.60	17.71	18.14
4H	2H	14.14	15.51	14.54	15.86	16.24	13.79	15.16	14.19	15.51	15.88
	3H	16.12	17.27	16.53	17.66	18.06	15.71	16.86	16.12	17.26	17.66
	4H	16.90	17.93	17.33	18.35	18.78	16.47	17.51	16.90	17.92	18.36
	6H	17.49	18.40	17.95	18.84	19.29	17.06	17.96	17.51	18.41	18.86
	8H	17.68	18.53	18.14	18.97	19.44	17.24	18.09	17.70	18.53	19.00
	12H	17.81	18.57	18.29	19.05	19.52	17.36	18.12	17.84	18.60	19.07
8H	4H	17.17	18.02	17.63	18.46	18.92	16.80	17.64	17.26	18.08	18.55
	6H	17.88	18.59	18.38	19.07	19.55	17.50	18.21	18.00	18.69	19.17
	8H	18.14	18.77	18.65	19.28	19.77	17.75	18.38	18.26	18.89	19.37
	12H	18.34	18.90	18.85	19.39	19.95	17.93	18.49	18.44	18.98	19.54
12H	4H	17.20	17.96	17.68	18.43	18.90	16.83	17.59	17.31	18.07	18.54
	6H	17.93	18.56	18.44	19.07	19.55	17.56	18.19	18.07	18.70	19.19
	8H	18.24	18.80	18.75	19.29	19.85	17.87	18.42	18.37	18.91	19.47