

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931355

Luminaire Tested: DFN2DS-TR3F0-050DS835-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931355
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-050DS835-FLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4950.0 lumens
Efficiency: N/A
Efficacy: 99.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931355

CATALOG NUMBER: DFN2DS-TR3F0-050DS835-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931355

CATALOG NUMBER: DFN2DS-TR3F0-050DS835-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2424	2424	2424
5°	2434	2399	2413
10°	2419	2374	2386
15°	2389	2343	2341
20°	2347	2297	2295
25°	2305	2240	2240
30°	2250	2189	2170
35°	2200	2126	2095
40°	2136	2063	2024
45°	2074	2001	1952
50°	2005	1937	1868
55°	1935	1861	1793
60°	1855	1772	1707
65°	1771	1682	1605
70°	1663	1574	1500
75°	1513	1450	1415
80°	1343	1302	1235
85°	1095	1044	936

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2074 cd/sqm

TEST NUMBER: P931355

CATALOG NUMBER: DFN2DS-TR3F0-050DS835-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.1	3.7
10°-20°	515.2	10.4
20°-30°	757.2	15.3
30°-40°	879.4	17.8
40°-50°	878.3	17.7
50°-60°	765.8	15.5
60°-70°	566.1	11.4
70°-80°	320.3	6.5
80°-90°	84.5	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1455.5	29.4
0°-40°	2334.9	47.2
0°-60°	3979.0	80.4
0°-90°	4950.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4950.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1946	1946	1946	1946	1946	
5°	1946	1938	1918	1932	1929	185
15°	1852	1841	1816	1824	1815	522
25°	1676	1661	1630	1633	1630	771
35°	1446	1428	1398	1386	1377	903
45°	1177	1164	1136	1115	1108	908
55°	891	879	857	834	825	796
65°	601	589	571	554	544	594
75°	314	311	301	290	294	335
85°	77	75	73	67	66	90
90°	0	0	0	0	0	

TEST NUMBER: P931355

CATALOG NUMBER: DFN2DS-TR3F0-050DS835-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1945.5	1945.5	1945.5	1945.5	1945.5
2.5°	1956.8	1947.5	1926.9	1945.5	1942.0
5°	1945.5	1938.2	1917.5	1932.4	1928.9
7.5°	1932.4	1921.3	1900.7	1915.8	1912.0
10°	1912.0	1898.9	1876.5	1891.3	1885.8
12.5°	1883.8	1872.7	1850.3	1859.6	1855.8
15°	1852.0	1840.9	1816.5	1824.1	1814.7
17.5°	1812.7	1801.6	1777.2	1786.5	1777.2
20°	1769.7	1758.6	1732.4	1737.9	1730.6
22.5°	1726.8	1709.9	1685.5	1685.5	1681.7
25°	1676.2	1661.3	1629.5	1633.1	1629.5
27.5°	1620.0	1606.9	1582.7	1577.1	1567.8
30°	1564.0	1549.0	1521.0	1515.4	1507.9
32.5°	1504.1	1493.0	1463.0	1451.7	1444.2
35°	1446.1	1427.5	1397.5	1386.2	1376.9
37.5°	1380.6	1363.8	1333.8	1320.7	1311.4
40°	1313.4	1298.3	1268.3	1251.6	1244.1
42.5°	1247.9	1232.8	1203.0	1184.1	1173.0
45°	1176.8	1163.7	1135.5	1115.1	1107.5
47.5°	1107.5	1094.4	1064.5	1043.8	1032.7
50°	1034.5	1025.2	999.0	972.8	963.4
52.5°	963.4	950.3	926.1	905.5	892.4
55°	890.6	879.3	856.8	834.4	825.1
57.5°	817.5	808.2	783.8	761.4	753.8
60°	744.5	737.2	711.0	690.3	684.8
62.5°	673.5	660.4	641.7	623.0	615.5
65°	600.6	589.3	570.6	553.8	544.4
67.5°	525.8	516.3	499.6	486.5	478.9
70°	456.5	449.0	432.1	419.0	411.7
72.5°	385.5	377.9	368.6	355.5	349.9
75°	314.2	310.6	301.1	290.0	293.8
77.5°	250.7	243.1	239.4	233.8	228.3
80°	187.2	185.2	181.4	175.9	172.1
82.5°	127.2	127.2	125.4	117.9	117.9
85°	76.6	74.8	73.0	67.3	65.5
87.5°	33.7	30.0	26.2	20.6	18.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931355

CATALOG NUMBER: DFN2DS-TR3F0-050DS835-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.36	15.97	14.72	16.28	16.60	13.92	15.53	14.28	15.84	16.15
	3H	16.11	17.56	16.49	17.89	18.25	15.62	17.07	16.00	17.40	17.76
	4H	16.76	18.12	17.15	18.47	18.85	16.26	17.63	16.66	17.98	18.35
	6H	17.22	18.49	17.64	18.86	19.25	16.72	17.99	17.13	18.36	18.75
	8H	17.37	18.58	17.79	18.97	19.37	16.87	18.08	17.29	18.46	18.86
	12H	17.46	18.62	17.89	19.00	19.43	16.95	18.11	17.38	18.49	18.92
4H	2H	14.92	16.29	15.32	16.64	17.01	14.57	15.94	14.97	16.28	16.66
	3H	16.89	18.04	17.30	18.44	18.84	16.49	17.63	16.90	18.03	18.43
	4H	17.67	18.71	18.10	19.12	19.56	17.25	18.28	17.68	18.70	19.13
	6H	18.27	19.17	18.72	19.61	20.07	17.84	18.74	18.29	19.18	19.64
	8H	18.46	19.30	18.92	19.75	20.21	18.02	18.87	18.48	19.31	19.77
	12H	18.59	19.35	19.07	19.82	20.29	18.14	18.90	18.62	19.37	19.84
8H	4H	17.94	18.79	18.41	19.23	19.70	17.57	18.42	18.03	18.86	19.32
	6H	18.66	19.36	19.15	19.85	20.33	18.28	18.98	18.77	19.47	19.94
	8H	18.92	19.55	19.43	20.06	20.54	18.53	19.16	19.04	19.66	20.15
	12H	19.12	19.68	19.62	20.17	20.73	18.71	19.26	19.21	19.75	20.31
12H	4H	17.97	18.73	18.45	19.21	19.68	17.61	18.37	18.09	18.84	19.31
	6H	18.70	19.34	19.21	19.84	20.33	18.34	18.97	18.85	19.47	19.96
	8H	19.02	19.58	19.53	20.07	20.63	18.64	19.20	19.15	19.69	20.25