

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931373

Luminaire Tested: DFN2DS-TR3F0-060DS835-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931373
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-060DS835-FLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5940.0 lumens
Efficiency: N/A
Efficacy: 96.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 61.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931373

CATALOG NUMBER: DFN2DS-TR3F0-060DS835-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931373

CATALOG NUMBER: DFN2DS-TR3F0-060DS835-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2909	2909	2909
5°	2920	2878	2895
10°	2903	2849	2863
15°	2867	2812	2809
20°	2816	2757	2754
25°	2766	2689	2689
30°	2701	2626	2604
35°	2640	2551	2513
40°	2564	2476	2428
45°	2489	2401	2342
50°	2407	2324	2241
55°	2322	2234	2151
60°	2227	2126	2048
65°	2125	2019	1926
70°	1996	1889	1800
75°	1815	1740	1697
80°	1612	1562	1482
85°	1314	1252	1124

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2489 cd/sqm

TEST NUMBER: P931373

CATALOG NUMBER: DFN2DS-TR3F0-060DS835-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.7	3.7
10°-20°	618.3	10.4
20°-30°	908.6	15.3
30°-40°	1055.3	17.8
40°-50°	1054.0	17.7
50°-60°	919.0	15.5
60°-70°	679.4	11.4
70°-80°	384.4	6.5
80°-90°	101.4	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1746.6	29.4
0°-40°	2801.8	47.2
0°-60°	4774.8	80.4
0°-90°	5940.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5940.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2335	2335	2335	2335	2335	
5°	2335	2326	2301	2319	2315	222
15°	2222	2209	2180	2189	2178	626
25°	2011	1994	1955	1960	1955	926
35°	1735	1713	1677	1663	1652	1084
45°	1412	1396	1363	1338	1329	1090
55°	1069	1055	1028	1001	990	955
65°	721	707	685	664	653	713
75°	377	373	361	348	352	402
85°	92	90	88	81	79	108
90°	0	0	0	0	0	

TEST NUMBER: P931373

CATALOG NUMBER: DFN2DS-TR3F0-060DS835-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2334.6	2334.6	2334.6	2334.6	2334.6
2.5°	2348.2	2337.0	2312.2	2334.6	2330.3
5°	2334.6	2325.8	2301.0	2318.9	2314.6
7.5°	2318.9	2305.6	2280.8	2298.9	2294.4
10°	2294.4	2278.7	2251.7	2269.6	2262.9
12.5°	2260.6	2247.2	2220.3	2231.5	2227.0
15°	2222.4	2209.1	2179.8	2188.9	2177.7
17.5°	2175.3	2162.0	2132.7	2143.8	2132.7
20°	2123.6	2110.3	2078.8	2085.5	2076.7
22.5°	2072.2	2051.9	2022.6	2022.6	2018.1
25°	2011.4	1993.6	1955.4	1959.7	1955.4
27.5°	1944.0	1928.3	1899.2	1892.6	1881.4
30°	1876.9	1858.7	1825.2	1818.5	1809.4
32.5°	1804.9	1791.6	1755.6	1742.0	1733.0
35°	1735.4	1713.0	1677.0	1663.4	1652.2
37.5°	1656.8	1636.5	1600.6	1584.8	1573.6
40°	1576.0	1557.9	1522.0	1502.0	1492.9
42.5°	1497.4	1479.3	1443.6	1421.0	1407.6
45°	1412.2	1396.4	1362.6	1338.1	1329.0
47.5°	1329.0	1313.3	1277.4	1252.6	1239.2
50°	1241.4	1230.2	1198.8	1167.3	1156.1
52.5°	1156.1	1140.4	1111.3	1086.6	1070.9
55°	1068.7	1055.1	1028.2	1001.3	990.1
57.5°	981.1	969.9	940.6	913.7	904.6
60°	893.4	884.6	853.2	828.4	821.7
62.5°	808.1	792.4	770.0	747.6	738.6
65°	720.7	707.2	684.8	664.5	653.3
67.5°	630.9	619.5	599.5	583.8	574.7
70°	547.8	538.8	518.5	502.8	494.0
72.5°	462.5	453.5	442.3	426.6	419.9
75°	377.0	372.8	361.3	348.0	352.5
77.5°	300.8	291.8	287.2	280.6	273.9
80°	224.6	222.2	217.7	211.0	206.5
82.5°	152.7	152.7	150.5	141.5	141.5
85°	91.9	89.8	87.6	80.7	78.6
87.5°	40.5	36.0	31.4	24.8	22.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931373

CATALOG NUMBER: DFN2DS-TR3F0-060DS835-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.99	16.60	15.36	16.92	17.23	14.55	16.16	14.91	16.47	16.79
	3H	16.74	18.20	17.12	18.52	18.88	16.25	17.71	16.63	18.03	18.39
	4H	17.39	18.76	17.79	19.11	19.48	16.89	18.26	17.29	18.61	18.99
	6H	17.86	19.13	18.27	19.49	19.88	17.36	18.63	17.77	18.99	19.38
	8H	18.00	19.21	18.43	19.60	20.00	17.50	18.71	17.92	19.10	19.50
	12H	18.09	19.25	18.52	19.63	20.06	17.58	18.74	18.01	19.12	19.55
4H	2H	15.55	16.92	15.95	17.27	17.65	15.20	16.57	15.60	16.92	17.29
	3H	17.53	18.67	17.94	19.07	19.47	17.12	18.27	17.53	18.67	19.07
	4H	18.30	19.34	18.74	19.75	20.19	17.88	18.92	18.31	19.33	19.77
	6H	18.90	19.81	19.36	20.25	20.70	18.47	19.37	18.92	19.81	20.27
	8H	19.09	19.94	19.55	20.38	20.85	18.65	19.50	19.11	19.94	20.41
	12H	19.22	19.98	19.70	20.46	20.93	18.77	19.53	19.25	20.01	20.48
8H	4H	18.58	19.42	19.04	19.87	20.33	18.20	19.05	18.66	19.49	19.96
	6H	19.29	20.00	19.79	20.48	20.96	18.91	19.61	19.40	20.10	20.58
	8H	19.55	20.18	20.06	20.69	21.18	19.16	19.79	19.67	20.30	20.78
	12H	19.75	20.31	20.26	20.80	21.36	19.34	19.90	19.85	20.39	20.95
12H	4H	18.60	19.36	19.08	19.84	20.31	18.24	19.00	18.72	19.48	19.94
	6H	19.34	19.97	19.85	20.48	20.96	18.97	19.60	19.48	20.11	20.59
	8H	19.65	20.21	20.16	20.70	21.26	19.27	19.83	19.78	20.32	20.88