

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931391

Luminaire Tested: DFN2DS-TR3F0-070DS835-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931391
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-070DS835-FLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6930.0 lumens
Efficiency: N/A
Efficacy: 93.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 74.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931391

CATALOG NUMBER: DFN2DS-TR3F0-070DS835-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931391

CATALOG NUMBER: DFN2DS-TR3F0-070DS835-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3394	3394	3394
5°	3407	3358	3378
10°	3387	3324	3341
15°	3345	3281	3278
20°	3285	3216	3213
25°	3227	3137	3137
30°	3151	3064	3037
35°	3080	2976	2932
40°	2991	2888	2833
45°	2903	2801	2732
50°	2808	2711	2615
55°	2709	2606	2509
60°	2598	2481	2389
65°	2479	2356	2247
70°	2328	2204	2100
75°	2118	2029	1980
80°	1880	1823	1729
85°	1534	1463	1311

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2903 cd/sqm

TEST NUMBER: P931391

CATALOG NUMBER: DFN2DS-TR3F0-070DS835-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	256.4	3.7
10°-20°	721.3	10.4
20°-30°	1060.0	15.3
30°-40°	1231.1	17.8
40°-50°	1229.6	17.7
50°-60°	1072.2	15.5
60°-70°	792.6	11.4
70°-80°	448.4	6.5
80°-90°	118.4	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2037.7	29.4
0°-40°	3268.8	47.2
0°-60°	5570.6	80.4
0°-90°	6930.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6930.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2724	2724	2724	2724	2724	
5°	2724	2714	2685	2705	2700	259
15°	2593	2577	2543	2554	2541	730
25°	2347	2326	2281	2286	2281	1080
35°	2025	1998	1956	1941	1928	1264
45°	1648	1629	1590	1561	1550	1271
55°	1247	1231	1200	1168	1155	1115
65°	841	825	799	775	762	831
75°	440	435	422	406	411	470
85°	107	105	102	94	92	126
90°	0	0	0	0	0	

TEST NUMBER: P931391

CATALOG NUMBER: DFN2DS-TR3F0-070DS835-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2723.7	2723.7	2723.7	2723.7	2723.7
2.5°	2739.6	2726.5	2697.6	2723.7	2718.7
5°	2723.7	2713.5	2684.6	2705.4	2700.4
7.5°	2705.4	2689.8	2660.9	2682.1	2676.8
10°	2676.8	2658.4	2627.0	2647.9	2640.1
12.5°	2637.3	2621.8	2590.4	2603.4	2598.1
15°	2592.9	2577.3	2543.1	2553.7	2540.6
17.5°	2537.8	2522.3	2488.1	2501.2	2488.1
20°	2477.5	2462.0	2425.3	2433.1	2422.8
22.5°	2417.5	2393.9	2359.7	2359.7	2354.4
25°	2346.7	2325.8	2281.4	2286.4	2281.4
27.5°	2268.0	2249.7	2215.8	2208.0	2194.9
30°	2189.7	2168.5	2129.4	2121.6	2111.0
32.5°	2105.7	2090.2	2048.2	2032.4	2021.8
35°	2024.6	1998.5	1956.5	1940.7	1927.6
37.5°	1932.9	1909.3	1867.3	1849.0	1835.9
40°	1838.7	1817.6	1775.6	1752.3	1741.7
42.5°	1747.0	1725.9	1684.2	1657.8	1642.2
45°	1647.5	1629.2	1589.7	1561.1	1550.5
47.5°	1550.5	1532.2	1490.2	1461.3	1445.8
50°	1448.3	1435.2	1398.5	1361.9	1348.8
52.5°	1348.8	1330.5	1296.6	1267.7	1249.3
55°	1246.8	1231.0	1199.6	1168.2	1155.1
57.5°	1144.6	1131.5	1097.3	1065.9	1055.4
60°	1042.3	1032.0	995.4	966.5	958.7
62.5°	942.8	924.5	898.4	872.3	861.7
65°	840.9	825.0	798.9	775.3	762.2
67.5°	736.1	722.8	699.4	681.1	670.5
70°	639.1	628.6	604.9	586.6	576.3
72.5°	539.6	529.1	516.0	497.7	489.9
75°	439.9	434.9	421.5	406.0	411.3
77.5°	351.0	340.4	335.1	327.3	319.6
80°	262.0	259.3	254.0	246.2	240.9
82.5°	178.1	178.1	175.6	165.1	165.1
85°	107.3	104.8	102.3	94.2	91.7
87.5°	47.2	42.0	36.7	28.9	26.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931391

CATALOG NUMBER: DFN2DS-TR3F0-070DS835-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.53	17.14	15.89	17.45	17.77	15.08	16.69	15.45	17.01	17.32
	3H	17.28	18.73	17.66	19.06	19.42	16.79	18.24	17.16	18.57	18.93
	4H	17.92	19.29	18.32	19.64	20.02	17.43	18.80	17.83	19.15	19.52
	6H	18.39	19.66	18.81	20.03	20.42	17.89	19.16	18.30	19.53	19.92
	8H	18.54	19.75	18.96	20.14	20.54	18.03	19.24	18.46	19.63	20.03
	12H	18.63	19.79	19.06	20.17	20.60	18.12	19.28	18.54	19.66	20.09
4H	2H	16.09	17.46	16.49	17.81	18.18	15.74	17.10	16.13	17.45	17.83
	3H	18.06	19.21	18.47	19.61	20.01	17.66	18.80	18.07	19.20	19.60
	4H	18.84	19.88	19.27	20.29	20.73	18.42	19.45	18.85	19.87	20.30
	6H	19.44	20.34	19.89	20.78	21.24	19.00	19.91	19.46	20.35	20.81
	8H	19.63	20.47	20.09	20.92	21.38	19.19	20.03	19.65	20.48	20.94
	12H	19.76	20.52	20.24	20.99	21.46	19.31	20.07	19.79	20.54	21.01
8H	4H	19.11	19.96	19.57	20.40	20.87	18.74	19.59	19.20	20.03	20.49
	6H	19.83	20.53	20.32	21.02	21.49	19.45	20.15	19.94	20.64	21.11
	8H	20.09	20.72	20.60	21.22	21.71	19.70	20.33	20.21	20.83	21.32
	12H	20.29	20.85	20.79	21.34	21.90	19.87	20.43	20.38	20.92	21.48
12H	4H	19.14	19.90	19.62	20.38	20.84	18.78	19.53	19.26	20.01	20.48
	6H	19.87	20.51	20.38	21.01	21.50	19.50	20.14	20.01	20.64	21.13
	8H	20.19	20.75	20.69	21.24	21.80	19.81	20.37	20.32	20.86	21.42