

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931392

Luminaire Tested: DFN2DS-TR3F0-070DS835-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931392
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-070DS835-RLL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5950.0 lumens
Efficiency: N/A
Efficacy: 80.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 74.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931392

CATALOG NUMBER: DFN2DS-TR3F0-070DS835-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931392

CATALOG NUMBER: DFN2DS-TR3F0-070DS835-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3605	3605	3605
5°	3619	3560	3580
10°	3591	3502	3472
15°	3550	3398	3300
20°	3493	3250	3086
25°	3434	3081	2880
30°	3353	2908	2614
35°	3274	2721	2382
40°	3194	2525	2112
45°	3101	2307	1869
50°	3005	2086	1630
55°	2906	1848	1400
60°	2793	1599	1162
65°	2663	1343	1057
70°	2509	1106	972
75°	2319	1008	908
80°	2047	901	827
85°	1608	711	711

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3101 cd/sqm

TEST NUMBER: P931392

CATALOG NUMBER: DFN2DS-TR3F0-070DS835-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	271.1	4.6
10°-20°	744.3	12.5
20°-30°	1045.0	17.6
30°-40°	1139.2	19.1
40°-50°	1047.0	17.6
50°-60°	822.3	13.8
60°-70°	535.2	9.0
70°-80°	275.5	4.6
80°-90°	70.3	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2060.5	34.6
0°-40°	3199.7	53.8
0°-60°	5068.9	85.2
0°-90°	5950.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5950.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2893	2893	2893	2893	2893	
5°	2893	2880	2846	2870	2862	274
15°	2752	2723	2634	2584	2558	775
25°	2498	2414	2241	2134	2094	1149
35°	2152	2019	1788	1623	1566	1347
45°	1760	1584	1309	1123	1060	1359
55°	1338	1134	851	694	644	1195
65°	903	691	456	367	359	896
75°	482	298	209	191	189	509
85°	112	58	50	50	50	135
90°	0	0	0	0	0	

TEST NUMBER: P931392

CATALOG NUMBER: DFN2DS-TR3F0-070DS835-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2893.1	2893.1	2893.1	2893.1	2893.1
2.5°	2906.1	2893.1	2864.2	2890.6	2885.3
5°	2893.1	2880.0	2845.9	2869.5	2861.7
7.5°	2869.5	2853.9	2817.3	2827.5	2814.5
10°	2838.1	2819.8	2767.5	2759.5	2743.9
12.5°	2798.9	2775.3	2704.5	2688.9	2660.0
15°	2751.7	2722.8	2633.9	2584.2	2558.1
17.5°	2696.7	2654.8	2544.8	2487.2	2445.3
20°	2633.9	2581.4	2450.6	2385.3	2327.5
22.5°	2565.9	2505.6	2353.6	2264.7	2225.6
25°	2497.8	2413.9	2241.1	2133.9	2094.5
27.5°	2416.7	2327.5	2136.4	2013.4	1953.1
30°	2330.3	2230.6	2021.1	1887.8	1817.0
32.5°	2246.4	2125.9	1911.4	1754.2	1688.6
35°	2152.2	2018.6	1788.4	1623.4	1565.6
37.5°	2060.6	1916.4	1673.1	1492.2	1427.0
40°	1963.6	1806.7	1552.5	1366.7	1298.6
42.5°	1864.2	1696.7	1432.2	1238.3	1173.1
45°	1759.5	1583.9	1309.2	1123.1	1060.3
47.5°	1660.0	1474.2	1191.4	1005.3	947.8
50°	1550.0	1364.2	1076.1	895.3	840.6
52.5°	1442.5	1246.1	966.1	793.3	743.6
55°	1337.8	1133.6	850.8	693.9	644.2
57.5°	1230.6	1021.1	748.9	602.2	560.3
60°	1120.6	911.1	641.4	508.1	466.1
62.5°	1013.3	803.9	549.7	424.2	403.3
65°	903.3	691.1	455.6	366.7	358.6
67.5°	798.6	586.4	366.7	321.9	314.2
70°	688.6	484.4	303.6	277.5	266.9
72.5°	583.9	390.0	253.9	233.1	227.8
75°	481.7	298.3	209.4	191.1	188.6
77.5°	379.7	211.9	165.0	154.4	149.2
80°	285.3	151.9	125.6	115.3	115.3
82.5°	198.9	102.2	86.4	81.1	81.1
85°	112.5	57.5	49.7	49.7	49.7
87.5°	41.9	20.8	20.8	18.3	18.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931392

CATALOG NUMBER: DFN2DS-TR3F0-070DS835-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.69	17.21	16.05	17.53	17.84	11.65	13.17	12.02	13.49	13.80
	3H	17.46	18.82	17.83	19.15	19.51	12.92	14.28	13.29	14.61	14.97
	4H	18.12	19.40	18.52	19.75	20.13	13.42	14.70	13.82	15.05	15.43
	6H	18.61	19.79	19.02	20.16	20.55	13.80	14.98	14.21	15.35	15.74
	8H	18.78	19.90	19.20	20.29	20.69	13.92	15.05	14.35	15.44	15.84
	12H	18.88	19.96	19.31	20.34	20.77	14.00	15.08	14.43	15.46	15.89
4H	2H	15.79	17.07	16.19	17.42	17.80	12.35	13.63	12.75	13.98	14.35
	3H	17.73	18.79	18.14	19.19	19.59	13.79	14.85	14.20	15.25	15.65
	4H	18.48	19.43	18.91	19.85	20.29	14.39	15.35	14.82	15.76	16.20
	6H	19.07	19.90	19.53	20.34	20.80	14.88	15.71	15.33	16.15	16.61
	8H	19.28	20.06	19.75	20.50	20.97	15.04	15.82	15.50	16.26	16.73
	12H	19.44	20.13	19.92	20.61	21.08	15.16	15.85	15.64	16.33	16.80
8H	4H	18.50	19.28	18.96	19.72	20.19	14.74	15.52	15.21	15.96	16.43
	6H	19.14	19.78	19.63	20.27	20.75	15.33	15.97	15.83	16.46	16.94
	8H	19.39	19.97	19.90	20.47	20.96	15.55	16.13	16.06	16.64	17.12
	12H	19.59	20.10	20.10	20.59	21.16	15.73	16.24	16.24	16.73	17.30
12H	4H	18.49	19.18	18.97	19.66	20.13	14.79	15.48	15.27	15.96	16.43
	6H	19.12	19.70	19.63	20.21	20.69	15.39	15.97	15.91	16.48	16.97
	8H	19.40	19.91	19.91	20.41	20.97	15.67	16.18	16.18	16.67	17.23