

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930673

Luminaire Tested: DFN2DS-PN4F0-060DS840-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930673
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN4F0-060DS840-FLL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5945.9 lumens
Efficiency: N/A
Efficacy: 100.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.94' x L: 3.74' x H: 0')
CIE Type: Direct

Input Watts (W): 59.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930673

CATALOG NUMBER: DFN2DS-PN4F0-060DS840-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930673

CATALOG NUMBER: DFN2DS-PN4F0-060DS840-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1706	1706	1706
5°	1712	1688	1698
10°	1702	1671	1679
15°	1681	1649	1647
20°	1651	1616	1615
25°	1622	1577	1577
30°	1584	1540	1527
35°	1548	1496	1474
40°	1503	1452	1424
45°	1459	1408	1373
50°	1411	1363	1314
55°	1361	1310	1261
60°	1306	1247	1201
65°	1246	1184	1130
70°	1170	1108	1055
75°	1064	1020	995
80°	945	916	869
85°	771	735	659

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1459 cd/sqm

TEST NUMBER: P930673

CATALOG NUMBER: DFN2DS-PN4F0-060DS840-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	220.0	3.7
10°-20°	618.9	10.4
20°-30°	909.5	15.3
30°-40°	1056.3	17.8
40°-50°	1055.0	17.7
50°-60°	919.9	15.5
60°-70°	680.0	11.4
70°-80°	384.8	6.5
80°-90°	101.5	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1748.3	29.4
0°-40°	2804.6	47.2
0°-60°	4779.6	80.4
0°-90°	5945.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5945.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2337	2337	2337	2337	2337	
5°	2337	2328	2303	2321	2317	222
15°	2225	2211	2182	2191	2180	627
25°	2013	1996	1957	1962	1957	926
35°	1737	1715	1679	1665	1654	1085
45°	1414	1398	1364	1339	1330	1091
55°	1070	1056	1029	1002	991	956
65°	721	708	686	665	654	713
75°	377	373	362	348	353	403
85°	92	90	88	81	79	108
90°	0	0	0	0	0	

TEST NUMBER: P930673

CATALOG NUMBER: DFN2DS-PN4F0-060DS840-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2336.9	2336.9	2336.9	2336.9	2336.9
2.5°	2350.5	2339.3	2314.5	2336.9	2332.6
5°	2336.9	2328.1	2303.3	2321.2	2316.9
7.5°	2321.2	2307.9	2283.1	2301.2	2296.7
10°	2296.7	2281.0	2254.0	2271.9	2265.2
12.5°	2262.9	2249.4	2222.5	2233.7	2229.2
15°	2224.6	2211.3	2182.0	2191.1	2179.9
17.5°	2177.5	2164.2	2134.8	2145.9	2134.8
20°	2125.7	2112.4	2080.9	2087.6	2078.8
22.5°	2074.3	2054.0	2024.6	2024.6	2020.1
25°	2013.4	1995.6	1957.4	1961.7	1957.4
27.5°	1945.9	1930.2	1901.1	1894.5	1883.3
30°	1878.8	1860.6	1827.0	1820.3	1811.2
32.5°	1806.7	1793.4	1757.4	1743.7	1734.7
35°	1737.1	1714.7	1678.7	1665.1	1653.9
37.5°	1658.5	1638.1	1602.2	1586.4	1575.2
40°	1577.6	1559.5	1523.5	1503.5	1494.4
42.5°	1498.9	1480.8	1445.0	1422.4	1409.0
45°	1413.6	1397.8	1364.0	1339.4	1330.3
47.5°	1330.3	1314.6	1278.7	1253.9	1240.4
50°	1242.6	1231.4	1200.0	1168.5	1157.3
52.5°	1157.3	1141.5	1112.4	1087.7	1072.0
55°	1069.8	1056.2	1029.2	1002.3	991.1
57.5°	982.1	970.9	941.5	914.6	905.5
60°	894.3	885.5	854.1	829.2	822.5
62.5°	808.9	793.2	770.8	748.3	739.3
65°	721.4	707.9	685.5	665.2	654.0
67.5°	631.5	620.1	600.1	584.4	575.3
70°	548.3	539.3	519.0	503.3	494.5
72.5°	463.0	454.0	442.7	427.0	420.3
75°	377.4	373.2	361.7	348.3	352.9
77.5°	301.1	292.1	287.5	280.9	274.2
80°	224.8	222.4	217.9	211.2	206.7
82.5°	152.9	152.9	150.7	141.6	141.6
85°	92.0	89.9	87.7	80.8	78.7
87.5°	40.5	36.0	31.4	24.8	22.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930673

CATALOG NUMBER: DFN2DS-PN4F0-060DS840-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.14	14.75	13.50	15.06	15.38	12.69	14.30	13.06	14.62	14.93
	3H	14.89	16.34	15.27	16.67	17.03	14.40	15.85	14.77	16.18	16.54
	4H	15.53	16.90	15.93	17.25	17.63	15.04	16.41	15.44	16.76	17.13
	6H	16.00	17.27	16.41	17.64	18.03	15.50	16.77	15.91	17.14	17.53
	8H	16.15	17.36	16.57	17.75	18.15	15.64	16.85	16.07	17.24	17.64
	12H	16.24	17.40	16.67	17.78	18.21	15.73	16.89	16.15	17.27	17.70
4H	2H	13.70	15.07	14.10	15.42	15.79	13.35	14.72	13.74	15.06	15.44
	3H	15.67	16.82	16.08	17.22	17.62	15.27	16.41	15.68	16.81	17.21
	4H	16.45	17.49	16.88	17.90	18.34	16.03	17.06	16.46	17.48	17.91
	6H	17.05	17.95	17.50	18.39	18.85	16.61	17.52	17.07	17.96	18.42
	8H	17.24	18.08	17.70	18.53	18.99	16.80	17.64	17.26	18.09	18.55
	12H	17.37	18.13	17.85	18.60	19.07	16.92	17.68	17.40	18.15	18.62
8H	4H	16.72	17.57	17.18	18.01	18.48	16.35	17.20	16.81	17.64	18.10
	6H	17.44	18.14	17.93	18.63	19.10	17.06	17.76	17.55	18.25	18.72
	8H	17.70	18.33	18.21	18.83	19.32	17.31	17.94	17.82	18.44	18.93
	12H	17.90	18.46	18.40	18.95	19.51	17.48	18.04	17.99	18.53	19.09
12H	4H	16.75	17.51	17.23	17.99	18.45	16.38	17.14	16.87	17.62	18.09
	6H	17.48	18.12	17.99	18.62	19.11	17.11	17.75	17.62	18.25	18.74
	8H	17.80	18.36	18.30	18.85	19.41	17.42	17.98	17.93	18.47	19.03