

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931339

Luminaire Tested: DFN2DS-TR3F0-040DS840-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931339
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-040DS840-FLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3963.9 lumens
Efficiency: N/A
Efficacy: 101.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 39.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931339

CATALOG NUMBER: DFN2DS-TR3F0-040DS840-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931339

CATALOG NUMBER: DFN2DS-TR3F0-040DS840-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1941	1941	1941
5°	1949	1921	1932
10°	1937	1901	1911
15°	1913	1877	1875
20°	1879	1840	1838
25°	1845	1794	1794
30°	1802	1753	1737
35°	1762	1702	1677
40°	1711	1652	1621
45°	1661	1602	1563
50°	1606	1551	1496
55°	1549	1491	1436
60°	1486	1419	1366
65°	1418	1347	1286
70°	1332	1261	1201
75°	1212	1161	1132
80°	1075	1042	989
85°	878	836	751

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1661 cd/sqm

TEST NUMBER: P931339

CATALOG NUMBER: DFN2DS-TR3F0-040DS840-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.6	3.7
10°-20°	412.6	10.4
20°-30°	606.3	15.3
30°-40°	704.2	17.8
40°-50°	703.3	17.7
50°-60°	613.3	15.5
60°-70°	453.4	11.4
70°-80°	256.5	6.5
80°-90°	67.7	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1165.5	29.4
0°-40°	1869.8	47.2
0°-60°	3186.4	80.4
0°-90°	3963.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3963.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1558	1558	1558	1558	1558	
5°	1558	1552	1536	1547	1545	148
15°	1483	1474	1455	1461	1453	418
25°	1342	1330	1305	1308	1305	618
35°	1158	1143	1119	1110	1103	723
45°	942	932	909	893	887	727
55°	713	704	686	668	661	638
65°	481	472	457	443	436	476
75°	252	249	241	232	235	269
85°	61	60	58	54	52	72
90°	0	0	0	0	0	

TEST NUMBER: P931339

CATALOG NUMBER: DFN2DS-TR3F0-040DS840-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1558.0	1558.0	1558.0	1558.0	1558.0
2.5°	1567.1	1559.6	1543.0	1558.0	1555.2
5°	1558.0	1552.1	1535.5	1547.4	1544.6
7.5°	1547.4	1538.5	1522.0	1534.1	1531.1
10°	1531.1	1520.6	1502.7	1514.6	1510.1
12.5°	1508.5	1499.6	1481.7	1489.2	1486.1
15°	1483.1	1474.2	1454.7	1460.7	1453.3
17.5°	1451.7	1442.7	1423.2	1430.6	1423.2
20°	1417.1	1408.2	1387.3	1391.7	1385.9
22.5°	1382.8	1369.3	1349.7	1349.7	1346.7
25°	1342.2	1330.3	1304.9	1307.8	1304.9
27.5°	1297.3	1286.8	1267.5	1263.0	1255.6
30°	1252.5	1240.4	1218.0	1213.5	1207.5
32.5°	1204.5	1195.6	1171.6	1162.6	1156.5
35°	1158.1	1143.1	1119.1	1110.1	1102.6
37.5°	1105.6	1092.1	1068.1	1057.7	1050.1
40°	1051.8	1039.6	1015.6	1002.3	996.3
42.5°	999.3	987.2	963.4	948.2	939.3
45°	942.3	931.9	909.3	893.0	886.9
47.5°	886.9	876.4	852.5	835.9	827.0
50°	828.4	820.9	800.0	779.0	771.5
52.5°	771.5	761.1	741.6	725.1	714.6
55°	713.2	704.1	686.2	668.2	660.8
57.5°	654.7	647.2	627.6	609.7	603.7
60°	596.2	590.3	569.4	552.9	548.3
62.5°	539.3	528.8	513.9	498.9	492.9
65°	481.0	471.9	457.0	443.4	436.0
67.5°	421.0	413.4	400.1	389.6	383.6
70°	365.6	359.6	346.0	335.5	329.6
72.5°	308.7	302.6	295.2	284.7	280.2
75°	251.7	248.7	241.1	232.2	235.2
77.5°	200.7	194.7	191.7	187.2	182.8
80°	149.8	148.2	145.2	140.8	137.8
82.5°	101.9	101.9	100.5	94.4	94.4
85°	61.4	60.0	58.5	53.9	52.5
87.5°	27.0	24.0	21.0	16.5	14.9
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931339

CATALOG NUMBER: DFN2DS-TR3F0-040DS840-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.59	15.20	13.95	15.51	15.83	13.14	14.75	13.51	15.07	15.38
	3H	15.34	16.79	15.71	17.12	17.48	14.85	16.30	15.22	16.63	16.99
	4H	15.98	17.35	16.38	17.70	18.08	15.49	16.86	15.89	17.21	17.58
	6H	16.45	17.72	16.86	18.09	18.48	15.95	17.22	16.36	17.58	17.98
	8H	16.60	17.81	17.02	18.20	18.59	16.09	17.30	16.52	17.69	18.09
	12H	16.69	17.85	17.12	18.23	18.66	16.17	17.33	16.60	17.72	18.14
4H	2H	14.15	15.52	14.55	15.86	16.24	13.80	15.16	14.19	15.51	15.89
	3H	16.12	17.27	16.53	17.67	18.07	15.72	16.86	16.13	17.26	17.66
	4H	16.90	17.94	17.33	18.35	18.79	16.48	17.51	16.91	17.93	18.36
	6H	17.50	18.40	17.95	18.84	19.30	17.06	17.97	17.52	18.41	18.87
	8H	17.69	18.53	18.15	18.97	19.44	17.25	18.09	17.71	18.54	19.00
	12H	17.82	18.58	18.30	19.05	19.52	17.37	18.13	17.85	18.60	19.07
8H	4H	17.17	18.02	17.63	18.46	18.93	16.80	17.65	17.26	18.09	18.55
	6H	17.89	18.59	18.38	19.08	19.55	17.51	18.21	18.00	18.70	19.17
	8H	18.15	18.78	18.66	19.28	19.77	17.75	18.39	18.26	18.89	19.38
	12H	18.35	18.90	18.85	19.39	19.96	17.93	18.49	18.44	18.98	19.54
12H	4H	17.20	17.96	17.68	18.43	18.90	16.83	17.59	17.31	18.07	18.54
	6H	17.93	18.56	18.44	19.07	19.56	17.56	18.20	18.07	18.70	19.19
	8H	18.25	18.80	18.75	19.29	19.86	17.87	18.43	18.38	18.92	19.48