

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931357

Luminaire Tested: DFN2DS-TR3F0-050DS840-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931357
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-050DS840-FLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4955.0 lumens
Efficiency: N/A
Efficacy: 99.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931357

CATALOG NUMBER: DFN2DS-TR3F0-050DS840-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931357

CATALOG NUMBER: DFN2DS-TR3F0-050DS840-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2427	2427	2427
5°	2436	2401	2415
10°	2422	2377	2389
15°	2392	2346	2343
20°	2349	2300	2297
25°	2307	2243	2243
30°	2253	2191	2172
35°	2202	2128	2097
40°	2139	2065	2026
45°	2076	2003	1954
50°	2007	1939	1870
55°	1937	1863	1794
60°	1857	1774	1708
65°	1773	1684	1607
70°	1665	1576	1501
75°	1514	1451	1416
80°	1345	1303	1236
85°	1097	1045	938

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2076 cd/sqm

TEST NUMBER: P931357

CATALOG NUMBER: DFN2DS-TR3F0-050DS840-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.3	3.7
10°-20°	515.7	10.4
20°-30°	757.9	15.3
30°-40°	880.3	17.8
40°-50°	879.2	17.7
50°-60°	766.6	15.5
60°-70°	566.7	11.4
70°-80°	320.6	6.5
80°-90°	84.6	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1456.9	29.4
0°-40°	2337.2	47.2
0°-60°	3983.0	80.4
0°-90°	4955.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4955.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1947	1947	1947	1947	1947	
5°	1947	1940	1919	1934	1931	185
15°	1854	1843	1818	1826	1816	522
25°	1678	1663	1631	1635	1631	772
35°	1448	1429	1399	1388	1378	904
45°	1178	1165	1137	1116	1109	909
55°	892	880	858	835	826	797
65°	601	590	571	554	545	594
75°	314	311	301	290	294	336
85°	77	75	73	67	66	90
90°	0	0	0	0	0	

TEST NUMBER: P931357

CATALOG NUMBER: DFN2DS-TR3F0-050DS840-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1947.4	1947.4	1947.4	1947.4	1947.4
2.5°	1958.8	1949.4	1928.8	1947.4	1943.9
5°	1947.4	1940.1	1919.4	1934.3	1930.8
7.5°	1934.3	1923.2	1902.6	1917.7	1913.9
10°	1913.9	1900.8	1878.4	1893.2	1887.7
12.5°	1885.7	1874.6	1852.2	1861.5	1857.7
15°	1853.9	1842.7	1818.3	1825.9	1816.5
17.5°	1814.5	1803.4	1779.0	1788.3	1779.0
20°	1771.5	1760.4	1734.1	1739.6	1732.3
22.5°	1728.5	1711.6	1687.2	1687.2	1683.4
25°	1677.9	1663.0	1631.1	1634.7	1631.1
27.5°	1621.6	1608.5	1584.3	1578.7	1569.4
30°	1565.6	1550.5	1522.5	1516.9	1509.4
32.5°	1505.6	1494.5	1464.5	1453.2	1445.6
35°	1447.5	1428.9	1398.9	1387.6	1378.3
37.5°	1382.0	1365.2	1335.1	1322.0	1312.7
40°	1314.7	1299.6	1269.6	1252.9	1245.3
42.5°	1249.1	1234.0	1204.2	1185.3	1174.2
45°	1178.0	1164.9	1136.6	1116.2	1108.6
47.5°	1108.6	1095.5	1065.6	1044.8	1033.7
50°	1035.5	1026.2	1000.0	973.8	964.4
52.5°	964.4	951.3	927.0	906.4	893.3
55°	891.5	880.2	857.7	835.2	825.9
57.5°	818.3	809.0	784.6	762.2	754.6
60°	745.2	737.9	711.7	691.0	685.5
62.5°	674.2	661.1	642.3	623.6	616.1
65°	601.2	589.9	571.2	554.4	544.9
67.5°	526.3	516.8	500.1	487.0	479.4
70°	457.0	449.4	432.5	419.4	412.1
72.5°	385.9	378.3	369.0	355.9	350.2
75°	314.5	310.9	301.4	290.3	294.1
77.5°	251.0	243.3	239.6	234.0	228.5
80°	187.4	185.4	181.6	176.1	172.3
82.5°	127.3	127.3	125.5	118.0	118.0
85°	76.7	74.9	73.1	67.4	65.6
87.5°	33.7	30.0	26.2	20.6	18.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931357

CATALOG NUMBER: DFN2DS-TR3F0-050DS840-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.36	15.97	14.73	16.29	16.60	13.92	15.53	14.28	15.84	16.16
	3H	16.11	17.57	16.49	17.89	18.25	15.62	17.08	16.00	17.40	17.76
	4H	16.76	18.13	17.16	18.48	18.85	16.26	17.63	16.66	17.98	18.36
	6H	17.23	18.50	17.64	18.86	19.25	16.73	18.00	17.14	18.36	18.75
	8H	17.37	18.58	17.80	18.97	19.37	16.87	18.08	17.29	18.47	18.87
	12H	17.46	18.62	17.89	19.00	19.43	16.95	18.11	17.38	18.49	18.92
4H	2H	14.92	16.29	15.32	16.64	17.02	14.57	15.94	14.97	16.29	16.66
	3H	16.90	18.04	17.31	18.44	18.84	16.49	17.64	16.90	18.04	18.44
	4H	17.67	18.71	18.11	19.12	19.56	17.25	18.29	17.68	18.70	19.14
	6H	18.27	19.18	18.73	19.62	20.07	17.84	18.74	18.29	19.18	19.64
	8H	18.46	19.31	18.92	19.75	20.22	18.02	18.87	18.48	19.31	19.78
	12H	18.59	19.35	19.07	19.83	20.30	18.14	18.90	18.62	19.38	19.85
8H	4H	17.95	18.79	18.41	19.24	19.70	17.57	18.42	18.03	18.86	19.33
	6H	18.66	19.37	19.16	19.85	20.33	18.28	18.98	18.78	19.47	19.95
	8H	18.92	19.55	19.43	20.06	20.55	18.53	19.16	19.04	19.67	20.15
	12H	19.12	19.68	19.63	20.17	20.73	18.71	19.27	19.22	19.76	20.32
12H	4H	17.97	18.73	18.45	19.21	19.68	17.61	18.37	18.09	18.85	19.31
	6H	18.71	19.34	19.22	19.85	20.33	18.34	18.97	18.85	19.48	19.96
	8H	19.02	19.58	19.53	20.07	20.63	18.64	19.20	19.15	19.69	20.25