

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930639

Luminaire Tested: DFN2DS-PN4F0-040DS850-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930639
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN4F0-040DS850-FLL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4391.7 lumens
Efficiency: N/A
Efficacy: 115.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.94' x L: 3.74' x H: 0')
CIE Type: Direct

Input Watts (W): 38.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930639

CATALOG NUMBER: DFN2DS-PN4F0-040DS850-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930639

CATALOG NUMBER: DFN2DS-PN4F0-040DS850-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1260	1260	1260
5°	1265	1247	1254
10°	1257	1234	1240
15°	1242	1218	1217
20°	1220	1194	1193
25°	1198	1164	1164
30°	1170	1137	1128
35°	1143	1105	1089
40°	1110	1072	1052
45°	1078	1040	1014
50°	1042	1006	971
55°	1006	967	932
60°	964	921	887
65°	920	874	834
70°	864	818	779
75°	786	754	735
80°	698	676	642
85°	570	543	487

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1078 cd/sqm

TEST NUMBER: P930639

CATALOG NUMBER: DFN2DS-PN4F0-040DS850-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.5	3.7
10°-20°	457.1	10.4
20°-30°	671.7	15.3
30°-40°	780.2	17.8
40°-50°	779.2	17.7
50°-60°	679.5	15.5
60°-70°	502.3	11.4
70°-80°	284.2	6.5
80°-90°	75.0	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1291.3	29.4
0°-40°	2071.5	47.2
0°-60°	3530.2	80.4
0°-90°	4391.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4391.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1726	1726	1726	1726	1726	
5°	1726	1720	1701	1714	1711	164
15°	1643	1633	1612	1618	1610	463
25°	1487	1474	1446	1449	1446	684
35°	1283	1266	1240	1230	1222	801
45°	1044	1032	1007	989	983	806
55°	790	780	760	740	732	706
65°	533	523	506	491	483	527
75°	279	276	267	257	261	298
85°	68	66	65	60	58	80
90°	0	0	0	0	0	

TEST NUMBER: P930639

CATALOG NUMBER: DFN2DS-PN4F0-040DS850-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1726.0	1726.0	1726.0	1726.0	1726.0
2.5°	1736.1	1727.8	1709.5	1726.0	1722.9
5°	1726.0	1719.5	1701.2	1714.4	1711.3
7.5°	1714.4	1704.5	1686.2	1699.7	1696.3
10°	1696.3	1684.7	1664.8	1678.0	1673.0
12.5°	1671.3	1661.4	1641.5	1649.9	1646.4
15°	1643.1	1633.2	1611.6	1618.3	1610.0
17.5°	1608.3	1598.4	1576.8	1585.0	1576.8
20°	1570.0	1560.1	1537.0	1541.8	1535.4
22.5°	1532.0	1517.0	1495.4	1495.4	1492.0
25°	1487.1	1473.9	1445.7	1448.9	1445.7
27.5°	1437.3	1425.6	1404.2	1399.2	1391.0
30°	1387.6	1374.3	1349.4	1344.4	1337.8
32.5°	1334.5	1324.6	1298.0	1288.0	1281.2
35°	1283.0	1266.5	1239.9	1229.9	1221.6
37.5°	1224.9	1209.9	1183.3	1171.8	1163.5
40°	1165.2	1151.8	1125.2	1110.4	1103.8
42.5°	1107.1	1093.7	1067.3	1050.6	1040.7
45°	1044.0	1032.5	1007.4	989.3	982.6
47.5°	982.6	970.9	944.4	926.1	916.3
50°	917.8	909.5	886.3	863.0	854.7
52.5°	854.7	843.2	821.7	803.4	791.7
55°	790.2	780.1	760.2	740.3	732.1
57.5°	725.3	717.1	695.3	675.5	668.8
60°	660.5	654.0	630.8	612.5	607.5
62.5°	597.5	585.9	569.4	552.7	546.1
65°	532.9	522.8	506.3	491.3	483.1
67.5°	466.4	458.0	443.3	431.6	425.0
70°	405.0	398.4	383.4	371.7	365.2
72.5°	342.0	335.3	327.0	315.4	310.4
75°	278.8	275.6	267.2	257.3	260.6
77.5°	222.4	215.7	212.4	207.4	202.5
80°	166.0	164.2	160.9	156.0	152.7
82.5°	112.9	112.9	111.3	104.6	104.6
85°	68.0	66.4	64.8	59.7	58.1
87.5°	29.9	26.6	23.3	18.3	16.5
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930639

CATALOG NUMBER: DFN2DS-PN4F0-040DS850-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.09	13.70	12.45	14.01	14.32	11.64	13.25	12.01	13.57	13.88
	3H	13.84	15.29	14.21	15.62	15.98	13.34	14.80	13.72	15.13	15.49
	4H	14.48	15.85	14.88	16.20	16.57	13.99	15.36	14.39	15.70	16.08
	6H	14.95	16.22	15.36	16.58	16.98	14.45	15.72	14.86	16.08	16.47
	8H	15.09	16.30	15.52	16.69	17.09	14.59	15.80	15.02	16.19	16.59
	12H	15.18	16.34	15.61	16.73	17.15	14.67	15.83	15.10	16.21	16.64
4H	2H	12.65	14.02	13.04	14.36	14.74	12.29	13.66	12.69	14.01	14.39
	3H	14.62	15.77	15.03	16.17	16.57	14.21	15.36	14.62	15.76	16.16
	4H	15.40	16.43	15.83	16.85	17.28	14.97	16.01	15.41	16.42	16.86
	6H	15.99	16.90	16.45	17.34	17.80	15.56	16.47	16.02	16.91	17.36
	8H	16.18	17.03	16.64	17.47	17.94	15.75	16.59	16.21	17.03	17.50
	12H	16.32	17.08	16.80	17.55	18.02	15.86	16.62	16.34	17.10	17.57
8H	4H	15.67	16.52	16.13	16.96	17.43	15.30	16.14	15.76	16.59	17.05
	6H	16.38	17.09	16.88	17.58	18.05	16.00	16.71	16.50	17.19	17.67
	8H	16.64	17.27	17.15	17.78	18.27	16.25	16.88	16.76	17.39	17.88
	12H	16.84	17.40	17.35	17.89	18.45	16.43	16.99	16.94	17.48	18.04
12H	4H	15.70	16.46	16.18	16.93	17.40	15.33	16.09	15.81	16.57	17.04
	6H	16.43	17.06	16.94	17.57	18.06	16.06	16.69	16.57	17.20	17.69
	8H	16.74	17.30	17.25	17.79	18.35	16.37	16.92	16.87	17.41	17.98