

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930693

Luminaire Tested: DFN2DS-PN4F0-070DS850-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930693
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN4F0-070DS850-FLL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7685.4 lumens
Efficiency: N/A
Efficacy: 107.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.94' x L: 3.74' x H: 0')
CIE Type: Direct

Input Watts (W): 71.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930693

CATALOG NUMBER: DFN2DS-PN4F0-070DS850-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930693

CATALOG NUMBER: DFN2DS-PN4F0-070DS850-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2205	2205	2205
5°	2213	2182	2194
10°	2200	2159	2170
15°	2173	2131	2129
20°	2134	2089	2087
25°	2096	2038	2038
30°	2047	1990	1973
35°	2001	1934	1905
40°	1943	1876	1841
45°	1886	1820	1775
50°	1824	1761	1699
55°	1760	1693	1630
60°	1688	1612	1552
65°	1611	1530	1460
70°	1513	1432	1364
75°	1376	1318	1286
80°	1222	1184	1123
85°	997	951	852

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1886 cd/sqm

TEST NUMBER: P930693

CATALOG NUMBER: DFN2DS-PN4F0-070DS850-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	284.3	3.7
10°-20°	799.9	10.4
20°-30°	1175.6	15.3
30°-40°	1365.3	17.8
40°-50°	1363.6	17.7
50°-60°	1189.1	15.5
60°-70°	879.0	11.4
70°-80°	497.3	6.5
80°-90°	131.3	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2259.8	29.4
0°-40°	3625.1	47.2
0°-60°	6177.8	80.4
0°-90°	7685.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7685.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3021	3021	3021	3021	3021	
5°	3021	3009	2977	3000	2995	287
15°	2876	2858	2820	2832	2818	810
25°	2602	2579	2530	2536	2530	1198
35°	2245	2216	2170	2152	2138	1402
45°	1827	1807	1763	1731	1720	1410
55°	1383	1365	1330	1296	1281	1236
65°	933	915	886	860	845	922
75°	488	482	467	450	456	521
85°	119	116	114	104	102	140
90°	0	0	0	0	0	

TEST NUMBER: P930693

CATALOG NUMBER: DFN2DS-PN4F0-070DS850-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3020.6	3020.6	3020.6	3020.6	3020.6
2.5°	3038.2	3023.7	2991.6	3020.6	3015.0
5°	3020.6	3009.3	2977.2	3000.3	2994.7
7.5°	3000.3	2983.0	2950.9	2974.4	2968.6
10°	2968.6	2948.2	2913.3	2936.5	2927.9
12.5°	2924.8	2907.6	2872.8	2887.2	2881.3
15°	2875.5	2858.2	2820.3	2832.1	2817.5
17.5°	2814.4	2797.2	2759.3	2773.8	2759.3
20°	2747.5	2730.4	2689.7	2698.3	2686.9
22.5°	2681.0	2654.8	2616.9	2616.9	2611.0
25°	2602.5	2579.3	2530.1	2535.6	2530.1
27.5°	2515.2	2494.9	2457.3	2448.7	2434.1
30°	2428.4	2404.9	2361.5	2352.9	2341.1
32.5°	2335.2	2318.0	2271.5	2253.9	2242.2
35°	2245.3	2216.3	2169.8	2152.2	2137.7
37.5°	2143.6	2117.4	2070.8	2050.5	2036.0
40°	2039.1	2015.7	1969.1	1943.3	1931.5
42.5°	1937.4	1914.0	1867.8	1838.5	1821.2
45°	1827.1	1806.8	1763.0	1731.3	1719.5
47.5°	1719.5	1699.2	1652.6	1620.6	1603.4
50°	1606.2	1591.6	1550.9	1510.3	1495.8
52.5°	1495.8	1475.5	1437.9	1405.9	1385.5
55°	1382.7	1365.2	1330.4	1295.5	1281.0
57.5°	1269.4	1254.8	1216.9	1182.1	1170.4
60°	1155.9	1144.5	1103.9	1071.8	1063.2
62.5°	1045.6	1025.3	996.3	967.4	955.6
65°	932.6	914.9	886.0	859.8	845.3
67.5°	816.3	801.6	775.6	755.3	743.6
70°	708.8	697.1	670.8	650.5	639.1
72.5°	598.4	586.8	572.2	551.9	543.3
75°	487.8	482.3	467.4	450.3	456.1
77.5°	389.3	377.5	371.6	363.0	354.4
80°	290.6	287.6	281.7	273.0	267.2
82.5°	197.5	197.5	194.7	183.1	183.1
85°	119.0	116.2	113.5	104.5	101.7
87.5°	52.3	46.6	40.7	32.1	28.9
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930693

CATALOG NUMBER: DFN2DS-PN4F0-070DS850-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.03	15.64	14.39	15.95	16.27	13.59	15.20	13.95	15.51	15.82
	3H	15.78	17.23	16.16	17.56	17.92	15.29	16.74	15.67	17.07	17.43
	4H	16.43	17.80	16.82	18.14	18.52	15.93	17.30	16.33	17.65	18.02
	6H	16.90	18.16	17.31	18.53	18.92	16.39	17.66	16.80	18.03	18.42
	8H	17.04	18.25	17.46	18.64	19.04	16.54	17.75	16.96	18.14	18.53
	12H	17.13	18.29	17.56	18.67	19.10	16.62	17.78	17.05	18.16	18.59
4H	2H	14.59	15.96	14.99	16.31	16.68	14.24	15.61	14.64	15.95	16.33
	3H	16.57	17.71	16.97	18.11	18.51	16.16	17.30	16.57	17.70	18.10
	4H	17.34	18.38	17.77	18.79	19.23	16.92	17.95	17.35	18.37	18.80
	6H	17.94	18.84	18.39	19.28	19.74	17.51	18.41	17.96	18.85	19.31
	8H	18.13	18.97	18.59	19.42	19.88	17.69	18.54	18.15	18.98	19.44
	12H	18.26	19.02	18.74	19.50	19.97	17.81	18.57	18.29	19.04	19.51
8H	4H	17.62	18.46	18.08	18.90	19.37	17.24	18.09	17.70	18.53	19.00
	6H	18.33	19.03	18.82	19.52	20.00	17.95	18.65	18.44	19.14	19.61
	8H	18.59	19.22	19.10	19.73	20.21	18.20	18.83	18.71	19.33	19.82
	12H	18.79	19.35	19.30	19.84	20.40	18.38	18.93	18.88	19.42	19.99
12H	4H	17.64	18.40	18.12	18.88	19.35	17.28	18.04	17.76	18.51	18.98
	6H	18.37	19.01	18.88	19.51	20.00	18.01	18.64	18.52	19.14	19.63
	8H	18.69	19.25	19.20	19.74	20.30	18.31	18.87	18.82	19.36	19.92

END OF REPORT

FIELD PERFORMANCE MAY DIFFER FROM LABORATORY PERFORMANCE

7 of 7