

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931360

Luminaire Tested: DFN2DS-TR3F0-050DS850-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931360
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-050DS850-RLL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4713.3 lumens
Efficiency: N/A
Efficacy: 95.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931360

CATALOG NUMBER: DFN2DS-TR3F0-050DS850-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931360

CATALOG NUMBER: DFN2DS-TR3F0-050DS850-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2856	2856	2856
5°	2867	2820	2836
10°	2845	2774	2750
15°	2812	2692	2614
20°	2767	2574	2445
25°	2720	2441	2281
30°	2656	2304	2071
35°	2594	2155	1887
40°	2530	2000	1673
45°	2456	1827	1480
50°	2380	1653	1291
55°	2302	1464	1109
60°	2212	1266	920
65°	2110	1064	838
70°	1987	876	771
75°	1837	799	719
80°	1622	714	655
85°	1275	563	563

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2456 cd/sqm

TEST NUMBER: P931360

CATALOG NUMBER: DFN2DS-TR3F0-050DS850-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.8	4.6
10°-20°	589.6	12.5
20°-30°	827.8	17.6
30°-40°	902.4	19.1
40°-50°	829.4	17.6
50°-60°	651.3	13.8
60°-70°	424.0	9.0
70°-80°	218.2	4.6
80°-90°	55.7	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1632.2	34.6
0°-40°	2534.6	53.8
0°-60°	4015.3	85.2
0°-90°	4713.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4713.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2292	2292	2292	2292	2292	
5°	2292	2281	2254	2273	2267	217
15°	2180	2157	2086	2047	2026	614
25°	1979	1912	1775	1690	1659	910
35°	1705	1599	1417	1286	1240	1067
45°	1394	1255	1037	890	840	1076
55°	1060	898	674	550	510	947
65°	716	548	361	290	284	709
75°	382	236	166	151	149	404
85°	89	46	39	39	39	107
90°	0	0	0	0	0	

TEST NUMBER: P931360

CATALOG NUMBER: DFN2DS-TR3F0-050DS850-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2291.7	2291.7	2291.7	2291.7	2291.7
2.5°	2302.1	2291.7	2268.9	2289.8	2285.5
5°	2291.7	2281.4	2254.4	2273.0	2266.9
7.5°	2273.0	2260.7	2231.6	2239.8	2229.4
10°	2248.2	2233.6	2192.3	2185.9	2173.5
12.5°	2217.1	2198.5	2142.4	2130.1	2107.1
15°	2179.7	2156.9	2086.5	2047.1	2026.4
17.5°	2136.2	2103.0	2015.8	1970.2	1937.0
20°	2086.5	2044.9	1941.2	1889.5	1843.7
22.5°	2032.6	1984.8	1864.5	1794.0	1763.0
25°	1978.6	1912.1	1775.3	1690.3	1659.1
27.5°	1914.4	1843.7	1692.3	1594.9	1547.2
30°	1845.9	1767.0	1601.1	1495.4	1439.3
32.5°	1779.5	1684.0	1514.1	1389.6	1337.7
35°	1704.9	1599.1	1416.6	1285.9	1240.2
37.5°	1632.2	1518.1	1325.4	1182.1	1130.4
40°	1555.5	1431.2	1229.8	1082.6	1028.7
42.5°	1476.7	1344.0	1134.5	980.9	929.2
45°	1393.8	1254.7	1037.0	889.6	839.8
47.5°	1314.9	1167.8	943.8	796.4	750.8
50°	1227.9	1080.6	852.5	709.2	665.8
52.5°	1142.7	987.1	765.3	628.5	589.1
55°	1059.8	898.0	673.9	549.6	510.3
57.5°	974.8	808.9	593.2	477.1	443.8
60°	887.6	721.7	508.0	402.5	369.2
62.5°	802.7	636.8	435.5	336.0	319.5
65°	715.5	547.5	360.9	290.4	284.1
67.5°	632.6	464.6	290.4	255.1	248.9
70°	545.5	383.7	240.5	219.8	211.5
72.5°	462.6	309.0	201.2	184.6	180.4
75°	381.6	236.3	165.9	151.4	149.4
77.5°	300.8	167.9	130.8	122.3	118.1
80°	226.0	120.3	99.5	91.3	91.3
82.5°	157.6	81.0	68.4	64.2	64.2
85°	89.2	45.6	39.4	39.4	39.4
87.5°	33.3	16.5	16.5	14.5	14.5
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931360

CATALOG NUMBER: DFN2DS-TR3F0-050DS850-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.88	16.40	15.25	16.72	17.03	10.84	12.36	11.21	12.68	12.99
	3H	16.65	18.01	17.02	18.34	18.70	12.11	13.47	12.48	13.80	14.16
	4H	17.31	18.59	17.71	18.94	19.32	12.61	13.89	13.01	14.24	14.62
	6H	17.80	18.98	18.21	19.35	19.74	12.99	14.17	13.40	14.54	14.93
	8H	17.97	19.09	18.39	19.48	19.88	13.11	14.24	13.54	14.63	15.03
	12H	18.07	19.15	18.50	19.53	19.96	13.19	14.27	13.62	14.65	15.08
4H	2H	14.98	16.27	15.38	16.61	16.99	11.54	12.82	11.94	13.17	13.54
	3H	16.92	17.98	17.33	18.38	18.78	12.98	14.04	13.39	14.44	14.84
	4H	17.67	18.62	18.10	19.04	19.48	13.58	14.54	14.01	14.95	15.39
	6H	18.26	19.09	18.72	19.53	19.99	14.07	14.90	14.52	15.34	15.80
	8H	18.47	19.25	18.94	19.70	20.16	14.23	15.01	14.69	15.45	15.92
	12H	18.63	19.32	19.11	19.80	20.27	14.35	15.04	14.83	15.52	15.99
8H	4H	17.69	18.47	18.15	18.91	19.38	13.93	14.71	14.40	15.15	15.62
	6H	18.33	18.97	18.83	19.46	19.94	14.52	15.16	15.02	15.65	16.13
	8H	18.58	19.16	19.09	19.67	20.15	14.74	15.32	15.25	15.83	16.31
	12H	18.78	19.29	19.29	19.79	20.35	14.92	15.43	15.43	15.92	16.49
12H	4H	17.68	18.37	18.16	18.85	19.32	13.98	14.67	14.46	15.15	15.62
	6H	18.31	18.89	18.82	19.40	19.89	14.58	15.16	15.10	15.67	16.16
	8H	18.59	19.10	19.10	19.60	20.16	14.86	15.37	15.37	15.86	16.42