

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931414

Luminaire Tested: DFN2DS-TR3F0-080DS850-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931414
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-080DS850-RLL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7541.2 lumens
Efficiency: N/A
Efficacy: 88.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 85.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931414

CATALOG NUMBER: DFN2DS-TR3F0-080DS850-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931414

CATALOG NUMBER: DFN2DS-TR3F0-080DS850-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4569	4569	4569
5°	4587	4512	4537
10°	4551	4438	4400
15°	4499	4307	4183
20°	4427	4119	3912
25°	4353	3905	3650
30°	4250	3686	3313
35°	4150	3448	3018
40°	4048	3201	2677
45°	3930	2924	2368
50°	3808	2644	2065
55°	3684	2343	1774
60°	3539	2026	1472
65°	3376	1702	1340
70°	3180	1402	1233
75°	2939	1278	1151
80°	2594	1142	1048
85°	2039	901	901

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3930 cd/sqm

TEST NUMBER: P931414

CATALOG NUMBER: DFN2DS-TR3F0-080DS850-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	343.7	4.6
10°-20°	943.4	12.5
20°-30°	1324.5	17.6
30°-40°	1443.8	19.1
40°-50°	1327.0	17.6
50°-60°	1042.1	13.8
60°-70°	678.3	9.0
70°-80°	349.2	4.6
80°-90°	89.1	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2611.6	34.6
0°-40°	4055.4	53.8
0°-60°	6424.5	85.2
0°-90°	7541.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7541.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3667	3667	3667	3667	3667	
5°	3667	3650	3607	3637	3627	348
15°	3488	3451	3338	3275	3242	983
25°	3166	3060	2840	2705	2655	1456
35°	2728	2558	2267	2058	1984	1707
45°	2230	2008	1659	1423	1344	1722
55°	1696	1437	1078	879	816	1515
65°	1145	876	577	465	454	1135
75°	610	378	266	242	239	646
85°	143	73	63	63	63	171
90°	0	0	0	0	0	

TEST NUMBER: P931414

CATALOG NUMBER: DFN2DS-TR3F0-080DS850-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3666.8	3666.8	3666.8	3666.8	3666.8
2.5°	3683.3	3666.8	3630.2	3663.6	3656.9
5°	3666.8	3650.3	3606.9	3636.9	3627.0
7.5°	3636.9	3617.1	3570.6	3583.7	3567.1
10°	3597.0	3573.9	3507.7	3497.5	3477.7
12.5°	3547.5	3517.5	3427.7	3408.0	3371.4
15°	3487.6	3451.0	3338.3	3275.3	3242.2
17.5°	3417.8	3364.7	3225.3	3152.4	3099.2
20°	3338.3	3271.8	3106.0	3023.2	2949.9
22.5°	3252.0	3175.6	2983.1	2870.4	2820.7
25°	3165.8	3059.5	2840.5	2704.6	2654.6
27.5°	3062.9	2949.9	2707.7	2551.8	2475.4
30°	2953.5	2827.1	2561.7	2392.7	2302.8
32.5°	2847.1	2694.4	2422.6	2223.3	2140.3
35°	2727.8	2558.5	2266.6	2057.5	1984.2
37.5°	2611.6	2428.9	2120.5	1891.3	1808.6
40°	2488.8	2289.9	1967.7	1732.1	1645.9
42.5°	2362.7	2150.5	1815.2	1569.6	1486.7
45°	2230.0	2007.5	1659.3	1423.4	1343.9
47.5°	2104.0	1868.4	1510.0	1274.1	1201.3
50°	1964.5	1729.0	1364.0	1134.7	1065.3
52.5°	1828.3	1579.3	1224.4	1005.5	942.5
55°	1695.6	1436.8	1078.4	879.4	816.4
57.5°	1559.7	1294.2	949.2	763.3	710.1
60°	1420.2	1154.8	812.9	643.9	590.8
62.5°	1284.3	1018.8	696.8	537.6	511.2
65°	1144.9	875.9	577.3	464.8	454.5
67.5°	1012.2	743.3	464.8	408.0	398.2
70°	872.8	614.1	384.8	351.7	338.4
72.5°	740.0	494.3	321.8	295.4	288.7
75°	610.5	378.2	265.5	242.2	239.1
77.5°	481.3	268.6	209.2	195.7	189.1
80°	361.5	192.6	159.1	146.1	146.1
82.5°	252.1	129.5	109.5	102.8	102.8
85°	142.6	72.9	63.0	63.0	63.0
87.5°	53.1	26.4	26.4	23.3	23.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931414

CATALOG NUMBER: DFN2DS-TR3F0-080DS850-RL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.51	18.04	16.88	18.35	18.66	12.47	14.00	12.84	14.31	14.62
	3H	18.28	19.64	18.66	19.97	20.33	13.74	15.10	14.12	15.43	15.79
	4H	18.95	20.23	19.34	20.57	20.95	14.24	15.52	14.64	15.87	16.25
	6H	19.43	20.62	19.85	20.98	21.38	14.62	15.80	15.03	16.17	16.56
	8H	19.60	20.73	20.03	21.12	21.52	14.75	15.87	15.17	16.26	16.66
	12H	19.70	20.78	20.13	21.16	21.59	14.83	15.91	15.26	16.29	16.72
4H	2H	16.62	17.90	17.02	18.25	18.63	13.17	14.45	13.57	14.80	15.18
	3H	18.55	19.61	18.96	20.01	20.41	14.61	15.68	15.02	16.08	16.48
	4H	19.30	20.26	19.73	20.67	21.11	15.21	16.17	15.64	16.58	17.02
	6H	19.89	20.72	20.35	21.17	21.63	15.70	16.53	16.16	16.97	17.43
	8H	20.11	20.88	20.57	21.33	21.80	15.86	16.64	16.33	17.08	17.55
	12H	20.26	20.95	20.74	21.43	21.90	15.98	16.67	16.46	17.15	17.62
8H	4H	19.32	20.10	19.79	20.55	21.01	15.57	16.34	16.03	16.79	17.25
	6H	19.96	20.60	20.46	21.10	21.57	16.15	16.79	16.65	17.29	17.76
	8H	20.21	20.79	20.73	21.30	21.79	16.37	16.95	16.89	17.46	17.95
	12H	20.42	20.93	20.93	21.42	21.98	16.55	17.06	17.06	17.55	18.12
12H	4H	19.31	20.00	19.79	20.48	20.95	15.61	16.30	16.09	16.78	17.25
	6H	19.94	20.52	20.46	21.03	21.52	16.22	16.79	16.73	17.30	17.79
	8H	20.23	20.74	20.74	21.23	21.79	16.49	17.00	17.00	17.49	18.06