

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930678

Luminaire Tested: DFN2DS-PN4F0-060DS927-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930678
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN4F0-060DS927-RLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4039.2 lumens
Efficiency: N/A
Efficacy: 68.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.94' x L: 3.74' x H: 0')
CIE Type: Direct

Input Watts (W): 59.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930678

CATALOG NUMBER: DFN2DS-PN4F0-060DS927-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930678

CATALOG NUMBER: DFN2DS-PN4F0-060DS927-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1434	1434	1434
5°	1439	1416	1424
10°	1428	1393	1381
15°	1412	1351	1312
20°	1389	1292	1227
25°	1366	1225	1145
30°	1333	1157	1040
35°	1302	1082	947
40°	1270	1004	840
45°	1233	918	743
50°	1195	830	648
55°	1156	735	557
60°	1111	636	462
65°	1059	534	421
70°	998	440	387
75°	922	401	361
80°	814	358	329
85°	639	282	282

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1233 cd/sqm

TEST NUMBER: P930678

CATALOG NUMBER: DFN2DS-PN4F0-060DS927-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.1	4.6
10°-20°	505.3	12.5
20°-30°	709.4	17.6
30°-40°	773.3	19.1
40°-50°	710.8	17.6
50°-60°	558.2	13.8
60°-70°	363.3	9.0
70°-80°	187.0	4.6
80°-90°	47.7	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1398.8	34.6
0°-40°	2172.1	53.8
0°-60°	3441.1	85.2
0°-90°	4039.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4039.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1964	1964	1964	1964	1964	
5°	1964	1955	1932	1948	1943	186
15°	1868	1848	1788	1754	1736	526
25°	1696	1639	1521	1449	1422	780
35°	1461	1370	1214	1102	1063	914
45°	1194	1075	889	762	720	922
55°	908	770	578	471	437	812
65°	613	469	309	249	244	608
75°	327	202	142	130	128	346
85°	76	39	34	34	34	92
90°	0	0	0	0	0	

TEST NUMBER: P930678

CATALOG NUMBER: DFN2DS-PN4F0-060DS927-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1964.0	1964.0	1964.0	1964.0	1964.0
2.5°	1972.9	1964.0	1944.4	1962.3	1958.7
5°	1964.0	1955.1	1931.9	1948.0	1942.7
7.5°	1948.0	1937.4	1912.5	1919.5	1910.6
10°	1926.6	1914.2	1878.8	1873.3	1862.7
12.5°	1900.1	1884.0	1835.9	1825.4	1805.8
15°	1868.0	1848.4	1788.0	1754.3	1736.5
17.5°	1830.7	1802.2	1727.5	1688.5	1660.0
20°	1788.0	1752.4	1663.6	1619.2	1580.0
22.5°	1741.8	1700.9	1597.8	1537.4	1510.8
25°	1695.7	1638.7	1521.4	1448.6	1421.9
27.5°	1640.6	1580.0	1450.3	1366.8	1325.9
30°	1581.9	1514.2	1372.1	1281.5	1233.5
32.5°	1525.0	1443.2	1297.6	1190.9	1146.3
35°	1461.1	1370.4	1214.1	1102.0	1062.8
37.5°	1398.8	1300.9	1135.8	1013.0	968.7
40°	1333.0	1226.5	1053.9	927.7	881.6
42.5°	1265.5	1151.8	972.3	840.6	796.4
45°	1194.4	1075.2	888.8	762.4	719.8
47.5°	1126.9	1000.8	808.8	682.5	643.4
50°	1052.3	926.1	730.5	607.8	570.6
52.5°	979.2	845.9	655.9	538.6	504.8
55°	908.2	769.6	577.6	471.1	437.3
57.5°	835.4	693.2	508.4	408.8	380.3
60°	760.7	618.6	435.4	344.9	316.4
62.5°	687.9	545.8	373.2	288.0	273.8
65°	613.2	469.2	309.3	248.9	243.5
67.5°	542.1	398.1	248.9	218.6	213.3
70°	467.4	328.8	206.1	188.4	181.2
72.5°	396.4	264.8	172.3	158.2	154.6
75°	327.0	202.5	142.2	129.7	128.1
77.5°	257.8	143.9	112.0	104.9	101.3
80°	193.6	103.1	85.2	78.2	78.2
82.5°	135.0	69.4	58.6	55.0	55.0
85°	76.3	39.0	33.7	33.7	33.7
87.5°	28.5	14.2	14.2	12.4	12.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930678

CATALOG NUMBER: DFN2DS-PN4F0-060DS927-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.49	14.01	12.85	14.32	14.64	8.45	9.97	8.81	10.28	10.60
	3H	14.25	15.62	14.63	15.94	16.31	9.71	11.08	10.09	11.40	11.77
	4H	14.92	16.20	15.32	16.55	16.93	10.21	11.49	10.61	11.84	12.22
	6H	15.41	16.59	15.82	16.96	17.35	10.59	11.78	11.01	12.14	12.54
	8H	15.57	16.70	16.00	17.09	17.49	10.72	11.85	11.15	12.24	12.64
	12H	15.67	16.75	16.11	17.14	17.56	10.80	11.88	11.23	12.26	12.69
4H	2H	12.59	13.87	12.99	14.22	14.60	9.14	10.42	9.54	10.77	11.15
	3H	14.52	15.59	14.93	15.99	16.39	10.59	11.65	11.00	12.05	12.45
	4H	15.27	16.23	15.71	16.64	17.08	11.18	12.14	11.62	12.56	13.00
	6H	15.86	16.70	16.32	17.14	17.60	11.67	12.50	12.13	12.95	13.41
	8H	16.08	16.86	16.54	17.30	17.77	11.83	12.61	12.30	13.06	13.52
	12H	16.23	16.93	16.71	17.41	17.88	11.95	12.65	12.43	13.12	13.60
8H	4H	15.30	16.07	15.76	16.52	16.99	11.54	12.32	12.00	12.76	13.23
	6H	15.93	16.58	16.43	17.07	17.55	12.13	12.77	12.62	13.26	13.74
	8H	16.18	16.76	16.70	17.27	17.76	12.35	12.92	12.86	13.43	13.92
	12H	16.39	16.90	16.90	17.39	17.96	12.52	13.03	13.03	13.53	14.09
12H	4H	15.28	15.98	15.76	16.45	16.93	11.58	12.28	12.06	12.75	13.23
	6H	15.92	16.49	16.43	17.00	17.49	12.19	12.77	12.70	13.28	13.76
	8H	16.20	16.71	16.71	17.20	17.77	12.46	12.97	12.97	13.46	14.03