

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930786

Luminaire Tested: DFN2DS-PN4F0-120DS927-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930786
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN4F0-120DS927-RLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8078.4 lumens
Efficiency: N/A
Efficacy: 61.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.94' x L: 3.74' x H: 0')
CIE Type: Direct

Input Watts (W): 131
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930786

CATALOG NUMBER: DFN2DS-PN4F0-120DS927-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930786

CATALOG NUMBER: DFN2DS-PN4F0-120DS927-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2867	2867	2867
5°	2878	2831	2847
10°	2856	2785	2761
15°	2823	2702	2625
20°	2778	2585	2455
25°	2731	2451	2290
30°	2667	2313	2079
35°	2604	2164	1894
40°	2540	2009	1680
45°	2466	1835	1486
50°	2390	1659	1296
55°	2312	1470	1113
60°	2221	1271	924
65°	2118	1068	841
70°	1996	880	773
75°	1845	802	722
80°	1628	716	658
85°	1280	565	565

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2466 cd/sqm

TEST NUMBER: P930786

CATALOG NUMBER: DFN2DS-PN4F0-120DS927-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	368.1	4.6
10°-20°	1010.6	12.5
20°-30°	1418.9	17.6
30°-40°	1546.6	19.1
40°-50°	1421.5	17.6
50°-60°	1116.4	13.8
60°-70°	726.7	9.0
70°-80°	374.1	4.6
80°-90°	95.5	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2797.6	34.6
0°-40°	4344.2	53.8
0°-60°	6882.2	85.2
0°-90°	8078.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8078.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3928	3928	3928	3928	3928	
5°	3928	3910	3864	3896	3885	372
15°	3736	3697	3576	3509	3473	1053
25°	3391	3277	3043	2897	2844	1560
35°	2922	2741	2428	2204	2126	1829
45°	2389	2150	1778	1525	1440	1845
55°	1816	1539	1155	942	875	1623
65°	1226	938	619	498	487	1216
75°	654	405	284	260	256	692
85°	153	78	68	68	68	183
90°	0	0	0	0	0	

TEST NUMBER: P930786

CATALOG NUMBER: DFN2DS-PN4F0-120DS927-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3928.0	3928.0	3928.0	3928.0	3928.0
2.5°	3945.7	3928.0	3888.8	3924.6	3917.4
5°	3928.0	3910.3	3863.9	3895.9	3885.4
7.5°	3895.9	3874.8	3825.0	3839.0	3821.2
10°	3853.3	3828.4	3757.5	3746.6	3725.5
12.5°	3800.1	3768.1	3671.9	3650.8	3611.6
15°	3736.0	3696.8	3576.1	3508.6	3473.2
17.5°	3661.3	3604.4	3455.0	3377.0	3320.1
20°	3576.1	3504.8	3327.2	3238.6	3160.1
22.5°	3483.7	3401.9	3195.6	3074.9	3021.7
25°	3391.3	3277.4	3042.8	2897.2	2843.7
27.5°	3281.2	3160.1	2900.6	2733.6	2651.7
30°	3163.9	3028.5	2744.1	2563.1	2466.9
32.5°	3050.0	2886.3	2595.1	2381.7	2292.7
35°	2922.2	2740.7	2428.0	2204.1	2125.6
37.5°	2797.7	2602.0	2271.5	2026.0	1937.4
40°	2666.0	2453.0	2107.9	1855.6	1763.2
42.5°	2531.0	2303.6	1944.6	1681.3	1592.7
45°	2388.8	2150.5	1777.5	1524.8	1439.5
47.5°	2253.8	2001.5	1617.6	1364.9	1286.8
50°	2104.5	1852.2	1461.1	1215.6	1141.3
52.5°	1958.5	1691.9	1311.7	1077.1	1009.6
55°	1816.4	1539.2	1155.2	942.1	874.6
57.5°	1670.7	1386.4	1016.8	817.7	760.7
60°	1521.4	1237.0	870.8	689.8	632.9
62.5°	1375.9	1091.5	746.4	575.9	547.6
65°	1226.5	938.4	618.6	497.9	486.9
67.5°	1084.3	796.1	497.9	437.1	426.6
70°	935.0	657.8	412.2	376.8	362.4
72.5°	792.8	529.5	344.7	316.4	309.3
75°	654.0	405.0	284.4	259.5	256.1
77.5°	515.6	287.7	224.1	209.7	202.5
80°	387.4	206.3	170.4	156.5	156.5
82.5°	270.1	138.8	117.3	110.1	110.1
85°	152.8	78.1	67.5	67.5	67.5
87.5°	56.9	28.3	28.3	24.9	24.9
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930786

CATALOG NUMBER: DFN2DS-PN4F0-120DS927-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.89	16.42	15.26	16.73	17.04	10.86	12.38	11.22	12.69	13.01
	3H	16.66	18.03	17.04	18.35	18.71	12.12	13.49	12.50	13.81	14.18
	4H	17.33	18.61	17.73	18.96	19.33	12.62	13.90	13.02	14.25	14.63
	6H	17.82	19.00	18.23	19.36	19.76	13.00	14.19	13.42	14.55	14.94
	8H	17.98	19.11	18.41	19.50	19.90	13.13	14.25	13.55	14.64	15.04
	12H	18.08	19.16	18.51	19.54	19.97	13.21	14.29	13.64	14.67	15.10
4H	2H	15.00	16.28	15.40	16.63	17.01	11.55	12.83	11.95	13.18	13.56
	3H	16.93	17.99	17.34	18.39	18.80	12.99	14.06	13.40	14.46	14.86
	4H	17.68	18.64	18.11	19.05	19.49	13.59	14.55	14.03	14.97	15.40
	6H	18.27	19.10	18.73	19.55	20.01	14.08	14.91	14.54	15.36	15.82
	8H	18.49	19.26	18.95	19.71	20.18	14.24	15.02	14.71	15.46	15.93
	12H	18.64	19.34	19.12	19.81	20.29	14.36	15.05	14.84	15.53	16.00
8H	4H	17.71	18.48	18.17	18.93	19.39	13.95	14.72	14.41	15.17	15.64
	6H	18.34	18.99	18.84	19.48	19.95	14.53	15.18	15.03	15.67	16.14
	8H	18.59	19.17	19.11	19.68	20.17	14.75	15.33	15.27	15.84	16.33
	12H	18.80	19.31	19.31	19.80	20.36	14.93	15.44	15.44	15.94	16.50
12H	4H	17.69	18.38	18.17	18.86	19.33	13.99	14.69	14.47	15.16	15.63
	6H	18.32	18.90	18.84	19.41	19.90	14.60	15.17	15.11	15.68	16.17
	8H	18.61	19.12	19.12	19.61	20.17	14.87	15.38	15.38	15.87	16.44