

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931326

Luminaire Tested: DFN2DS-TR3F0-030DS927-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931326
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-030DS927-RLL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2019.6 lumens
Efficiency: N/A
Efficacy: 71.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 28.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931326

CATALOG NUMBER: DFN2DS-TR3F0-030DS927-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931326

CATALOG NUMBER: DFN2DS-TR3F0-030DS927-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1224	1224	1224
5°	1228	1208	1215
10°	1219	1189	1179
15°	1205	1153	1120
20°	1186	1103	1048
25°	1166	1046	977
30°	1138	987	887
35°	1111	923	808
40°	1084	857	717
45°	1052	783	634
50°	1020	708	553
55°	987	627	475
60°	948	543	394
65°	904	456	359
70°	851	375	330
75°	787	342	308
80°	695	306	281
85°	546	242	242

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1052 cd/sqm

TEST NUMBER: P931326

CATALOG NUMBER: DFN2DS-TR3F0-030DS927-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.0	4.6
10°-20°	252.7	12.5
20°-30°	354.7	17.6
30°-40°	386.7	19.1
40°-50°	355.4	17.6
50°-60°	279.1	13.8
60°-70°	181.6	9.0
70°-80°	93.5	4.6
80°-90°	23.9	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	699.4	34.6
0°-40°	1086.1	53.8
0°-60°	1720.5	85.2
0°-90°	2019.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2019.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	982	982	982	982	982	
5°	982	978	966	974	971	93
15°	934	924	894	877	868	263
25°	848	819	761	724	711	390
35°	730	685	607	551	531	457
45°	597	538	444	381	360	461
55°	454	385	289	236	219	406
65°	307	235	155	124	122	304
75°	164	101	71	65	64	173
85°	38	20	17	17	17	46
90°	0	0	0	0	0	

TEST NUMBER: P931326

CATALOG NUMBER: DFN2DS-TR3F0-030DS927-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	982.0	982.0	982.0	982.0	982.0
2.5°	986.4	982.0	972.2	981.1	979.4
5°	982.0	977.6	966.0	974.0	971.3
7.5°	974.0	968.7	956.3	959.7	955.3
10°	963.3	957.1	939.4	936.6	931.4
12.5°	950.0	942.0	918.0	912.7	902.9
15°	934.0	924.2	894.0	877.1	868.3
17.5°	915.3	901.1	863.8	844.3	830.0
20°	894.0	876.2	831.8	809.7	790.0
22.5°	871.0	850.4	798.9	768.7	755.4
25°	847.8	819.3	760.7	724.3	710.9
27.5°	820.3	790.0	725.2	683.4	662.9
30°	791.0	757.2	686.0	640.8	616.7
32.5°	762.5	721.6	648.8	595.4	573.2
35°	730.5	685.2	607.0	551.0	531.4
37.5°	699.4	650.5	567.9	506.5	484.4
40°	666.5	613.2	527.0	463.9	440.8
42.5°	632.7	575.9	486.1	420.3	398.1
45°	597.2	537.6	444.4	381.2	359.9
47.5°	563.4	500.4	404.4	341.2	321.7
50°	526.1	463.0	365.3	303.9	285.3
52.5°	489.6	423.0	328.0	269.3	252.4
55°	454.1	384.8	288.8	235.5	218.7
57.5°	417.7	346.6	254.2	204.4	190.2
60°	380.3	309.3	217.7	172.4	158.2
62.5°	344.0	272.8	186.6	144.0	136.9
65°	306.6	234.6	154.6	124.4	121.7
67.5°	271.1	199.0	124.4	109.3	106.6
70°	233.7	164.4	103.0	94.2	90.6
72.5°	198.2	132.3	86.2	79.1	77.3
75°	163.5	101.3	71.1	64.9	64.0
77.5°	128.9	71.9	56.0	52.4	50.6
80°	96.9	51.6	42.6	39.1	39.1
82.5°	67.5	34.7	29.3	27.6	27.6
85°	38.2	19.5	16.9	16.9	16.9
87.5°	14.3	7.0	7.0	6.3	6.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931326

CATALOG NUMBER: DFN2DS-TR3F0-030DS927-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.94	13.46	12.30	13.77	14.09	7.90	9.42	8.26	9.73	10.05
	3H	13.70	15.07	14.08	15.39	15.76	9.16	10.53	9.54	10.85	11.22
	4H	14.37	15.65	14.77	16.00	16.38	9.66	10.94	10.06	11.29	11.67
	6H	14.86	16.04	15.27	16.41	16.80	10.04	11.23	10.46	11.59	11.98
	8H	15.02	16.15	15.45	16.54	16.94	10.17	11.30	10.60	11.68	12.09
	12H	15.13	16.20	15.56	16.59	17.01	10.25	11.33	10.68	11.71	12.14
4H	2H	12.04	13.32	12.44	13.67	14.05	8.59	9.87	8.99	10.22	10.60
	3H	13.97	15.04	14.38	15.44	15.84	10.03	11.10	10.45	11.50	11.90
	4H	14.72	15.68	15.16	16.09	16.53	10.63	11.59	11.07	12.01	12.45
	6H	15.31	16.15	15.77	16.59	17.05	11.12	11.95	11.58	12.40	12.86
	8H	15.53	16.31	15.99	16.75	17.22	11.28	12.06	11.75	12.51	12.97
	12H	15.68	16.38	16.16	16.86	17.33	11.40	12.10	11.88	12.58	13.05
8H	4H	14.75	15.52	15.21	15.97	16.44	10.99	11.77	11.45	12.21	12.68
	6H	15.38	16.03	15.88	16.52	17.00	11.57	12.22	12.07	12.71	13.19
	8H	15.63	16.21	16.15	16.72	17.21	11.80	12.37	12.31	12.88	13.37
	12H	15.84	16.35	16.35	16.84	17.41	11.98	12.49	12.49	12.98	13.54
12H	4H	14.73	15.43	15.21	15.90	16.38	11.03	11.73	11.51	12.20	12.68
	6H	15.37	15.94	15.88	16.45	16.94	11.64	12.22	12.15	12.72	13.21
	8H	15.65	16.16	16.16	16.65	17.22	11.91	12.42	12.42	12.91	13.48