

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930661

Luminaire Tested: DFN2DS-PN4F0-050DS930-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930661
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN4F0-050DS930-FLL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4034.2 lumens
Efficiency: N/A
Efficacy: 82.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.94' x L: 3.74' x H: 0')
CIE Type: Direct

Input Watts (W): 48.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930661

CATALOG NUMBER: DFN2DS-PN4F0-050DS930-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930661

CATALOG NUMBER: DFN2DS-PN4F0-050DS930-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1157	1157	1157
5°	1162	1145	1152
10°	1155	1134	1139
15°	1141	1119	1118
20°	1120	1097	1096
25°	1100	1070	1070
30°	1074	1045	1036
35°	1050	1015	1000
40°	1020	985	966
45°	990	955	932
50°	957	925	892
55°	924	889	856
60°	886	846	815
65°	845	803	766
70°	794	752	716
75°	722	692	675
80°	641	621	590
85°	523	498	447

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 990 cd/sqm

TEST NUMBER: P930661

CATALOG NUMBER: DFN2DS-PN4F0-050DS930-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.2	3.7
10°-20°	419.9	10.4
20°-30°	617.1	15.3
30°-40°	716.7	17.8
40°-50°	715.8	17.7
50°-60°	624.2	15.5
60°-70°	461.4	11.4
70°-80°	261.0	6.5
80°-90°	68.9	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1186.2	29.4
0°-40°	1902.9	47.2
0°-60°	3242.9	80.4
0°-90°	4034.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4034.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1586	1586	1586	1586	1586	
5°	1586	1580	1563	1575	1572	151
15°	1509	1500	1480	1487	1479	425
25°	1366	1354	1328	1331	1328	629
35°	1179	1163	1139	1130	1122	736
45°	959	948	925	909	903	740
55°	726	717	698	680	672	649
65°	490	480	465	451	444	484
75°	256	253	245	236	239	273
85°	62	61	60	55	53	73
90°	0	0	0	0	0	

TEST NUMBER: P930661

CATALOG NUMBER: DFN2DS-PN4F0-050DS930-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1585.6	1585.6	1585.6	1585.6	1585.6
2.5°	1594.8	1587.2	1570.4	1585.6	1582.7
5°	1585.6	1579.6	1562.8	1574.9	1572.1
7.5°	1574.9	1565.9	1549.1	1561.4	1558.3
10°	1558.3	1547.6	1529.3	1541.4	1536.9
12.5°	1535.3	1526.3	1508.0	1515.6	1512.5
15°	1509.4	1500.3	1480.4	1486.6	1479.0
17.5°	1477.4	1468.3	1448.4	1456.0	1448.4
20°	1442.3	1433.3	1411.9	1416.4	1410.4
22.5°	1407.3	1393.6	1373.7	1373.7	1370.6
25°	1366.1	1354.0	1328.0	1331.0	1328.0
27.5°	1320.3	1309.6	1289.9	1285.3	1277.8
30°	1274.7	1262.4	1239.6	1235.1	1228.9
32.5°	1225.8	1216.8	1192.3	1183.1	1177.0
35°	1178.6	1163.4	1139.0	1129.8	1122.2
37.5°	1125.2	1111.5	1087.0	1076.4	1068.8
40°	1070.4	1058.1	1033.7	1020.1	1013.9
42.5°	1017.0	1004.7	980.4	965.0	956.0
45°	959.1	948.4	925.4	908.8	902.6
47.5°	902.6	891.9	867.6	850.7	841.7
50°	843.1	835.5	814.2	792.8	785.2
52.5°	785.2	774.5	754.8	738.0	727.3
55°	725.8	716.6	698.3	680.0	672.5
57.5°	666.3	658.7	638.8	620.5	614.3
60°	606.8	600.8	579.5	562.6	558.1
62.5°	548.9	538.2	523.0	507.7	501.6
65°	489.5	480.3	465.0	451.3	443.7
67.5°	428.5	420.8	407.2	396.5	390.3
70°	372.0	365.9	352.2	341.5	335.5
72.5°	314.2	308.0	300.4	289.7	285.2
75°	256.1	253.1	245.4	236.4	239.4
77.5°	204.3	198.1	195.1	190.5	186.1
80°	152.6	150.9	147.8	143.4	140.3
82.5°	103.7	103.7	102.2	96.1	96.1
85°	62.4	61.0	59.5	54.8	53.4
87.5°	27.5	24.4	21.4	16.8	15.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930661

CATALOG NUMBER: DFN2DS-PN4F0-050DS930-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.79	13.40	12.16	13.72	14.03	11.35	12.96	11.71	13.27	13.58
	3H	13.54	15.00	13.92	15.32	15.68	13.05	14.50	13.43	14.83	15.19
	4H	14.19	15.56	14.59	15.90	16.28	13.69	15.06	14.09	15.41	15.78
	6H	14.66	15.92	15.07	16.29	16.68	14.15	15.42	14.57	15.79	16.18
	8H	14.80	16.01	15.22	16.40	16.80	14.30	15.51	14.72	15.90	16.30
	12H	14.89	16.05	15.32	16.43	16.86	14.38	15.54	14.81	15.92	16.35
4H	2H	12.35	13.72	12.75	14.07	14.44	12.00	13.37	12.40	13.71	14.09
	3H	14.33	15.47	14.74	15.87	16.27	13.92	15.07	14.33	15.46	15.86
	4H	15.10	16.14	15.53	16.55	16.99	14.68	15.71	15.11	16.13	16.56
	6H	15.70	16.60	16.15	17.04	17.50	15.27	16.17	15.72	16.61	17.07
	8H	15.89	16.73	16.35	17.18	17.64	15.45	16.30	15.91	16.74	17.21
	12H	16.02	16.78	16.50	17.26	17.73	15.57	16.33	16.05	16.80	17.27
8H	4H	15.38	16.22	15.84	16.66	17.13	15.00	15.85	15.46	16.29	16.76
	6H	16.09	16.79	16.58	17.28	17.76	15.71	16.41	16.20	16.90	17.38
	8H	16.35	16.98	16.86	17.49	17.97	15.96	16.59	16.47	17.10	17.58
	12H	16.55	17.11	17.06	17.60	18.16	16.14	16.69	16.64	17.18	17.75
12H	4H	15.40	16.16	15.88	16.64	17.11	15.04	15.80	15.52	16.27	16.74
	6H	16.14	16.77	16.64	17.27	17.76	15.77	16.40	16.28	16.91	17.39
	8H	16.45	17.01	16.96	17.50	18.06	16.07	16.63	16.58	17.12	17.68

END OF REPORT

FIELD PERFORMANCE MAY DIFFER FROM LABORATORY PERFORMANCE

7 of 7