

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930679

Luminaire Tested: DFN2DS-PN4F0-060DS930-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930679
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN4F0-060DS930-FLL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4841.1 lumens
Efficiency: N/A
Efficacy: 81.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.94' x L: 3.74' x H: 0')
CIE Type: Direct

Input Watts (W): 59.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930679

CATALOG NUMBER: DFN2DS-PN4F0-060DS930-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930679

CATALOG NUMBER: DFN2DS-PN4F0-060DS930-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1389	1389	1389
5°	1394	1374	1382
10°	1386	1360	1367
15°	1369	1343	1341
20°	1344	1316	1315
25°	1320	1284	1284
30°	1289	1254	1243
35°	1260	1218	1200
40°	1224	1182	1159
45°	1188	1146	1118
50°	1149	1109	1070
55°	1108	1066	1027
60°	1063	1015	978
65°	1015	964	920
70°	953	902	859
75°	867	831	810
80°	769	746	707
85°	627	598	537

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1188 cd/sqm

TEST NUMBER: P930679

CATALOG NUMBER: DFN2DS-PN4F0-060DS930-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.1	3.7
10°-20°	503.9	10.4
20°-30°	740.5	15.3
30°-40°	860.0	17.8
40°-50°	859.0	17.7
50°-60°	749.0	15.5
60°-70°	553.7	11.4
70°-80°	313.3	6.5
80°-90°	82.7	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1423.5	29.4
0°-40°	2283.5	47.2
0°-60°	3891.5	80.4
0°-90°	4841.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4841.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1903	1903	1903	1903	1903	
5°	1903	1896	1875	1890	1886	181
15°	1811	1800	1776	1784	1775	510
25°	1639	1625	1594	1597	1594	754
35°	1414	1396	1367	1356	1346	883
45°	1151	1138	1110	1091	1083	888
55°	871	860	838	816	807	779
65°	587	576	558	542	532	581
75°	307	304	294	284	287	328
85°	75	73	71	66	64	88
90°	0	0	0	0	0	

TEST NUMBER: P930679

CATALOG NUMBER: DFN2DS-PN4F0-060DS930-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1902.7	1902.7	1902.7	1902.7	1902.7
2.5°	1913.8	1904.7	1884.4	1902.7	1899.2
5°	1902.7	1895.5	1875.3	1889.9	1886.4
7.5°	1889.9	1879.1	1858.9	1873.6	1869.9
10°	1869.9	1857.1	1835.1	1849.7	1844.3
12.5°	1842.4	1831.5	1809.5	1818.7	1815.0
15°	1811.3	1800.4	1776.5	1784.0	1774.8
17.5°	1772.9	1762.0	1738.2	1747.2	1738.2
20°	1730.7	1719.9	1694.2	1699.7	1692.5
22.5°	1688.8	1672.3	1648.4	1648.4	1644.8
25°	1639.3	1624.8	1593.7	1597.2	1593.7
27.5°	1584.4	1571.6	1547.8	1542.5	1533.3
30°	1529.7	1514.8	1487.5	1482.1	1474.7
32.5°	1471.0	1460.2	1430.8	1419.7	1412.4
35°	1414.4	1396.1	1366.8	1355.7	1346.5
37.5°	1350.3	1333.7	1304.5	1291.6	1282.5
40°	1284.4	1269.7	1240.4	1224.1	1216.7
42.5°	1220.4	1205.6	1176.5	1158.1	1147.2
45°	1150.9	1138.1	1110.5	1090.6	1083.1
47.5°	1083.1	1070.3	1041.1	1020.9	1009.9
50°	1011.7	1002.6	977.0	951.3	942.2
52.5°	942.2	929.4	905.7	885.6	872.8
55°	871.0	859.9	838.0	816.1	806.9
57.5°	799.6	790.5	766.6	744.7	737.2
60°	728.1	720.9	695.4	675.1	669.7
62.5°	658.6	645.8	627.6	609.3	602.0
65°	587.4	576.4	558.1	541.6	532.4
67.5°	514.2	504.9	488.6	475.8	468.4
70°	446.5	439.1	422.6	409.8	402.6
72.5°	376.9	369.6	360.5	347.7	342.2
75°	307.3	303.8	294.5	283.6	287.3
77.5°	245.2	237.8	234.1	228.7	223.2
80°	183.0	181.1	177.4	172.0	168.3
82.5°	124.5	124.5	122.7	115.3	115.3
85°	74.9	73.2	71.4	65.8	64.1
87.5°	33.0	29.3	25.6	20.2	18.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930679

CATALOG NUMBER: DFN2DS-PN4F0-060DS930-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.42	14.04	12.79	14.35	14.66	11.98	13.59	12.34	13.90	14.22
	3H	14.17	15.63	14.55	15.96	16.32	13.68	15.14	14.06	15.46	15.82
	4H	14.82	16.19	15.22	16.54	16.91	14.33	15.69	14.72	16.04	16.42
	6H	15.29	16.56	15.70	16.92	17.31	14.79	16.06	15.20	16.42	16.81
	8H	15.43	16.64	15.86	17.03	17.43	14.93	16.14	15.35	16.53	16.93
	12H	15.52	16.68	15.95	17.06	17.49	15.01	16.17	15.44	16.55	16.98
4H	2H	12.98	14.35	13.38	14.70	15.08	12.63	14.00	13.03	14.35	14.72
	3H	14.96	16.11	15.37	16.50	16.90	14.55	15.70	14.96	16.10	16.50
	4H	15.74	16.77	16.17	17.19	17.62	15.31	16.35	15.74	16.76	17.20
	6H	16.33	17.24	16.79	17.68	18.13	15.90	16.81	16.35	17.25	17.70
	8H	16.52	17.37	16.98	17.81	18.28	16.08	16.93	16.54	17.37	17.84
	12H	16.65	17.41	17.13	17.89	18.36	16.20	16.96	16.68	17.44	17.91
8H	4H	16.01	16.86	16.47	17.30	17.76	15.64	16.48	16.10	16.92	17.39
	6H	16.72	17.43	17.22	17.92	18.39	16.34	17.05	16.84	17.53	18.01
	8H	16.98	17.61	17.49	18.12	18.61	16.59	17.22	17.10	17.73	18.21
	12H	17.18	17.74	17.69	18.23	18.79	16.77	17.33	17.28	17.82	18.38
12H	4H	16.04	16.80	16.52	17.27	17.74	15.67	16.43	16.15	16.91	17.38
	6H	16.77	17.40	17.28	17.91	18.39	16.40	17.03	16.91	17.54	18.03
	8H	17.08	17.64	17.59	18.13	18.69	16.71	17.26	17.21	17.75	18.31