

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931415

Luminaire Tested: DFN2DS-TR3F0-080DS927-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931415
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-080DS927-FLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6272.6 lumens
Efficiency: N/A
Efficacy: 73.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 85.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931415

CATALOG NUMBER: DFN2DS-TR3F0-080DS927-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931415

CATALOG NUMBER: DFN2DS-TR3F0-080DS927-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3072	3072	3072
5°	3084	3039	3057
10°	3066	3009	3024
15°	3028	2970	2967
20°	2974	2911	2908
25°	2920	2839	2839
30°	2852	2773	2749
35°	2788	2694	2654
40°	2707	2614	2564
45°	2628	2536	2473
50°	2541	2454	2367
55°	2452	2359	2271
60°	2351	2245	2162
65°	2244	2132	2034
70°	2108	1995	1900
75°	1917	1837	1792
80°	1702	1650	1564
85°	1388	1324	1187

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2628 cd/sqm

TEST NUMBER: P931415

CATALOG NUMBER: DFN2DS-TR3F0-080DS927-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	232.0	3.7
10°-20°	652.9	10.4
20°-30°	959.5	15.3
30°-40°	1114.4	17.8
40°-50°	1113.0	17.7
50°-60°	970.5	15.5
60°-70°	717.4	11.4
70°-80°	405.9	6.5
80°-90°	107.1	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1844.4	29.4
0°-40°	2958.8	47.2
0°-60°	5042.2	80.4
0°-90°	6272.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6272.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2465	2465	2465	2465	2465	
5°	2465	2456	2430	2449	2444	234
15°	2347	2333	2302	2312	2300	661
25°	2124	2105	2065	2070	2065	977
35°	1832	1809	1771	1757	1745	1144
45°	1491	1475	1439	1413	1404	1151
55°	1128	1114	1086	1057	1046	1009
65°	761	747	723	702	690	752
75°	398	394	382	368	372	425
85°	97	95	93	85	83	114
90°	0	0	0	0	0	

TEST NUMBER: P931415

CATALOG NUMBER: DFN2DS-TR3F0-080DS927-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2465.3	2465.3	2465.3	2465.3	2465.3
2.5°	2479.7	2467.9	2441.7	2465.3	2460.8
5°	2465.3	2456.1	2429.9	2448.8	2444.3
7.5°	2448.8	2434.7	2408.6	2427.6	2422.9
10°	2422.9	2406.3	2377.8	2396.7	2389.7
12.5°	2387.2	2373.1	2344.6	2356.4	2351.7
15°	2346.9	2332.8	2301.9	2311.5	2299.7
17.5°	2297.1	2283.0	2252.1	2263.9	2252.1
20°	2242.5	2228.5	2195.3	2202.3	2193.0
22.5°	2188.2	2166.8	2135.9	2135.9	2131.1
25°	2124.1	2105.2	2065.0	2069.5	2065.0
27.5°	2052.9	2036.3	2005.6	1998.5	1986.7
30°	1982.0	1962.8	1927.4	1920.4	1910.8
32.5°	1906.0	1891.9	1853.9	1839.6	1830.1
35°	1832.5	1808.9	1770.9	1756.6	1744.8
37.5°	1749.5	1728.1	1690.2	1673.6	1661.8
40°	1664.3	1645.1	1607.2	1586.1	1576.5
42.5°	1581.3	1562.1	1524.4	1500.5	1486.5
45°	1491.3	1474.6	1438.9	1413.0	1403.5
47.5°	1403.5	1386.9	1348.9	1322.7	1308.6
50°	1310.9	1299.1	1265.9	1232.7	1220.9
52.5°	1220.9	1204.2	1173.6	1147.4	1130.8
55°	1128.5	1114.2	1085.8	1057.4	1045.5
57.5°	1036.0	1024.2	993.2	964.8	955.2
60°	943.4	934.2	900.9	874.8	867.7
62.5°	853.4	836.8	813.1	789.5	780.0
65°	761.1	746.8	723.1	701.7	689.9
67.5°	666.2	654.2	633.0	616.5	606.9
70°	578.5	568.9	547.6	531.0	521.6
72.5°	488.4	478.9	467.0	450.5	443.4
75°	398.1	393.6	381.6	367.5	372.2
77.5°	317.7	308.1	303.3	296.3	289.2
80°	237.2	234.7	229.9	222.9	218.0
82.5°	161.3	161.3	159.0	149.4	149.4
85°	97.1	94.8	92.6	85.3	83.0
87.5°	42.8	38.0	33.2	26.1	23.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931415

CATALOG NUMBER: DFN2DS-TR3F0-080DS927-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.18	16.79	15.55	17.11	17.42	14.74	16.35	15.10	16.66	16.98
	3H	16.93	18.39	17.31	18.71	19.07	16.44	17.90	16.82	18.22	18.58
	4H	17.58	18.95	17.98	19.30	19.67	17.08	18.45	17.48	18.80	19.18
	6H	18.05	19.32	18.46	19.68	20.07	17.55	18.81	17.96	19.18	19.57
	8H	18.19	19.40	18.62	19.79	20.19	17.69	18.90	18.11	19.29	19.69
	12H	18.28	19.44	18.71	19.82	20.25	17.77	18.93	18.20	19.31	19.74
4H	2H	15.74	17.11	16.14	17.46	17.84	15.39	16.76	15.79	17.11	17.48
	3H	17.72	18.86	18.13	19.26	19.66	17.31	18.46	17.72	18.85	19.25
	4H	18.49	19.53	18.93	19.94	20.38	18.07	19.11	18.50	19.52	19.96
	6H	19.09	20.00	19.54	20.44	20.89	18.66	19.56	19.11	20.00	20.46
	8H	19.28	20.13	19.74	20.57	21.03	18.84	19.69	19.30	20.13	20.60
	12H	19.41	20.17	19.89	20.65	21.12	18.96	19.72	19.44	20.20	20.66
8H	4H	18.77	19.61	19.23	20.06	20.52	18.39	19.24	18.85	19.68	20.15
	6H	19.48	20.18	19.98	20.67	21.15	19.10	19.80	19.59	20.29	20.77
	8H	19.74	20.37	20.25	20.88	21.36	19.35	19.98	19.86	20.49	20.97
	12H	19.94	20.50	20.45	20.99	21.55	19.53	20.09	20.03	20.58	21.14
12H	4H	18.79	19.55	19.27	20.03	20.50	18.43	19.19	18.91	19.66	20.13
	6H	19.53	20.16	20.04	20.67	21.15	19.16	19.79	19.67	20.30	20.78
	8H	19.84	20.40	20.35	20.89	21.45	19.46	20.02	19.97	20.51	21.07