

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931416

Luminaire Tested: DFN2DS-TR3F0-080DS927-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931416
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-080DS927-RLL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5385.6 lumens
Efficiency: N/A
Efficacy: 63.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 85.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931416

CATALOG NUMBER: DFN2DS-TR3F0-080DS927-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931416

CATALOG NUMBER: DFN2DS-TR3F0-080DS927-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3263	3263	3263
5°	3276	3222	3240
10°	3251	3170	3143
15°	3213	3076	2987
20°	3162	2942	2794
25°	3108	2789	2607
30°	3035	2632	2366
35°	2963	2462	2156
40°	2891	2286	1912
45°	2807	2088	1691
50°	2720	1888	1475
55°	2631	1673	1267
60°	2528	1447	1051
65°	2411	1216	957
70°	2271	1001	880
75°	2099	913	822
80°	1853	816	748
85°	1457	643	643

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2807 cd/sqm

TEST NUMBER: P931416

CATALOG NUMBER: DFN2DS-TR3F0-080DS927-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	245.4	4.6
10°-20°	673.7	12.5
20°-30°	945.9	17.6
30°-40°	1031.1	19.1
40°-50°	947.7	17.6
50°-60°	744.3	13.8
60°-70°	484.4	9.0
70°-80°	249.4	4.6
80°-90°	63.7	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1865.1	34.6
0°-40°	2896.2	53.8
0°-60°	4588.1	85.2
0°-90°	5385.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5385.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2619	2619	2619	2619	2619	
5°	2619	2607	2576	2597	2590	248
15°	2491	2464	2384	2339	2315	702
25°	2261	2185	2028	1932	1896	1040
35°	1948	1827	1619	1469	1417	1219
45°	1593	1434	1185	1016	960	1230
55°	1211	1026	770	628	583	1082
65°	818	626	412	332	325	811
75°	436	270	190	173	171	461
85°	102	52	45	45	45	122
90°	0	0	0	0	0	

TEST NUMBER: P931416

CATALOG NUMBER: DFN2DS-TR3F0-080DS927-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2618.7	2618.7	2618.7	2618.7	2618.7
2.5°	2630.5	2618.7	2592.5	2616.4	2611.6
5°	2618.7	2606.9	2575.9	2597.3	2590.2
7.5°	2597.3	2583.2	2550.0	2559.3	2547.5
10°	2568.9	2552.3	2505.0	2497.7	2483.6
12.5°	2533.4	2512.1	2447.9	2433.8	2407.7
15°	2490.7	2464.5	2384.1	2339.1	2315.4
17.5°	2440.9	2402.9	2303.4	2251.3	2213.3
20°	2384.1	2336.6	2218.2	2159.1	2106.7
22.5°	2322.5	2267.9	2130.4	2049.9	2014.5
25°	2260.8	2185.0	2028.5	1931.5	1895.8
27.5°	2187.4	2106.7	1933.7	1822.4	1767.8
30°	2109.3	2019.0	1829.4	1708.7	1644.6
32.5°	2033.3	1924.2	1730.1	1587.8	1528.5
35°	1948.1	1827.1	1618.7	1469.4	1417.0
37.5°	1865.1	1734.6	1514.4	1350.7	1291.6
40°	1777.4	1635.3	1405.2	1237.0	1175.4
42.5°	1687.4	1535.8	1296.3	1120.9	1061.8
45°	1592.6	1433.7	1185.0	1016.5	959.7
47.5°	1502.6	1334.4	1078.4	909.9	857.9
50°	1402.9	1234.8	974.1	810.4	760.8
52.5°	1305.7	1127.9	874.4	718.1	673.1
55°	1210.9	1026.1	770.1	628.1	583.1
57.5°	1113.9	924.3	677.9	545.1	507.1
60°	1014.2	824.7	580.5	459.8	421.9
62.5°	917.2	727.6	497.6	384.0	365.1
65°	817.7	625.5	412.3	331.9	324.6
67.5°	722.9	530.8	331.9	291.4	284.4
70°	623.3	438.5	274.8	251.1	241.6
72.5°	528.5	353.0	229.8	211.0	206.2
75°	436.0	270.1	189.6	173.0	170.8
77.5°	343.7	191.8	149.4	139.8	135.0
80°	258.2	137.6	113.7	104.3	104.3
82.5°	180.0	92.5	78.2	73.4	73.4
85°	101.9	52.0	45.0	45.0	45.0
87.5°	37.9	18.8	18.8	16.6	16.6
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931416

CATALOG NUMBER: DFN2DS-TR3F0-080DS927-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.34	16.87	15.71	17.18	17.49	11.30	12.83	11.67	13.14	13.45
	3H	17.11	18.47	17.49	18.80	19.16	12.57	13.93	12.95	14.26	14.62
	4H	17.78	19.06	18.18	19.41	19.78	13.07	14.35	13.47	14.70	15.08
	6H	18.26	19.45	18.68	19.81	20.21	13.45	14.63	13.86	15.00	15.39
	8H	18.43	19.56	18.86	19.95	20.35	13.58	14.70	14.00	15.09	15.49
	12H	18.53	19.61	18.96	19.99	20.42	13.66	14.74	14.09	15.12	15.55
4H	2H	15.45	16.73	15.85	17.08	17.46	12.00	13.28	12.40	13.63	14.01
	3H	17.38	18.44	17.79	18.84	19.25	13.44	14.51	13.85	14.91	15.31
	4H	18.13	19.09	18.56	19.50	19.94	14.04	15.00	14.47	15.41	15.85
	6H	18.72	19.55	19.18	20.00	20.46	14.53	15.36	14.99	15.80	16.26
	8H	18.94	19.71	19.40	20.16	20.63	14.69	15.47	15.16	15.91	16.38
	12H	19.09	19.78	19.57	20.26	20.73	14.81	15.50	15.29	15.98	16.45
8H	4H	18.15	18.93	18.62	19.38	19.84	14.40	15.17	14.86	15.62	16.09
	6H	18.79	19.43	19.29	19.93	20.40	14.98	15.63	15.48	16.12	16.59
	8H	19.04	19.62	19.56	20.13	20.62	15.20	15.78	15.72	16.29	16.78
	12H	19.25	19.76	19.76	20.25	20.81	15.38	15.89	15.89	16.38	16.95
12H	4H	18.14	18.83	18.62	19.31	19.78	14.44	15.13	14.92	15.61	16.08
	6H	18.77	19.35	19.29	19.86	20.35	15.05	15.62	15.56	16.13	16.62
	8H	19.06	19.57	19.57	20.06	20.62	15.32	15.83	15.83	16.32	16.89