

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931433

Luminaire Tested: DFN2DS-TR3F0-090DS927-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931433
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-090DS927-FLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7056.8 lumens
Efficiency: N/A
Efficacy: 71.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 99.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931433

CATALOG NUMBER: DFN2DS-TR3F0-090DS927-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931433

CATALOG NUMBER: DFN2DS-TR3F0-090DS927-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3456	3456	3456
5°	3469	3419	3440
10°	3449	3385	3402
15°	3406	3341	3338
20°	3345	3275	3272
25°	3285	3194	3194
30°	3208	3120	3093
35°	3136	3031	2986
40°	3046	2941	2885
45°	2956	2853	2782
50°	2859	2761	2663
55°	2758	2654	2556
60°	2645	2526	2433
65°	2525	2399	2289
70°	2371	2244	2138
75°	2157	2067	2016
80°	1915	1856	1761
85°	1561	1488	1335

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2956 cd/sqm

TEST NUMBER: P931433

CATALOG NUMBER: DFN2DS-TR3F0-090DS927-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	261.0	3.7
10°-20°	734.5	10.4
20°-30°	1079.4	15.3
30°-40°	1253.7	17.8
40°-50°	1252.1	17.7
50°-60°	1091.8	15.5
60°-70°	807.1	11.4
70°-80°	456.6	6.5
80°-90°	120.5	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2074.9	29.4
0°-40°	3328.6	47.2
0°-60°	5672.5	80.4
0°-90°	7056.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7056.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2774	2774	2774	2774	2774	
5°	2774	2763	2734	2755	2750	263
15°	2640	2624	2590	2600	2587	744
25°	2390	2368	2323	2328	2323	1100
35°	2062	2035	1992	1976	1963	1287
45°	1678	1659	1619	1590	1579	1295
55°	1270	1254	1222	1190	1176	1135
65°	856	840	814	790	776	847
75°	448	443	429	413	419	478
85°	109	107	104	96	93	128
90°	0	0	0	0	0	

TEST NUMBER: P931433

CATALOG NUMBER: DFN2DS-TR3F0-090DS927-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2773.5	2773.5	2773.5	2773.5	2773.5
2.5°	2789.7	2776.4	2747.0	2773.5	2768.4
5°	2773.5	2763.1	2733.7	2754.9	2749.7
7.5°	2754.9	2739.1	2709.6	2731.1	2725.7
10°	2725.7	2707.1	2675.1	2696.3	2688.4
12.5°	2685.5	2669.7	2637.8	2651.0	2645.7
15°	2640.3	2624.5	2589.6	2600.4	2587.1
17.5°	2584.2	2568.4	2533.6	2546.9	2533.6
20°	2522.8	2507.0	2469.6	2477.5	2467.1
22.5°	2461.7	2437.7	2402.8	2402.8	2397.5
25°	2389.5	2368.3	2323.1	2328.2	2323.1
27.5°	2309.5	2290.8	2256.3	2248.4	2235.1
30°	2229.7	2208.2	2168.3	2160.3	2149.6
32.5°	2144.3	2128.4	2085.7	2069.6	2058.8
35°	2061.7	2035.0	1992.3	1976.2	1962.9
37.5°	1968.3	1944.2	1901.4	1882.8	1869.5
40°	1872.3	1850.8	1808.1	1784.3	1773.6
42.5°	1778.9	1757.4	1715.0	1688.1	1672.3
45°	1677.6	1659.0	1618.8	1589.6	1578.9
47.5°	1578.9	1560.2	1517.5	1488.1	1472.2
50°	1474.8	1461.5	1424.1	1386.8	1373.5
52.5°	1373.5	1354.8	1320.3	1290.9	1272.2
55°	1269.7	1253.5	1221.5	1189.6	1176.3
57.5°	1165.5	1152.2	1117.4	1085.4	1074.7
60°	1061.4	1050.9	1013.5	984.1	976.2
62.5°	960.1	941.4	914.8	888.2	877.5
65°	856.2	840.1	813.5	789.5	776.2
67.5°	749.5	736.0	712.2	693.6	682.8
70°	650.8	640.0	616.0	597.3	586.9
72.5°	549.5	538.7	525.4	506.8	498.9
75°	448.0	442.8	429.3	413.4	418.8
77.5°	357.4	346.7	341.3	333.4	325.4
80°	266.8	264.0	258.6	250.7	245.4
82.5°	181.4	181.4	178.8	168.1	168.1
85°	109.2	106.7	104.1	95.9	93.4
87.5°	48.1	42.7	37.4	29.5	26.6
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931433

CATALOG NUMBER: DFN2DS-TR3F0-090DS927-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.59	17.20	15.96	17.52	17.83	15.15	16.76	15.51	17.07	17.39
	3H	17.34	18.80	17.72	19.12	19.48	16.85	18.30	17.23	18.63	18.99
	4H	17.99	19.36	18.39	19.70	20.08	17.49	18.86	17.89	19.21	19.59
	6H	18.46	19.73	18.87	20.09	20.48	17.96	19.22	18.37	19.59	19.98
	8H	18.60	19.81	19.02	20.20	20.60	18.10	19.31	18.52	19.70	20.10
	12H	18.69	19.85	19.12	20.23	20.66	18.18	19.34	18.61	19.72	20.15
4H	2H	16.15	17.52	16.55	17.87	18.24	15.80	17.17	16.20	17.52	17.89
	3H	18.13	19.27	18.54	19.67	20.07	17.72	18.87	18.13	19.26	19.66
	4H	18.90	19.94	19.33	20.35	20.79	18.48	19.52	18.91	19.93	20.37
	6H	19.50	20.40	19.95	20.85	21.30	19.07	19.97	19.52	20.41	20.87
	8H	19.69	20.54	20.15	20.98	21.44	19.25	20.10	19.71	20.54	21.01
	12H	19.82	20.58	20.30	21.06	21.53	19.37	20.13	19.85	20.61	21.07
8H	4H	19.18	20.02	19.64	20.47	20.93	18.80	19.65	19.26	20.09	20.56
	6H	19.89	20.59	20.38	21.08	21.56	19.51	20.21	20.00	20.70	21.18
	8H	20.15	20.78	20.66	21.29	21.77	19.76	20.39	20.27	20.90	21.38
	12H	20.35	20.91	20.86	21.40	21.96	19.94	20.49	20.44	20.99	21.55
12H	4H	19.20	19.96	19.68	20.44	20.91	18.84	19.60	19.32	20.07	20.54
	6H	19.94	20.57	20.45	21.08	21.56	19.57	20.20	20.08	20.71	21.19
	8H	20.25	20.81	20.76	21.30	21.86	19.87	20.43	20.38	20.92	21.48