

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931345

Luminaire Tested: DFN2DS-TR3F0-040DS930-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931345
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-040DS930-FLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3227.4 lumens
Efficiency: N/A
Efficacy: 82.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 39.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931345

CATALOG NUMBER: DFN2DS-TR3F0-040DS930-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931345

CATALOG NUMBER: DFN2DS-TR3F0-040DS930-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1581	1581	1581
5°	1587	1564	1573
10°	1577	1548	1556
15°	1558	1528	1526
20°	1530	1498	1496
25°	1503	1461	1461
30°	1467	1427	1415
35°	1434	1386	1366
40°	1393	1345	1320
45°	1352	1305	1273
50°	1308	1263	1218
55°	1262	1214	1169
60°	1210	1155	1113
65°	1155	1097	1047
70°	1084	1026	978
75°	987	945	922
80°	875	849	805
85°	715	681	611

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1352 cd/sqm

TEST NUMBER: P931345

CATALOG NUMBER: DFN2DS-TR3F0-040DS930-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.4	3.7
10°-20°	335.9	10.4
20°-30°	493.7	15.3
30°-40°	573.4	17.8
40°-50°	572.7	17.7
50°-60°	499.3	15.5
60°-70°	369.1	11.4
70°-80°	208.8	6.5
80°-90°	55.1	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	949.0	29.4
0°-40°	1522.3	47.2
0°-60°	2594.3	80.4
0°-90°	3227.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3227.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1268	1268	1268	1268	1268	
5°	1268	1264	1250	1260	1258	120
15°	1208	1200	1184	1189	1183	340
25°	1093	1083	1062	1065	1062	503
35°	943	931	911	904	898	589
45°	767	759	740	727	722	592
55°	581	573	559	544	538	519
65°	392	384	372	361	355	387
75°	205	202	196	189	192	219
85°	50	49	48	44	43	59
90°	0	0	0	0	0	

TEST NUMBER: P931345

CATALOG NUMBER: DFN2DS-TR3F0-040DS930-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1268.5	1268.5	1268.5	1268.5	1268.5
2.5°	1275.9	1269.8	1256.3	1268.5	1266.2
5°	1268.5	1263.7	1250.2	1259.9	1257.6
7.5°	1259.9	1252.7	1239.2	1249.1	1246.6
10°	1246.6	1238.1	1223.5	1233.2	1229.5
12.5°	1228.2	1221.0	1206.4	1212.5	1209.9
15°	1207.5	1200.3	1184.4	1189.2	1183.2
17.5°	1181.9	1174.7	1158.8	1164.8	1158.8
20°	1153.8	1146.5	1129.5	1133.1	1128.4
22.5°	1125.8	1114.8	1098.9	1098.9	1096.5
25°	1092.8	1083.1	1062.4	1064.8	1062.4
27.5°	1056.2	1047.7	1032.0	1028.3	1022.3
30°	1019.7	1009.9	991.7	988.0	983.1
32.5°	980.7	973.4	953.9	946.5	941.6
35°	942.9	930.7	911.2	903.8	897.7
37.5°	900.2	889.2	869.6	861.1	855.0
40°	856.3	846.5	826.9	816.1	811.2
42.5°	813.6	803.8	784.4	772.0	764.8
45°	767.2	758.8	740.3	727.1	722.1
47.5°	722.1	713.5	694.1	680.6	673.4
50°	674.5	668.4	651.3	634.2	628.1
52.5°	628.1	619.6	603.8	590.4	581.8
55°	580.7	573.3	558.7	544.0	538.0
57.5°	533.0	527.0	511.0	496.4	491.5
60°	485.4	480.6	463.6	450.1	446.5
62.5°	439.1	430.6	418.4	406.2	401.3
65°	391.6	384.2	372.0	361.0	355.0
67.5°	342.8	336.6	325.8	317.2	312.3
70°	297.6	292.7	281.7	273.2	268.4
72.5°	251.3	246.4	240.3	231.8	228.1
75°	204.9	202.5	196.3	189.1	191.5
77.5°	163.4	158.5	156.1	152.4	148.8
80°	122.0	120.7	118.3	114.7	112.2
82.5°	83.0	83.0	81.8	76.9	76.9
85°	50.0	48.8	47.6	43.8	42.7
87.5°	22.0	19.6	17.1	13.4	12.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931345

CATALOG NUMBER: DFN2DS-TR3F0-040DS930-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.87	14.48	13.24	14.80	15.11	12.43	14.04	12.79	14.35	14.67
	3H	14.62	16.08	15.00	16.40	16.76	14.13	15.59	14.51	15.91	16.27
	4H	15.27	16.64	15.67	16.99	17.36	14.77	16.14	15.17	16.49	16.87
	6H	15.74	17.01	16.15	17.37	17.76	15.24	16.51	15.65	16.87	17.26
	8H	15.88	17.09	16.31	17.48	17.88	15.38	16.59	15.80	16.98	17.38
	12H	15.97	17.13	16.40	17.51	17.94	15.46	16.62	15.89	17.00	17.43
4H	2H	13.43	14.80	13.83	15.15	15.53	13.08	14.45	13.48	14.80	15.17
	3H	15.41	16.56	15.82	16.95	17.35	15.00	16.15	15.41	16.55	16.95
	4H	16.19	17.22	16.62	17.63	18.07	15.76	16.80	16.19	17.21	17.65
	6H	16.78	17.69	17.24	18.13	18.58	16.35	17.25	16.80	17.69	18.15
	8H	16.97	17.82	17.43	18.26	18.73	16.53	17.38	16.99	17.82	18.29
	12H	17.10	17.86	17.58	18.34	18.81	16.65	17.41	17.13	17.89	18.36
8H	4H	16.46	17.31	16.92	17.75	18.21	16.08	16.93	16.55	17.37	17.84
	6H	17.17	17.88	17.67	18.36	18.84	16.79	17.49	17.29	17.98	18.46
	8H	17.43	18.06	17.94	18.57	19.06	17.04	17.67	17.55	18.18	18.66
	12H	17.63	18.19	18.14	18.68	19.24	17.22	17.78	17.73	18.27	18.83
12H	4H	16.48	17.24	16.96	17.72	18.19	16.12	16.88	16.60	17.36	17.83
	6H	17.22	17.85	17.73	18.36	18.84	16.85	17.48	17.36	17.99	18.47
	8H	17.53	18.09	18.04	18.58	19.14	17.15	17.71	17.66	18.20	18.76