

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931346

Luminaire Tested: DFN2DS-TR3F0-040DS930-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931346
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-040DS930-RLL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2771.0 lumens
Efficiency: N/A
Efficacy: 70.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 39.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931346

CATALOG NUMBER: DFN2DS-TR3F0-040DS930-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931346

CATALOG NUMBER: DFN2DS-TR3F0-040DS930-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	86		
2	101	94	87	82	98	92	86	81	88	83	79	85	81	78	82	79	76	74		
3	93	83	76	70	90	82	75	69	79	73	68	76	71	67	74	69	66	64		
4	86	75	66	60	83	73	66	60	71	64	59	69	63	58	66	62	57	55		
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51	49		
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43		
7	68	56	47	42	67	55	47	42	53	46	41	52	46	41	51	45	41	39		
8	64	51	43	38	62	51	43	37	49	42	37	48	42	37	47	41	37	35		
9	60	47	39	34	59	47	39	34	46	39	34	44	38	34	44	38	34	32		
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	41	35	31	29		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1679	1679	1679
5°	1685	1658	1667
10°	1673	1631	1617
15°	1653	1583	1537
20°	1627	1513	1437
25°	1599	1435	1341
30°	1562	1354	1218
35°	1525	1267	1109
40°	1488	1176	984
45°	1444	1074	870
50°	1399	971	759
55°	1354	861	652
60°	1300	744	541
65°	1240	625	492
70°	1168	515	453
75°	1080	470	423
80°	953	419	385
85°	749	330	330

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1444 cd/sqm

TEST NUMBER: P931346

CATALOG NUMBER: DFN2DS-TR3F0-040DS930-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	4.6
10°-20°	346.7	12.5
20°-30°	486.7	17.6
30°-40°	530.5	19.1
40°-50°	487.6	17.6
50°-60°	382.9	13.8
60°-70°	249.3	9.0
70°-80°	128.3	4.6
80°-90°	32.8	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	959.6	34.6
0°-40°	1490.1	53.8
0°-60°	2360.7	85.2
0°-90°	2771.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2771.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1347	1347	1347	1347	1347	
5°	1347	1341	1325	1336	1333	128
15°	1282	1268	1227	1204	1191	361
25°	1163	1124	1044	994	975	535
35°	1002	940	833	756	729	627
45°	819	738	610	523	494	633
55°	623	528	396	323	300	557
65°	421	322	212	171	167	417
75°	224	139	98	89	88	237
85°	52	27	23	23	23	63
90°	0	0	0	0	0	

TEST NUMBER: P931346

CATALOG NUMBER: DFN2DS-TR3F0-040DS930-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1347.4	1347.4	1347.4	1347.4	1347.4
2.5°	1353.5	1347.4	1333.9	1346.2	1343.7
5°	1347.4	1341.2	1325.4	1336.4	1332.8
7.5°	1336.4	1329.1	1312.1	1316.8	1310.8
10°	1321.8	1313.2	1288.8	1285.1	1277.9
12.5°	1303.5	1292.5	1259.5	1252.2	1238.8
15°	1281.5	1268.1	1226.7	1203.5	1191.4
17.5°	1255.9	1236.4	1185.1	1158.4	1138.8
20°	1226.7	1202.2	1141.2	1110.8	1083.9
22.5°	1195.0	1166.9	1096.1	1054.7	1036.5
25°	1163.2	1124.2	1043.7	993.8	975.4
27.5°	1125.5	1083.9	995.0	937.7	909.5
30°	1085.3	1038.8	941.2	879.1	846.2
32.5°	1046.2	990.1	890.1	817.0	786.4
35°	1002.4	940.1	832.8	756.0	729.1
37.5°	959.7	892.5	779.1	695.0	664.6
40°	914.5	841.4	723.1	636.5	604.8
42.5°	868.1	790.1	667.0	576.7	546.3
45°	819.4	737.7	609.7	523.1	493.8
47.5°	773.1	686.6	554.9	468.2	441.4
50°	721.8	635.3	501.1	417.0	391.4
52.5°	671.8	580.4	450.0	369.4	346.3
55°	623.1	528.0	396.3	323.1	300.0
57.5°	573.1	475.6	348.7	280.4	261.0
60°	521.8	424.3	298.7	236.6	217.1
62.5°	472.0	374.4	256.0	197.6	187.9
65°	420.7	321.8	212.1	170.7	167.0
67.5°	372.0	273.1	170.7	150.0	146.3
70°	320.7	225.6	141.4	129.3	124.3
72.5°	272.0	181.7	118.3	108.6	106.1
75°	224.3	139.0	97.6	89.0	87.9
77.5°	176.9	98.7	76.9	72.0	69.4
80°	132.8	70.7	58.4	53.7	53.7
82.5°	92.7	47.6	40.3	37.7	37.7
85°	52.4	26.8	23.1	23.1	23.1
87.5°	19.6	9.7	9.7	8.6	8.6
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931346

CATALOG NUMBER: DFN2DS-TR3F0-040DS930-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.04	14.56	13.40	14.87	15.19	8.99	10.52	9.36	10.83	11.14
	3H	14.80	16.17	15.18	16.49	16.86	10.26	11.63	10.64	11.95	12.32
	4H	15.47	16.75	15.87	17.10	17.47	10.76	12.04	11.16	12.39	12.77
	6H	15.96	17.14	16.37	17.51	17.90	11.14	12.33	11.56	12.69	13.08
	8H	16.12	17.25	16.55	17.64	18.04	11.27	12.39	11.69	12.78	13.18
	12H	16.22	17.30	16.66	17.68	18.11	11.35	12.43	11.78	12.81	13.24
4H	2H	13.14	14.42	13.54	14.77	15.15	9.69	10.97	10.09	11.32	11.70
	3H	15.07	16.14	15.48	16.54	16.94	11.13	12.20	11.54	12.60	13.00
	4H	15.82	16.78	16.25	17.19	17.63	11.73	12.69	12.17	13.11	13.54
	6H	16.41	17.25	16.87	17.69	18.15	12.22	13.05	12.68	13.50	13.96
	8H	16.63	17.41	17.09	17.85	18.32	12.38	13.16	12.85	13.60	14.07
	12H	16.78	17.48	17.26	17.95	18.43	12.50	13.19	12.98	13.67	14.14
8H	4H	15.85	16.62	16.31	17.07	17.54	12.09	12.87	12.55	13.31	13.78
	6H	16.48	17.13	16.98	17.62	18.09	12.67	13.32	13.17	13.81	14.29
	8H	16.73	17.31	17.25	17.82	18.31	12.89	13.47	13.41	13.98	14.47
	12H	16.94	17.45	17.45	17.94	18.50	13.07	13.58	13.58	14.08	14.64
12H	4H	15.83	16.53	16.31	17.00	17.47	12.13	12.83	12.61	13.30	13.78
	6H	16.46	17.04	16.98	17.55	18.04	12.74	13.32	13.25	13.82	14.31
	8H	16.75	17.26	17.26	17.75	18.32	13.01	13.52	13.52	14.01	14.58