

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931399

Luminaire Tested: DFN2DS-TR3F0-070DS930-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931399
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-070DS930-FLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5648.0 lumens
Efficiency: N/A
Efficacy: 75.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 74.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931399

CATALOG NUMBER: DFN2DS-TR3F0-070DS930-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931399

CATALOG NUMBER: DFN2DS-TR3F0-070DS930-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2766	2766	2766
5°	2777	2737	2753
10°	2760	2709	2723
15°	2726	2674	2671
20°	2678	2621	2618
25°	2630	2556	2556
30°	2568	2497	2476
35°	2510	2426	2390
40°	2438	2354	2309
45°	2366	2283	2227
50°	2288	2210	2131
55°	2207	2124	2045
60°	2117	2022	1947
65°	2021	1920	1832
70°	1898	1796	1711
75°	1726	1654	1614
80°	1532	1485	1409
85°	1250	1192	1068

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2366 cd/sqm

TEST NUMBER: P931399

CATALOG NUMBER: DFN2DS-TR3F0-070DS930-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	208.9	3.7
10°-20°	587.9	10.4
20°-30°	863.9	15.3
30°-40°	1003.4	17.8
40°-50°	1002.1	17.7
50°-60°	873.8	15.5
60°-70°	646.0	11.4
70°-80°	365.5	6.5
80°-90°	96.5	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1660.7	29.4
0°-40°	2664.1	47.2
0°-60°	4540.1	80.4
0°-90°	5648.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5648.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2220	2220	2220	2220	2220	
5°	2220	2212	2188	2205	2201	211
15°	2113	2100	2073	2081	2071	595
25°	1913	1896	1859	1863	1859	880
35°	1650	1629	1594	1582	1571	1030
45°	1343	1328	1296	1272	1264	1036
55°	1016	1003	978	952	941	908
65°	685	672	651	632	621	678
75°	358	354	344	331	335	383
85°	87	85	83	77	75	103
90°	0	0	0	0	0	

TEST NUMBER: P931399

CATALOG NUMBER: DFN2DS-TR3F0-070DS930-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2219.8	2219.8	2219.8	2219.8	2219.8
2.5°	2232.8	2222.1	2198.5	2219.8	2215.7
5°	2219.8	2211.5	2187.9	2204.9	2200.8
7.5°	2204.9	2192.2	2168.6	2185.9	2181.6
10°	2181.6	2166.6	2141.0	2158.0	2151.7
12.5°	2149.4	2136.8	2111.2	2121.8	2117.5
15°	2113.2	2100.5	2072.6	2081.3	2070.6
17.5°	2068.3	2055.7	2027.8	2038.5	2027.8
20°	2019.2	2006.5	1976.6	1983.0	1974.6
22.5°	1970.3	1951.0	1923.2	1923.2	1918.8
25°	1912.6	1895.5	1859.3	1863.4	1859.3
27.5°	1848.4	1833.5	1805.9	1799.5	1788.8
30°	1784.6	1767.3	1735.5	1729.1	1720.5
32.5°	1716.1	1703.5	1669.3	1656.4	1647.8
35°	1650.0	1628.8	1594.5	1581.7	1571.0
37.5°	1575.3	1556.1	1521.8	1506.9	1496.3
40°	1498.5	1481.3	1447.1	1428.1	1419.5
42.5°	1423.8	1406.6	1372.6	1351.1	1338.4
45°	1342.7	1327.8	1295.6	1272.3	1263.7
47.5°	1263.7	1248.7	1214.5	1191.0	1178.3
50°	1180.4	1169.7	1139.8	1109.9	1099.3
52.5°	1099.3	1084.4	1056.7	1033.2	1018.2
55°	1016.1	1003.3	977.7	952.1	941.4
57.5°	932.8	922.2	894.3	868.7	860.2
60°	849.5	841.1	811.3	787.7	781.3
62.5°	768.4	753.5	732.2	710.9	702.3
65°	685.3	672.4	651.1	631.9	621.2
67.5°	599.9	589.1	570.0	555.1	546.5
70°	520.9	512.3	493.0	478.1	469.7
72.5°	439.8	431.2	420.5	405.6	399.3
75°	358.5	354.4	343.5	330.9	335.2
77.5°	286.1	277.4	273.1	266.7	260.5
80°	213.5	211.3	207.0	200.7	196.3
82.5°	145.2	145.2	143.1	134.6	134.6
85°	87.4	85.4	83.4	76.8	74.7
87.5°	38.5	34.2	29.9	23.6	21.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931399

CATALOG NUMBER: DFN2DS-TR3F0-070DS930-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.82	16.43	15.18	16.74	17.06	14.37	15.98	14.74	16.30	16.61
	3H	16.57	18.02	16.94	18.35	18.71	16.08	17.53	16.45	17.86	18.22
	4H	17.21	18.58	17.61	18.93	19.31	16.72	18.09	17.12	18.44	18.81
	6H	17.68	18.95	18.09	19.32	19.71	17.18	18.45	17.59	18.82	19.21
	8H	17.83	19.04	18.25	19.43	19.83	17.32	18.53	17.75	18.92	19.32
	12H	17.92	19.08	18.35	19.46	19.89	17.40	18.56	17.83	18.95	19.37
4H	2H	15.38	16.75	15.78	17.09	17.47	15.03	16.39	15.42	16.74	17.12
	3H	17.35	18.50	17.76	18.90	19.30	16.95	18.09	17.36	18.49	18.89
	4H	18.13	19.17	18.56	19.58	20.02	17.71	18.74	18.14	19.16	19.59
	6H	18.73	19.63	19.18	20.07	20.53	18.29	19.20	18.75	19.64	20.10
	8H	18.92	19.76	19.38	20.20	20.67	18.48	19.32	18.94	19.77	20.23
	12H	19.05	19.81	19.53	20.28	20.75	18.60	19.36	19.08	19.83	20.30
8H	4H	18.40	19.25	18.86	19.69	20.16	18.03	18.88	18.49	19.32	19.78
	6H	19.12	19.82	19.61	20.31	20.78	18.74	19.44	19.23	19.93	20.40
	8H	19.38	20.01	19.89	20.51	21.00	18.99	19.62	19.49	20.12	20.61
	12H	19.58	20.13	20.08	20.62	21.19	19.16	19.72	19.67	20.21	20.77
12H	4H	18.43	19.19	18.91	19.66	20.13	18.06	18.82	18.54	19.30	19.77
	6H	19.16	19.79	19.67	20.30	20.79	18.79	19.43	19.30	19.93	20.42
	8H	19.48	20.03	19.98	20.52	21.09	19.10	19.66	19.61	20.15	20.71

END OF REPORT