

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930701

Luminaire Tested: DFN2DS-PN4F0-070DS940-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930701
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN4F0-070DS940-FLL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6181.6 lumens
Efficiency: N/A
Efficacy: 86.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.94' x L: 3.74' x H: 0')
CIE Type: Direct

Input Watts (W): 71.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930701

CATALOG NUMBER: DFN2DS-PN4F0-070DS940-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930701

CATALOG NUMBER: DFN2DS-PN4F0-070DS940-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90	88	86	84
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80	76	73	71
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63	58	54	51
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57	51	47	45
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52	46	41	39
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47	41	37	35
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44	38	33	31
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40	34	30	28
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37	32	27	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1773	1773	1773
5°	1780	1755	1765
10°	1770	1737	1746
15°	1748	1714	1713
20°	1717	1681	1679
25°	1686	1639	1639
30°	1646	1601	1587
35°	1609	1555	1532
40°	1563	1509	1480
45°	1517	1464	1428
50°	1467	1417	1366
55°	1415	1362	1311
60°	1357	1296	1249
65°	1296	1231	1174
70°	1217	1152	1097
75°	1107	1060	1035
80°	982	953	903
85°	802	765	685

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1517 cd/sqm

TEST NUMBER: P930701

CATALOG NUMBER: DFN2DS-PN4F0-070DS940-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	228.7	3.7
10°-20°	643.4	10.4
20°-30°	945.5	15.3
30°-40°	1098.2	17.8
40°-50°	1096.8	17.7
50°-60°	956.4	15.5
60°-70°	707.0	11.4
70°-80°	400.0	6.5
80°-90°	105.6	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1817.6	29.4
0°-40°	2915.8	47.2
0°-60°	4969.0	80.4
0°-90°	6181.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6181.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2430	2430	2430	2430	2430	
5°	2430	2420	2395	2413	2409	231
15°	2313	2299	2268	2278	2266	651
25°	2093	2075	2035	2040	2035	963
35°	1806	1783	1745	1731	1719	1128
45°	1470	1453	1418	1392	1383	1134
55°	1112	1098	1070	1042	1030	994
65°	750	736	713	692	680	742
75°	392	388	376	362	367	419
85°	96	94	91	84	82	112
90°	0	0	0	0	0	

TEST NUMBER: P930701

CATALOG NUMBER: DFN2DS-PN4F0-070DS940-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2429.5	2429.5	2429.5	2429.5	2429.5
2.5°	2443.7	2432.0	2406.3	2429.5	2425.1
5°	2429.5	2420.4	2394.7	2413.2	2408.8
7.5°	2413.2	2399.3	2373.5	2392.4	2387.7
10°	2387.7	2371.3	2343.3	2361.9	2355.0
12.5°	2352.5	2338.6	2310.6	2322.2	2317.5
15°	2312.9	2299.0	2268.4	2277.9	2266.2
17.5°	2263.7	2249.9	2219.4	2231.1	2219.4
20°	2209.9	2196.1	2163.4	2170.3	2161.1
22.5°	2156.4	2135.4	2104.9	2104.9	2100.1
25°	2093.3	2074.6	2035.0	2039.5	2035.0
27.5°	2023.1	2006.7	1976.5	1969.5	1957.9
30°	1953.2	1934.3	1899.4	1892.5	1883.0
32.5°	1878.3	1864.5	1827.0	1812.9	1803.4
35°	1805.9	1782.7	1745.2	1731.1	1719.4
37.5°	1724.1	1703.1	1665.6	1649.3	1637.6
40°	1640.1	1621.3	1583.8	1563.1	1553.6
42.5°	1558.3	1539.5	1502.3	1478.8	1464.8
45°	1469.6	1453.2	1418.0	1392.5	1383.0
47.5°	1383.0	1366.7	1329.3	1303.5	1289.7
50°	1291.9	1280.2	1247.5	1214.8	1203.1
52.5°	1203.1	1186.8	1156.6	1130.8	1114.4
55°	1112.1	1098.1	1070.0	1042.0	1030.3
57.5°	1021.0	1009.3	978.8	950.8	941.4
60°	929.7	920.5	887.9	862.1	855.2
62.5°	841.0	824.7	801.4	778.1	768.6
65°	750.1	735.9	712.6	691.6	679.9
67.5°	656.6	644.7	623.9	607.5	598.1
70°	570.1	560.7	539.6	523.2	514.1
72.5°	481.3	472.0	460.3	443.9	437.0
75°	392.4	387.9	376.0	362.2	366.9
77.5°	313.1	303.6	298.9	292.0	285.1
80°	233.7	231.3	226.6	219.6	214.9
82.5°	158.9	158.9	156.6	147.3	147.3
85°	95.7	93.5	91.3	84.0	81.8
87.5°	42.1	37.5	32.7	25.8	23.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930701

CATALOG NUMBER: DFN2DS-PN4F0-070DS940-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.27	14.88	13.64	15.20	15.51	12.83	14.44	13.19	14.75	15.07
	3H	15.02	16.48	15.40	16.80	17.16	14.53	15.99	14.91	16.31	16.67
	4H	15.67	17.04	16.07	17.39	17.76	15.17	16.54	15.57	16.89	17.27
	6H	16.14	17.41	16.55	17.77	18.16	15.64	16.91	16.05	17.27	17.66
	8H	16.28	17.49	16.71	17.88	18.28	15.78	16.99	16.20	17.38	17.78
	12H	16.37	17.53	16.80	17.91	18.34	15.86	17.02	16.29	17.40	17.83
4H	2H	13.83	15.20	14.23	15.55	15.93	13.48	14.85	13.88	15.20	15.57
	3H	15.81	16.96	16.22	17.35	17.75	15.40	16.55	15.81	16.95	17.35
	4H	16.59	17.62	17.02	18.03	18.47	16.16	17.20	16.59	17.61	18.05
	6H	17.18	18.09	17.64	18.53	18.98	16.75	17.65	17.20	18.10	18.55
	8H	17.37	18.22	17.83	18.66	19.13	16.93	17.78	17.39	18.22	18.69
	12H	17.50	18.26	17.98	18.74	19.21	17.05	17.81	17.53	18.29	18.76
8H	4H	16.86	17.71	17.32	18.15	18.61	16.48	17.33	16.95	17.77	18.24
	6H	17.57	18.28	18.07	18.76	19.24	17.19	17.89	17.69	18.38	18.86
	8H	17.83	18.46	18.34	18.97	19.46	17.44	18.07	17.95	18.58	19.06
	12H	18.03	18.59	18.54	19.08	19.64	17.62	18.18	18.13	18.67	19.23
12H	4H	16.88	17.64	17.36	18.12	18.59	16.52	17.28	17.00	17.76	18.23
	6H	17.62	18.25	18.13	18.76	19.24	17.25	17.88	17.76	18.39	18.87
	8H	17.93	18.49	18.44	18.98	19.54	17.55	18.11	18.06	18.60	19.16