

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931383

Luminaire Tested: DFN2DS-TR3F0-060DS935-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931383
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-060DS935-FLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5108.4 lumens
Efficiency: N/A
Efficacy: 82.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 61.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931383

CATALOG NUMBER: DFN2DS-TR3F0-060DS935-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931383

CATALOG NUMBER: DFN2DS-TR3F0-060DS935-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2502	2502	2502
5°	2511	2475	2490
10°	2497	2450	2462
15°	2466	2418	2416
20°	2422	2371	2368
25°	2378	2312	2312
30°	2322	2259	2239
35°	2270	2194	2161
40°	2205	2129	2088
45°	2140	2065	2014
50°	2070	1999	1927
55°	1997	1921	1850
60°	1915	1829	1761
65°	1828	1736	1656
70°	1716	1625	1548
75°	1561	1496	1460
80°	1386	1343	1274
85°	1129	1077	967

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2140 cd/sqm

TEST NUMBER: P931383

CATALOG NUMBER: DFN2DS-TR3F0-060DS935-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.0	3.7
10°-20°	531.7	10.4
20°-30°	781.4	15.3
30°-40°	907.5	17.8
40°-50°	906.4	17.7
50°-60°	790.4	15.5
60°-70°	584.3	11.4
70°-80°	330.6	6.5
80°-90°	87.2	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1502.1	29.4
0°-40°	2409.6	47.2
0°-60°	4106.3	80.4
0°-90°	5108.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5108.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2008	2008	2008	2008	2008	
5°	2008	2000	1979	1994	1991	191
15°	1911	1900	1875	1882	1873	538
25°	1730	1714	1682	1685	1682	796
35°	1492	1473	1442	1430	1421	932
45°	1214	1201	1172	1151	1143	937
55°	919	907	884	861	852	822
65°	620	608	589	572	562	613
75°	324	321	311	299	303	346
85°	79	77	75	69	68	93
90°	0	0	0	0	0	

TEST NUMBER: P931383

CATALOG NUMBER: DFN2DS-TR3F0-060DS935-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2007.8	2007.8	2007.8	2007.8	2007.8
2.5°	2019.5	2009.8	1988.5	2007.8	2004.1
5°	2007.8	2000.2	1978.9	1994.3	1990.6
7.5°	1994.3	1982.8	1961.5	1977.1	1973.2
10°	1973.2	1959.7	1936.5	1951.9	1946.1
12.5°	1944.1	1932.6	1909.5	1919.1	1915.2
15°	1911.3	1899.8	1874.6	1882.5	1872.8
17.5°	1870.8	1859.3	1834.1	1843.7	1834.1
20°	1826.3	1814.9	1787.8	1793.5	1786.0
22.5°	1782.1	1764.6	1739.4	1739.4	1735.6
25°	1729.8	1714.5	1681.6	1685.3	1681.6
27.5°	1671.8	1658.3	1633.3	1627.6	1618.0
30°	1614.1	1598.5	1569.7	1563.9	1556.1
32.5°	1552.2	1540.8	1509.8	1498.1	1490.4
35°	1492.4	1473.2	1442.2	1430.5	1420.9
37.5°	1424.8	1407.4	1376.5	1362.9	1353.3
40°	1355.4	1339.8	1308.9	1291.7	1283.9
42.5°	1287.8	1272.2	1241.5	1222.1	1210.5
45°	1214.5	1200.9	1171.8	1150.8	1142.9
47.5°	1142.9	1129.4	1098.6	1077.2	1065.7
50°	1067.6	1058.0	1031.0	1003.9	994.2
52.5°	994.2	980.7	955.7	934.5	921.0
55°	919.1	907.4	884.3	861.1	851.5
57.5°	843.7	834.1	808.9	785.8	778.0
60°	768.3	760.8	733.8	712.4	706.7
62.5°	695.0	681.5	662.2	642.9	635.2
65°	619.8	608.2	588.9	571.5	561.8
67.5°	542.6	532.8	515.6	502.1	494.2
70°	471.1	463.4	445.9	432.4	424.8
72.5°	397.8	390.0	380.4	366.9	361.1
75°	324.2	320.6	310.7	299.3	303.2
77.5°	258.7	250.9	247.0	241.3	235.6
80°	193.2	191.1	187.2	181.5	177.6
82.5°	131.3	131.3	129.4	121.7	121.7
85°	79.0	77.2	75.3	69.4	67.6
87.5°	34.8	31.0	27.0	21.3	19.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931383

CATALOG NUMBER: DFN2DS-TR3F0-060DS935-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.47	16.08	14.83	16.39	16.71	14.02	15.64	14.39	15.95	16.26
	3H	16.22	17.67	16.60	18.00	18.36	15.73	17.18	16.10	17.51	17.87
	4H	16.87	18.23	17.26	18.58	18.96	16.37	17.74	16.77	18.09	18.46
	6H	17.33	18.60	17.75	18.97	19.36	16.83	18.10	17.24	18.47	18.86
	8H	17.48	18.69	17.90	19.08	19.48	16.97	18.19	17.40	18.57	18.97
	12H	17.57	18.73	18.00	19.11	19.54	17.06	18.22	17.49	18.60	19.03
4H	2H	15.03	16.40	15.43	16.75	17.12	14.68	16.05	15.08	16.39	16.77
	3H	17.00	18.15	17.41	18.55	18.95	16.60	17.74	17.01	18.14	18.54
	4H	17.78	18.82	18.21	19.23	19.67	17.36	18.39	17.79	18.81	19.24
	6H	18.38	19.28	18.83	19.72	20.18	17.95	18.85	18.40	19.29	19.75
	8H	18.57	19.41	19.03	19.86	20.32	18.13	18.98	18.59	19.42	19.88
	12H	18.70	19.46	19.18	19.93	20.40	18.25	19.01	18.73	19.48	19.95
8H	4H	18.05	18.90	18.51	19.34	19.81	17.68	18.53	18.14	18.97	19.43
	6H	18.77	19.47	19.26	19.96	20.44	18.39	19.09	18.88	19.58	20.05
	8H	19.03	19.66	19.54	20.17	20.65	18.64	19.27	19.15	19.77	20.26
	12H	19.23	19.79	19.73	20.28	20.84	18.81	19.37	19.32	19.86	20.42
12H	4H	18.08	18.84	18.56	19.32	19.79	17.72	18.48	18.20	18.95	19.42
	6H	18.81	19.45	19.32	19.95	20.44	18.45	19.08	18.96	19.58	20.07
	8H	19.13	19.69	19.63	20.18	20.74	18.75	19.31	19.26	19.80	20.36