

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931420

Luminaire Tested: DFN2DS-TR3F0-080DS935-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931420
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-080DS935-RLL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5848.0 lumens
Efficiency: N/A
Efficacy: 68.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 85.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931420

CATALOG NUMBER: DFN2DS-TR3F0-080DS935-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931420

CATALOG NUMBER: DFN2DS-TR3F0-080DS935-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3543	3543	3543
5°	3557	3499	3518
10°	3530	3442	3412
15°	3489	3340	3243
20°	3433	3194	3034
25°	3375	3029	2830
30°	3296	2858	2570
35°	3218	2674	2341
40°	3139	2482	2076
45°	3047	2267	1836
50°	2953	2050	1601
55°	2857	1817	1375
60°	2745	1571	1142
65°	2618	1320	1039
70°	2466	1087	956
75°	2279	991	893
80°	2012	886	813
85°	1581	698	698

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3047 cd/sqm

TEST NUMBER: P931420

CATALOG NUMBER: DFN2DS-TR3F0-080DS935-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	266.5	4.6
10°-20°	731.6	12.5
20°-30°	1027.1	17.6
30°-40°	1119.6	19.1
40°-50°	1029.1	17.6
50°-60°	808.2	13.8
60°-70°	526.0	9.0
70°-80°	270.8	4.6
80°-90°	69.1	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2025.2	34.6
0°-40°	3144.8	53.8
0°-60°	4982.0	85.2
0°-90°	5848.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5848.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2844	2844	2844	2844	2844	
5°	2844	2831	2797	2820	2813	270
15°	2704	2676	2589	2540	2514	762
25°	2455	2373	2203	2097	2059	1129
35°	2115	1984	1758	1596	1539	1324
45°	1729	1557	1287	1104	1042	1335
55°	1315	1114	836	682	633	1175
65°	888	679	448	360	352	880
75°	473	293	206	188	185	501
85°	111	56	49	49	49	133
90°	0	0	0	0	0	

TEST NUMBER: P931420

CATALOG NUMBER: DFN2DS-TR3F0-080DS935-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2843.5	2843.5	2843.5	2843.5	2843.5
2.5°	2856.3	2843.5	2815.1	2841.0	2835.8
5°	2843.5	2830.7	2797.1	2820.3	2812.6
7.5°	2820.3	2805.0	2768.9	2779.1	2766.2
10°	2789.4	2771.4	2720.1	2712.2	2696.9
12.5°	2751.0	2727.7	2658.1	2642.8	2614.4
15°	2704.5	2676.1	2588.8	2539.9	2514.2
17.5°	2650.4	2609.2	2501.1	2444.6	2403.4
20°	2588.8	2537.2	2408.6	2344.4	2287.6
22.5°	2521.9	2462.6	2313.3	2225.9	2187.4
25°	2455.0	2372.6	2202.7	2097.4	2058.6
27.5°	2375.2	2287.6	2099.8	1978.9	1919.6
30°	2290.4	2192.3	1986.5	1855.4	1785.8
32.5°	2207.9	2089.5	1878.7	1724.1	1659.7
35°	2115.3	1984.0	1757.7	1595.6	1538.7
37.5°	2025.2	1883.6	1644.4	1466.6	1402.5
40°	1930.0	1775.7	1525.9	1343.2	1276.3
42.5°	1832.2	1667.6	1407.6	1217.2	1152.9
45°	1729.3	1556.8	1286.7	1103.8	1042.1
47.5°	1631.6	1448.9	1171.0	988.1	931.6
50°	1523.4	1340.8	1057.7	880.0	826.1
52.5°	1417.8	1224.7	949.5	779.8	730.9
55°	1314.9	1114.2	836.3	682.0	633.1
57.5°	1209.5	1003.6	736.1	591.9	550.7
60°	1101.3	895.5	630.4	499.3	458.1
62.5°	996.0	790.1	540.3	416.9	396.5
65°	887.9	679.2	447.7	360.4	352.4
67.5°	784.9	576.4	360.4	316.4	308.8
70°	676.8	476.2	298.4	272.7	262.4
72.5°	573.9	383.3	249.6	229.1	223.9
75°	473.4	293.3	205.9	187.8	185.4
77.5°	373.2	208.3	162.2	151.8	146.6
80°	280.4	149.4	123.4	113.3	113.3
82.5°	195.5	100.4	84.9	79.7	79.7
85°	110.6	56.5	48.8	48.8	48.8
87.5°	41.2	20.5	20.5	18.1	18.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931420

CATALOG NUMBER: DFN2DS-TR3F0-080DS935-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.63	17.15	15.99	17.47	17.78	11.59	13.11	11.96	13.43	13.74
	3H	17.40	18.76	17.77	19.09	19.45	12.86	14.22	13.23	14.55	14.91
	4H	18.06	19.34	18.46	19.69	20.07	13.36	14.64	13.76	14.99	15.37
	6H	18.55	19.73	18.96	20.10	20.49	13.74	14.92	14.15	15.29	15.68
	8H	18.72	19.84	19.14	20.23	20.63	13.86	14.99	14.29	15.38	15.78
	12H	18.82	19.90	19.25	20.28	20.71	13.94	15.02	14.37	15.40	15.83
4H	2H	15.73	17.01	16.13	17.36	17.74	12.29	13.57	12.69	13.92	14.29
	3H	17.67	18.73	18.08	19.13	19.53	13.73	14.79	14.14	15.19	15.59
	4H	18.42	19.37	18.85	19.79	20.23	14.33	15.28	14.76	15.70	16.14
	6H	19.01	19.84	19.47	20.28	20.74	14.82	15.65	15.27	16.09	16.55
	8H	19.22	20.00	19.69	20.44	20.91	14.98	15.76	15.44	16.20	16.67
	12H	19.38	20.07	19.86	20.55	21.02	15.10	15.79	15.58	16.27	16.74
8H	4H	18.44	19.22	18.90	19.66	20.13	14.68	15.46	15.15	15.90	16.37
	6H	19.08	19.72	19.58	20.21	20.69	15.27	15.91	15.77	16.40	16.88
	8H	19.33	19.91	19.84	20.42	20.90	15.49	16.07	16.00	16.58	17.06
	12H	19.53	20.04	20.04	20.53	21.10	15.67	16.18	16.18	16.67	17.24
12H	4H	18.43	19.12	18.91	19.60	20.07	14.73	15.42	15.21	15.90	16.37
	6H	19.06	19.64	19.57	20.15	20.63	15.33	15.91	15.85	16.42	16.91
	8H	19.34	19.85	19.85	20.35	20.91	15.61	16.12	16.11	16.61	17.17