

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931331

Luminaire Tested: DFN2DS-TR3F0-030DS940-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931331
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-030DS940-FLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2649.3 lumens
Efficiency: N/A
Efficacy: 93.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 28.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931331

CATALOG NUMBER: DFN2DS-TR3F0-030DS940-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931331

CATALOG NUMBER: DFN2DS-TR3F0-030DS940-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1297	1297	1297
5°	1302	1284	1291
10°	1295	1271	1277
15°	1279	1254	1253
20°	1256	1229	1228
25°	1233	1199	1199
30°	1204	1171	1161
35°	1177	1138	1121
40°	1143	1104	1083
45°	1110	1071	1044
50°	1073	1037	1000
55°	1036	996	959
60°	993	948	913
65°	948	900	859
70°	890	843	803
75°	809	776	757
80°	719	696	661
85°	586	559	502

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1110 cd/sqm

TEST NUMBER: P931331

CATALOG NUMBER: DFN2DS-TR3F0-030DS940-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.0	3.7
10°-20°	275.7	10.4
20°-30°	405.2	15.3
30°-40°	470.6	17.8
40°-50°	470.1	17.7
50°-60°	409.9	15.5
60°-70°	303.0	11.4
70°-80°	171.4	6.5
80°-90°	45.3	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	779.0	29.4
0°-40°	1249.6	47.2
0°-60°	2129.6	80.4
0°-90°	2649.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2649.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1041	1041	1041	1041	1041	
5°	1041	1037	1026	1034	1032	99
15°	991	985	972	976	971	279
25°	897	889	872	874	872	413
35°	774	764	748	742	737	483
45°	630	623	608	597	593	486
55°	477	471	459	447	442	426
65°	322	315	305	296	291	318
75°	168	166	161	155	157	180
85°	41	40	39	36	35	48
90°	0	0	0	0	0	

TEST NUMBER: P931331

CATALOG NUMBER: DFN2DS-TR3F0-030DS940-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1041.2	1041.2	1041.2	1041.2	1041.2
2.5°	1047.3	1042.3	1031.2	1041.2	1039.4
5°	1041.2	1037.3	1026.2	1034.3	1032.3
7.5°	1034.3	1028.3	1017.2	1025.4	1023.3
10°	1023.3	1016.3	1004.3	1012.2	1009.3
12.5°	1008.2	1002.3	990.3	995.2	993.2
15°	991.2	985.3	972.2	976.2	971.2
17.5°	970.1	964.3	951.1	956.1	951.1
20°	947.1	941.1	927.1	930.1	926.2
22.5°	924.2	915.2	902.1	902.1	900.0
25°	897.1	889.1	872.1	874.1	872.1
27.5°	867.0	860.0	847.0	844.1	839.1
30°	837.1	829.0	814.0	811.0	807.0
32.5°	805.0	799.1	783.0	776.9	772.9
35°	774.0	764.0	747.9	741.9	736.9
37.5°	738.9	729.9	713.9	706.8	701.8
40°	702.9	694.9	678.8	669.9	665.9
42.5°	667.8	659.8	643.8	633.8	627.8
45°	629.8	622.8	607.7	596.7	592.7
47.5°	592.7	585.8	569.7	558.7	552.7
50°	553.7	548.7	534.7	520.7	515.7
52.5°	515.7	508.6	495.7	484.6	477.6
55°	476.7	470.6	458.6	446.6	441.6
57.5°	437.5	432.5	419.5	407.5	403.5
60°	398.5	394.5	380.5	369.5	366.5
62.5°	360.5	353.4	343.4	333.4	329.4
65°	321.5	315.4	305.4	296.4	291.4
67.5°	281.4	276.3	267.3	260.4	256.4
70°	244.3	240.3	231.3	224.2	220.3
72.5°	206.3	202.2	197.2	190.3	187.3
75°	168.1	166.3	161.2	155.2	157.3
77.5°	134.2	130.1	128.1	125.1	122.2
80°	100.2	99.1	97.0	94.1	92.1
82.5°	68.1	68.1	67.2	63.1	63.1
85°	41.0	40.1	39.1	36.0	35.1
87.5°	18.0	16.1	14.0	11.1	10.0
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931331

CATALOG NUMBER: DFN2DS-TR3F0-030DS940-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.19	13.80	12.55	14.11	14.43	11.74	13.35	12.11	13.67	13.98
	3H	13.94	15.39	14.31	15.72	16.08	13.45	14.90	13.82	15.23	15.59
	4H	14.58	15.95	14.98	16.30	16.68	14.09	15.46	14.49	15.81	16.18
	6H	15.05	16.32	15.46	16.69	17.08	14.55	15.82	14.96	16.19	16.58
	8H	15.20	16.41	15.62	16.80	17.19	14.69	15.90	15.12	16.29	16.69
	12H	15.29	16.45	15.72	16.83	17.26	14.77	15.93	15.20	16.32	16.75
4H	2H	12.75	14.12	13.15	14.46	14.84	12.40	13.76	12.79	14.11	14.49
	3H	14.72	15.87	15.13	16.27	16.67	14.32	15.46	14.73	15.86	16.26
	4H	15.50	16.54	15.93	16.95	17.38	15.08	16.11	15.51	16.53	16.96
	6H	16.10	17.00	16.55	17.44	17.90	15.66	16.57	16.12	17.01	17.47
	8H	16.29	17.13	16.75	17.57	18.04	15.85	16.69	16.31	17.14	17.60
	12H	16.42	17.18	16.90	17.65	18.12	15.97	16.73	16.45	17.20	17.67
8H	4H	15.77	16.62	16.23	17.06	17.53	15.40	16.25	15.86	16.69	17.15
	6H	16.49	17.19	16.98	17.68	18.15	16.11	16.81	16.60	17.30	17.77
	8H	16.75	17.38	17.26	17.88	18.37	16.35	16.99	16.86	17.49	17.98
	12H	16.95	17.50	17.45	17.99	18.56	16.53	17.09	17.04	17.58	18.14
12H	4H	15.80	16.56	16.28	17.03	17.50	15.43	16.19	15.91	16.67	17.14
	6H	16.53	17.16	17.04	17.67	18.16	16.16	16.80	16.67	17.30	17.79
	8H	16.85	17.40	17.35	17.89	18.46	16.47	17.03	16.98	17.52	18.08