

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931367

Luminaire Tested: DFN2DS-TR3F0-050DS940-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931367
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-050DS940-FLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4415.4 lumens
Efficiency: N/A
Efficacy: 89.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931367

CATALOG NUMBER: DFN2DS-TR3F0-050DS940-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931367

CATALOG NUMBER: DFN2DS-TR3F0-050DS940-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2162	2162	2162
5°	2171	2139	2152
10°	2158	2118	2128
15°	2131	2090	2088
20°	2093	2049	2047
25°	2056	1998	1998
30°	2007	1952	1935
35°	1962	1896	1868
40°	1906	1840	1805
45°	1850	1785	1741
50°	1789	1727	1666
55°	1726	1660	1599
60°	1655	1581	1522
65°	1580	1501	1432
70°	1484	1404	1338
75°	1350	1293	1262
80°	1198	1161	1102
85°	977	931	835

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1850 cd/sqm

TEST NUMBER: P931367

CATALOG NUMBER: DFN2DS-TR3F0-050DS940-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.3	3.7
10°-20°	459.6	10.4
20°-30°	675.4	15.3
30°-40°	784.4	17.8
40°-50°	783.4	17.7
50°-60°	683.1	15.5
60°-70°	505.0	11.4
70°-80°	285.7	6.5
80°-90°	75.4	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1298.3	29.4
0°-40°	2082.7	47.2
0°-60°	3549.3	80.4
0°-90°	4415.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4415.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1735	1735	1735	1735	1735	
5°	1735	1729	1710	1724	1721	165
15°	1652	1642	1620	1627	1619	465
25°	1495	1482	1454	1457	1454	688
35°	1290	1273	1247	1236	1228	806
45°	1050	1038	1013	995	988	810
55°	794	784	764	744	736	710
65°	536	526	509	494	486	530
75°	280	277	269	259	262	299
85°	68	67	65	60	58	80
90°	0	0	0	0	0	

TEST NUMBER: P931367

CATALOG NUMBER: DFN2DS-TR3F0-050DS940-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1735.4	1735.4	1735.4	1735.4	1735.4
2.5°	1745.5	1737.2	1718.8	1735.4	1732.3
5°	1735.4	1728.9	1710.4	1723.7	1720.6
7.5°	1723.7	1713.8	1695.4	1708.9	1705.5
10°	1705.5	1693.8	1673.8	1687.0	1682.1
12.5°	1680.3	1670.4	1650.5	1658.8	1655.4
15°	1652.0	1642.1	1620.3	1627.1	1618.7
17.5°	1616.9	1607.0	1585.3	1593.6	1585.3
20°	1578.6	1568.7	1545.3	1550.2	1543.7
22.5°	1540.3	1525.2	1503.5	1503.5	1500.1
25°	1495.2	1481.9	1453.5	1456.7	1453.5
27.5°	1445.0	1433.4	1411.8	1406.8	1398.5
30°	1395.1	1381.7	1356.7	1351.7	1345.0
32.5°	1341.7	1331.8	1305.0	1294.9	1288.2
35°	1289.9	1273.3	1246.6	1236.5	1228.2
37.5°	1231.5	1216.5	1189.7	1178.1	1169.8
40°	1171.6	1158.1	1131.3	1116.4	1109.7
42.5°	1113.1	1099.7	1073.1	1056.2	1046.3
45°	1049.7	1038.0	1012.9	994.7	987.9
47.5°	987.9	976.2	949.5	931.1	921.2
50°	922.8	914.5	891.1	867.7	859.4
52.5°	859.4	847.7	826.1	807.7	796.0
55°	794.4	784.3	764.3	744.3	736.0
57.5°	729.2	720.9	699.1	679.2	672.4
60°	664.1	657.6	634.2	615.7	610.8
62.5°	600.8	589.1	572.4	555.7	549.0
65°	535.7	525.7	509.0	494.0	485.6
67.5°	469.0	460.5	445.6	434.0	427.2
70°	407.2	400.5	385.4	373.7	367.2
72.5°	343.9	337.1	328.8	317.1	312.1
75°	280.3	277.1	268.6	258.7	262.1
77.5°	223.6	216.8	213.5	208.5	203.6
80°	167.0	165.2	161.8	156.9	153.5
82.5°	113.5	113.5	111.9	105.2	105.2
85°	68.3	66.7	65.1	60.0	58.4
87.5°	30.1	26.8	23.4	18.4	16.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931367

CATALOG NUMBER: DFN2DS-TR3F0-050DS940-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.96	15.57	14.33	15.89	16.20	13.52	15.13	13.88	15.44	15.76
	3H	15.71	17.17	16.09	17.49	17.85	15.22	16.68	15.60	17.00	17.36
	4H	16.36	17.73	16.76	18.08	18.45	15.86	17.23	16.26	17.58	17.96
	6H	16.83	18.10	17.24	18.46	18.85	16.33	17.60	16.74	17.96	18.35
	8H	16.97	18.18	17.40	18.57	18.97	16.47	17.68	16.89	18.07	18.47
	12H	17.06	18.22	17.49	18.60	19.03	16.55	17.71	16.98	18.09	18.52
4H	2H	14.52	15.89	14.92	16.24	16.62	14.17	15.54	14.57	15.89	16.26
	3H	16.50	17.64	16.91	18.04	18.44	16.09	17.24	16.50	17.64	18.04
	4H	17.27	18.31	17.71	18.72	19.16	16.85	17.89	17.28	18.30	18.74
	6H	17.87	18.78	18.33	19.22	19.67	17.44	18.34	17.89	18.78	19.24
	8H	18.06	18.91	18.52	19.35	19.81	17.62	18.47	18.08	18.91	19.38
	12H	18.19	18.95	18.67	19.43	19.90	17.74	18.50	18.22	18.98	19.45
8H	4H	17.55	18.39	18.01	18.84	19.30	17.17	18.02	17.63	18.46	18.93
	6H	18.26	18.96	18.76	19.45	19.93	17.88	18.58	18.37	19.07	19.55
	8H	18.52	19.15	19.03	19.66	20.14	18.13	18.76	18.64	19.27	19.75
	12H	18.72	19.28	19.23	19.77	20.33	18.31	18.87	18.82	19.36	19.92
12H	4H	17.57	18.33	18.05	18.81	19.28	17.21	17.97	17.69	18.44	18.91
	6H	18.31	18.94	18.82	19.45	19.93	17.94	18.57	18.45	19.08	19.56
	8H	18.62	19.18	19.13	19.67	20.23	18.24	18.80	18.75	19.29	19.85