

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930868

Luminaire Tested: DFN2DS-SQ2F0-070DS830-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930868
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ2F0-070DS830-RLL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5604.9 lumens
Efficiency: N/A
Efficacy: 78.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.21' x L: 2.21' x H: 0')
CIE Type: Direct

Input Watts (W): 71.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930868

CATALOG NUMBER: DFN2DS-SQ2F0-070DS830-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930868

CATALOG NUMBER: DFN2DS-SQ2F0-070DS830-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5993	5993	5993
5°	6016	5917	5950
10°	5969	5821	5771
15°	5901	5648	5486
20°	5806	5402	5130
25°	5709	5122	4787
30°	5573	4834	4346
35°	5442	4522	3959
40°	5309	4198	3511
45°	5154	3835	3106
50°	4995	3468	2709
55°	4831	3073	2326
60°	4642	2657	1931
65°	4427	2233	1758
70°	4171	1839	1616
75°	3855	1676	1510
80°	3404	1498	1375
85°	2674	1181	1181

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5154 cd/sqm

TEST NUMBER: P930868

CATALOG NUMBER: DFN2DS-SQ2F0-070DS830-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	255.4	4.6
10°-20°	701.2	12.5
20°-30°	984.4	17.6
30°-40°	1073.1	19.1
40°-50°	986.3	17.6
50°-60°	774.6	13.8
60°-70°	504.2	9.0
70°-80°	259.5	4.6
80°-90°	66.2	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1941.0	34.6
0°-40°	3014.1	53.8
0°-60°	4775.0	85.2
0°-90°	5604.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5604.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2725	2725	2725	2725	2725	
5°	2725	2713	2681	2703	2696	258
15°	2592	2565	2481	2434	2410	730
25°	2353	2274	2111	2010	1973	1082
35°	2027	1902	1685	1529	1475	1269
45°	1657	1492	1233	1058	999	1280
55°	1260	1068	802	654	607	1126
65°	851	651	429	345	338	844
75°	454	281	197	180	178	480
85°	106	54	47	47	47	127
90°	0	0	0	0	0	

TEST NUMBER: P930868

CATALOG NUMBER: DFN2DS-SQ2F0-070DS830-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2725.3	2725.3	2725.3	2725.3	2725.3
2.5°	2737.5	2725.3	2698.1	2722.9	2718.0
5°	2725.3	2713.0	2680.8	2703.1	2695.7
7.5°	2703.1	2688.4	2653.9	2663.5	2651.3
10°	2673.5	2656.3	2607.0	2599.4	2584.8
12.5°	2636.6	2614.3	2547.6	2532.9	2505.7
15°	2592.1	2564.9	2481.1	2434.3	2409.7
17.5°	2540.3	2500.8	2397.2	2342.9	2303.5
20°	2481.1	2431.7	2308.5	2247.0	2192.5
22.5°	2417.1	2360.3	2217.1	2133.3	2096.5
25°	2352.9	2273.9	2111.1	2010.1	1973.0
27.5°	2276.5	2192.5	2012.5	1896.6	1839.8
30°	2195.1	2101.2	1903.9	1778.3	1711.6
32.5°	2116.1	2002.6	1800.5	1652.5	1590.7
35°	2027.4	1901.5	1684.7	1529.2	1474.8
37.5°	1941.1	1805.2	1576.1	1405.7	1344.2
40°	1849.7	1701.9	1462.5	1287.4	1223.3
42.5°	1756.1	1598.3	1349.1	1166.5	1105.1
45°	1657.4	1492.0	1233.3	1058.0	998.8
47.5°	1563.7	1388.7	1122.3	947.0	892.8
50°	1460.1	1285.1	1013.7	843.4	791.8
52.5°	1358.8	1173.8	910.1	747.3	700.5
55°	1260.2	1067.9	801.5	653.7	606.8
57.5°	1159.2	961.9	705.5	567.3	527.8
60°	1055.6	858.3	604.2	478.6	439.1
62.5°	954.5	757.3	517.8	399.6	379.9
65°	850.9	651.0	429.2	345.4	337.8
67.5°	752.3	552.4	345.4	303.2	296.0
70°	648.7	456.3	286.0	261.4	251.4
72.5°	550.0	367.4	239.2	219.6	214.6
75°	453.8	281.0	197.3	180.0	177.7
77.5°	357.7	199.6	155.4	145.4	140.5
80°	268.8	143.1	118.3	108.6	108.6
82.5°	187.4	96.3	81.4	76.4	76.4
85°	106.0	54.2	46.8	46.8	46.8
87.5°	39.5	19.6	19.6	17.2	17.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930868

CATALOG NUMBER: DFN2DS-SQ2F0-070DS830-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.46	18.98	17.82	19.29	19.61	13.42	14.94	13.78	15.25	15.57
	3H	19.22	20.59	19.60	20.91	21.28	14.68	16.05	15.06	16.37	16.74
	4H	19.89	21.17	20.29	21.52	21.90	15.18	16.46	15.58	16.81	17.19
	6H	20.38	21.56	20.79	21.93	22.32	15.56	16.75	15.98	17.11	17.51
	8H	20.54	21.67	20.97	22.06	22.46	15.69	16.82	16.11	17.20	17.61
	12H	20.64	21.72	21.08	22.11	22.53	15.77	16.85	16.20	17.23	17.66
4H	2H	17.56	18.84	17.96	19.19	19.57	14.11	15.39	14.51	15.74	16.12
	3H	19.49	20.56	19.90	20.96	21.36	15.55	16.62	15.97	17.02	17.42
	4H	20.24	21.20	20.68	21.61	22.05	16.15	17.11	16.59	17.53	17.96
	6H	20.83	21.67	21.29	22.11	22.57	16.64	17.47	17.10	17.92	18.38
	8H	21.05	21.83	21.51	22.27	22.74	16.80	17.58	17.27	18.03	18.49
	12H	21.20	21.90	21.68	22.38	22.85	16.92	17.62	17.40	18.09	18.57
8H	4H	20.27	21.04	20.73	21.49	21.96	16.51	17.29	16.97	17.73	18.20
	6H	20.90	21.55	21.40	22.04	22.52	17.09	17.74	17.59	18.23	18.71
	8H	21.15	21.73	21.67	22.24	22.73	17.32	17.89	17.83	18.40	18.89
	12H	21.36	21.87	21.87	22.36	22.93	17.49	18.00	18.00	18.50	19.06
12H	4H	20.25	20.95	20.73	21.42	21.89	16.55	17.25	17.03	17.72	18.20
	6H	20.88	21.46	21.40	21.97	22.46	17.16	17.74	17.67	18.25	18.73
	8H	21.17	21.68	21.68	22.17	22.74	17.43	17.94	17.94	18.43	19.00