

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930885

Luminaire Tested: DFN2DS-SQ2F0-080DS830-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930885
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ2F0-080DS830-FLL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7460.7 lumens
Efficiency: N/A
Efficacy: 90.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.21' x L: 2.21' x H: 0')
CIE Type: Direct

Input Watts (W): 82.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930885

CATALOG NUMBER: DFN2DS-SQ2F0-080DS830-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930885

CATALOG NUMBER: DFN2DS-SQ2F0-080DS830-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6448	6448	6448
5°	6472	6380	6417
10°	6435	6315	6346
15°	6355	6232	6227
20°	6242	6110	6103
25°	6129	5959	5959
30°	5986	5821	5771
35°	5851	5654	5571
40°	5682	5487	5382
45°	5516	5322	5191
50°	5334	5150	4967
55°	5146	4951	4767
60°	4935	4712	4539
65°	4710	4475	4270
70°	4423	4187	3989
75°	4023	3856	3761
80°	3572	3463	3283
85°	2914	2778	2490

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5516 cd/sqm

TEST NUMBER: P930885

CATALOG NUMBER: DFN2DS-SQ2F0-080DS830-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.0	3.7
10°-20°	776.5	10.4
20°-30°	1141.2	15.3
30°-40°	1325.4	17.8
40°-50°	1323.8	17.7
50°-60°	1154.3	15.5
60°-70°	853.3	11.4
70°-80°	482.8	6.5
80°-90°	127.4	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2193.7	29.4
0°-40°	3519.1	47.2
0°-60°	5997.2	80.4
0°-90°	7460.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7460.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2932	2932	2932	2932	2932	
5°	2932	2921	2890	2913	2907	278
15°	2791	2775	2738	2749	2735	786
25°	2526	2504	2456	2461	2456	1163
35°	2180	2152	2106	2089	2075	1361
45°	1774	1754	1711	1681	1669	1369
55°	1342	1325	1292	1258	1244	1200
65°	905	888	860	835	821	895
75°	474	468	454	437	443	505
85°	116	113	110	102	99	136
90°	0	0	0	0	0	

TEST NUMBER: P930885

CATALOG NUMBER: DFN2DS-SQ2F0-080DS830-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2932.3	2932.3	2932.3	2932.3	2932.3
2.5°	2949.3	2935.3	2904.2	2932.3	2926.9
5°	2932.3	2921.2	2890.2	2912.6	2907.2
7.5°	2912.6	2895.8	2864.7	2887.4	2881.8
10°	2881.8	2862.0	2828.2	2850.6	2842.3
12.5°	2839.3	2822.5	2788.7	2802.7	2797.1
15°	2791.4	2774.7	2737.8	2749.2	2735.2
17.5°	2732.2	2715.4	2678.6	2692.7	2678.6
20°	2667.3	2650.5	2611.0	2619.4	2608.3
22.5°	2602.7	2577.2	2540.4	2540.4	2534.7
25°	2526.3	2503.9	2456.1	2461.4	2456.1
27.5°	2441.7	2422.0	2385.4	2377.0	2363.0
30°	2357.4	2334.6	2292.5	2284.1	2272.7
32.5°	2267.0	2250.2	2205.0	2188.0	2176.7
35°	2179.6	2151.5	2106.3	2089.3	2075.2
37.5°	2080.9	2055.4	2010.3	1990.5	1976.5
40°	1979.5	1956.7	1911.6	1886.4	1875.1
42.5°	1880.8	1858.0	1813.2	1784.7	1768.0
45°	1773.7	1753.9	1711.4	1680.6	1669.3
47.5°	1669.3	1649.5	1604.3	1573.2	1556.5
50°	1559.2	1545.2	1505.6	1466.1	1452.1
52.5°	1452.1	1432.3	1395.9	1364.8	1345.0
55°	1342.3	1325.2	1291.5	1257.7	1243.5
57.5°	1232.2	1218.2	1181.4	1147.5	1136.1
60°	1122.1	1111.1	1071.5	1040.4	1032.1
62.5°	1015.0	995.3	967.2	939.1	927.7
65°	905.3	888.2	860.0	834.6	820.6
67.5°	792.4	778.1	752.9	733.3	721.9
70°	688.0	676.6	651.3	631.5	620.4
72.5°	580.9	569.6	555.5	535.8	527.4
75°	473.5	468.2	453.9	437.1	442.7
77.5°	377.8	366.4	360.8	352.4	344.0
80°	282.1	279.1	273.5	265.1	259.3
82.5°	191.8	191.8	189.1	177.7	177.7
85°	115.5	112.8	110.1	101.5	98.7
87.5°	50.9	45.2	39.5	31.1	28.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930885

CATALOG NUMBER: DFN2DS-SQ2F0-080DS830-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.76	19.37	18.12	19.68	20.00	17.31	18.92	17.68	19.24	19.55
	3H	19.51	20.96	19.88	21.29	21.65	19.02	20.47	19.39	20.80	21.16
	4H	20.15	21.52	20.55	21.87	22.25	19.66	21.03	20.06	21.38	21.75
	6H	20.62	21.89	21.03	22.26	22.65	20.12	21.39	20.53	21.75	22.15
	8H	20.77	21.98	21.19	22.37	22.77	20.26	21.47	20.69	21.86	22.26
	12H	20.86	22.02	21.29	22.40	22.83	20.34	21.50	20.77	21.89	22.31
4H	2H	18.32	19.69	18.72	20.04	20.41	17.97	19.33	18.36	19.68	20.06
	3H	20.29	21.44	20.70	21.84	22.24	19.89	21.03	20.30	21.43	21.83
	4H	21.07	22.11	21.50	22.52	22.96	20.65	21.68	21.08	22.10	22.53
	6H	21.67	22.57	22.12	23.01	23.47	21.23	22.14	21.69	22.58	23.04
	8H	21.86	22.70	22.32	23.14	23.61	21.42	22.26	21.88	22.71	23.17
	12H	21.99	22.75	22.47	23.22	23.69	21.54	22.30	22.02	22.77	23.24
8H	4H	21.34	22.19	21.80	22.63	23.10	20.97	21.82	21.43	22.26	22.72
	6H	22.06	22.76	22.55	23.25	23.72	21.68	22.38	22.17	22.87	23.34
	8H	22.32	22.95	22.83	23.45	23.94	21.93	22.56	22.43	23.06	23.55
	12H	22.52	23.07	23.02	23.57	24.13	22.10	22.66	22.61	23.15	23.71
12H	4H	21.37	22.13	21.85	22.60	23.07	21.00	21.76	21.48	22.24	22.71
	6H	22.10	22.73	22.61	23.24	23.73	21.73	22.37	22.24	22.87	23.36
	8H	22.42	22.97	22.92	23.47	24.03	22.04	22.60	22.55	23.09	23.65