

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930852

Luminaire Tested: DFN2DS-SQ2F0-060DS835-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930852
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ2F0-060DS835-RLL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5100.0 lumens
Efficiency: N/A
Efficacy: 86.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.21' x L: 2.21' x H: 0')
CIE Type: Direct

Input Watts (W): 58.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930852

CATALOG NUMBER: DFN2DS-SQ2F0-060DS835-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930852

CATALOG NUMBER: DFN2DS-SQ2F0-060DS835-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5453	5453	5453
5°	5474	5384	5414
10°	5432	5297	5251
15°	5369	5139	4991
20°	5283	4915	4668
25°	5195	4661	4356
30°	5072	4399	3954
35°	4952	4115	3602
40°	4831	3820	3195
45°	4690	3490	2826
50°	4545	3155	2465
55°	4396	2796	2117
60°	4224	2418	1757
65°	4029	2032	1599
70°	3794	1673	1471
75°	3508	1525	1374
80°	3096	1363	1251
85°	2432	1075	1075

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4690 cd/sqm

TEST NUMBER: P930852

CATALOG NUMBER: DFN2DS-SQ2F0-060DS835-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	232.4	4.6
10°-20°	638.0	12.5
20°-30°	895.7	17.6
30°-40°	976.4	19.1
40°-50°	897.4	17.6
50°-60°	704.8	13.8
60°-70°	458.8	9.0
70°-80°	236.1	4.6
80°-90°	60.3	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1766.2	34.6
0°-40°	2742.6	53.8
0°-60°	4344.8	85.2
0°-90°	5100.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5100.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2480	2480	2480	2480	2480	
5°	2480	2469	2439	2460	2453	235
15°	2359	2334	2258	2215	2193	665
25°	2141	2069	1921	1829	1795	985
35°	1845	1730	1533	1391	1342	1155
45°	1508	1358	1122	963	909	1165
55°	1147	972	729	595	552	1025
65°	774	592	390	314	307	768
75°	413	256	180	164	162	437
85°	96	49	43	43	43	116
90°	0	0	0	0	0	

TEST NUMBER: P930852

CATALOG NUMBER: DFN2DS-SQ2F0-060DS835-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2479.8	2479.8	2479.8	2479.8	2479.8
2.5°	2491.0	2479.8	2455.0	2477.6	2473.1
5°	2479.8	2468.6	2439.3	2459.6	2452.9
7.5°	2459.6	2446.2	2414.8	2423.6	2412.4
10°	2432.6	2416.9	2372.2	2365.3	2351.9
12.5°	2399.1	2378.8	2318.1	2304.8	2280.0
15°	2358.6	2333.8	2257.6	2215.0	2192.6
17.5°	2311.5	2275.5	2181.2	2131.9	2096.0
20°	2257.6	2212.6	2100.5	2044.5	1995.0
22.5°	2199.3	2147.6	2017.4	1941.2	1907.6
25°	2141.0	2069.1	1921.0	1829.1	1795.3
27.5°	2071.5	1995.0	1831.2	1725.7	1674.1
30°	1997.4	1911.9	1732.4	1618.1	1557.4
32.5°	1925.5	1822.2	1638.4	1503.6	1447.4
35°	1844.8	1730.3	1532.9	1391.4	1341.9
37.5°	1766.2	1642.6	1434.1	1279.1	1223.1
40°	1683.1	1548.6	1330.7	1171.4	1113.1
42.5°	1597.9	1454.3	1227.6	1061.4	1005.5
45°	1508.1	1357.6	1122.2	962.6	908.8
47.5°	1422.9	1263.6	1021.2	861.7	812.4
50°	1328.6	1169.3	922.4	767.4	720.5
52.5°	1236.4	1068.1	828.1	680.0	637.4
55°	1146.7	971.7	729.3	594.8	552.1
57.5°	1054.8	875.2	641.9	516.2	480.2
60°	960.5	781.0	549.8	435.5	399.5
62.5°	868.6	689.1	471.2	363.6	345.7
65°	774.3	592.4	390.5	314.3	307.4
67.5°	684.5	502.6	314.3	276.0	269.3
70°	590.2	415.2	260.2	237.9	228.8
72.5°	500.5	334.3	217.6	199.8	195.2
75°	412.9	255.7	179.5	163.8	161.7
77.5°	325.5	181.7	141.4	132.4	127.9
80°	244.5	130.2	107.6	98.8	98.8
82.5°	170.5	87.6	74.0	69.5	69.5
85°	96.4	49.3	42.6	42.6	42.6
87.5°	36.0	17.9	17.9	15.7	15.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930852

CATALOG NUMBER: DFN2DS-SQ2F0-060DS835-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.13	18.65	17.49	18.96	19.28	13.09	14.61	13.45	14.92	15.24
	3H	18.89	20.26	19.27	20.59	20.95	14.35	15.72	14.73	16.05	16.41
	4H	19.56	20.84	19.96	21.19	21.57	14.86	16.14	15.26	16.48	16.86
	6H	20.05	21.23	20.46	21.60	21.99	15.24	16.42	15.65	16.79	17.18
	8H	20.21	21.34	20.64	21.73	22.13	15.36	16.49	15.79	16.88	17.28
	12H	20.32	21.39	20.75	21.78	22.21	15.44	16.52	15.87	16.90	17.33
4H	2H	17.23	18.51	17.63	18.86	19.24	13.78	15.06	14.18	15.41	15.79
	3H	19.16	20.23	19.58	20.63	21.03	15.23	16.29	15.64	16.69	17.09
	4H	19.91	20.87	20.35	21.29	21.72	15.83	16.78	16.26	17.20	17.64
	6H	20.51	21.34	20.96	21.78	22.24	16.31	17.15	16.77	17.59	18.05
	8H	20.72	21.50	21.18	21.94	22.41	16.48	17.25	16.94	17.70	18.17
	12H	20.87	21.57	21.36	22.05	22.52	16.59	17.29	17.08	17.77	18.24
8H	4H	19.94	20.72	20.40	21.16	21.63	16.18	16.96	16.64	17.40	17.87
	6H	20.58	21.22	21.07	21.71	22.19	16.77	17.41	17.26	17.90	18.38
	8H	20.83	21.40	21.34	21.91	22.40	16.99	17.56	17.50	18.07	18.56
	12H	21.03	21.54	21.54	22.03	22.60	17.17	17.68	17.68	18.17	18.73
12H	4H	19.92	20.62	20.40	21.10	21.57	16.22	16.92	16.71	17.40	17.87
	6H	20.56	21.13	21.07	21.64	22.13	16.83	17.41	17.34	17.92	18.41
	8H	20.84	21.35	21.35	21.84	22.41	17.10	17.61	17.61	18.11	18.67