

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931369

Luminaire Tested: DFN2DS-TR3F0-050DS950-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931369
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-050DS950-FLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4677.7 lumens
Efficiency: N/A
Efficacy: 94.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931369

CATALOG NUMBER: DFN2DS-TR3F0-050DS950-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931369

CATALOG NUMBER: DFN2DS-TR3F0-050DS950-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2291	2291	2291
5°	2300	2267	2280
10°	2286	2244	2255
15°	2258	2215	2212
20°	2218	2171	2169
25°	2178	2117	2117
30°	2127	2068	2050
35°	2079	2009	1979
40°	2019	1950	1912
45°	1960	1891	1844
50°	1895	1830	1765
55°	1828	1759	1694
60°	1754	1675	1613
65°	1674	1590	1517
70°	1572	1488	1418
75°	1429	1370	1337
80°	1269	1230	1167
85°	1035	987	885

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1960 cd/sqm

TEST NUMBER: P931369

CATALOG NUMBER: DFN2DS-TR3F0-050DS950-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.0	3.7
10°-20°	486.9	10.4
20°-30°	715.5	15.3
30°-40°	831.0	17.8
40°-50°	830.0	17.7
50°-60°	723.7	15.5
60°-70°	535.0	11.4
70°-80°	302.7	6.5
80°-90°	79.9	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1375.4	29.4
0°-40°	2206.5	47.2
0°-60°	3760.2	80.4
0°-90°	4677.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4677.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1838	1838	1838	1838	1838	
5°	1838	1832	1812	1826	1823	175
15°	1750	1740	1717	1724	1715	493
25°	1584	1570	1540	1543	1540	729
35°	1367	1349	1321	1310	1301	853
45°	1112	1100	1073	1054	1047	858
55°	842	831	810	788	780	752
65°	568	557	539	523	514	561
75°	297	294	284	274	278	317
85°	72	71	69	64	62	85
90°	0	0	0	0	0	

TEST NUMBER: P931369

CATALOG NUMBER: DFN2DS-TR3F0-050DS950-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1838.5	1838.5	1838.5	1838.5	1838.5
2.5°	1849.2	1840.4	1820.9	1838.5	1835.2
5°	1838.5	1831.6	1812.0	1826.1	1822.8
7.5°	1826.1	1815.6	1796.2	1810.4	1806.8
10°	1806.8	1794.5	1773.3	1787.3	1782.1
12.5°	1780.2	1769.7	1748.5	1757.3	1753.7
15°	1750.1	1739.7	1716.6	1723.8	1714.9
17.5°	1713.0	1702.5	1679.5	1688.2	1679.5
20°	1672.4	1661.9	1637.1	1642.3	1635.4
22.5°	1631.8	1615.9	1592.8	1592.8	1589.2
25°	1584.0	1569.9	1539.9	1543.3	1539.9
27.5°	1530.9	1518.5	1495.7	1490.4	1481.6
30°	1478.0	1463.8	1437.3	1432.1	1425.0
32.5°	1421.4	1410.9	1382.5	1371.9	1364.8
35°	1366.6	1349.0	1320.6	1310.0	1301.2
37.5°	1304.7	1288.8	1260.4	1248.1	1239.3
40°	1241.2	1226.9	1198.5	1182.8	1175.7
42.5°	1179.3	1165.0	1136.8	1119.0	1108.5
45°	1112.1	1099.7	1073.0	1053.8	1046.6
47.5°	1046.6	1034.2	1006.0	986.4	975.9
50°	977.6	968.8	944.1	919.3	910.4
52.5°	910.4	898.0	875.2	855.7	843.3
55°	841.6	830.9	809.7	788.5	779.7
57.5°	772.5	763.7	740.7	719.5	712.3
60°	703.6	696.7	671.9	652.3	647.1
62.5°	636.5	624.1	606.4	588.7	581.6
65°	567.6	556.9	539.2	523.3	514.5
67.5°	496.9	487.9	472.1	459.7	452.6
70°	431.4	424.3	408.3	396.0	389.1
72.5°	364.3	357.1	348.3	335.9	330.7
75°	296.9	293.5	284.5	274.0	277.6
77.5°	236.9	229.7	226.2	220.9	215.7
80°	176.9	175.0	171.4	166.2	162.6
82.5°	120.2	120.2	118.5	111.4	111.4
85°	72.4	70.7	69.0	63.6	61.9
87.5°	31.8	28.4	24.8	19.5	17.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931369

CATALOG NUMBER: DFN2DS-TR3F0-050DS950-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.16	15.77	14.53	16.09	16.40	13.72	15.33	14.08	15.64	15.96
	3H	15.91	17.37	16.29	17.69	18.05	15.42	16.88	15.80	17.20	17.56
	4H	16.56	17.93	16.96	18.28	18.65	16.06	17.43	16.46	17.78	18.16
	6H	17.03	18.30	17.44	18.66	19.05	16.53	17.80	16.94	18.16	18.55
	8H	17.17	18.38	17.60	18.77	19.17	16.67	17.88	17.09	18.27	18.67
	12H	17.26	18.42	17.69	18.80	19.23	16.75	17.91	17.18	18.29	18.72
4H	2H	14.72	16.09	15.12	16.44	16.82	14.37	15.74	14.77	16.09	16.46
	3H	16.70	17.84	17.11	18.24	18.64	16.29	17.44	16.70	17.84	18.24
	4H	17.47	18.51	17.91	18.92	19.36	17.05	18.09	17.48	18.50	18.94
	6H	18.07	18.98	18.53	19.42	19.87	17.64	18.54	18.09	18.98	19.44
	8H	18.26	19.11	18.72	19.55	20.01	17.82	18.67	18.28	19.11	19.58
	12H	18.39	19.15	18.87	19.63	20.10	17.94	18.70	18.42	19.18	19.65
8H	4H	17.75	18.59	18.21	19.04	19.50	17.37	18.22	17.83	18.66	19.13
	6H	18.46	19.17	18.96	19.65	20.13	18.08	18.78	18.57	19.27	19.75
	8H	18.72	19.35	19.23	19.86	20.34	18.33	18.96	18.84	19.47	19.95
	12H	18.92	19.48	19.43	19.97	20.53	18.51	19.07	19.02	19.56	20.12
12H	4H	17.77	18.53	18.25	19.01	19.48	17.41	18.17	17.89	18.65	19.11
	6H	18.51	19.14	19.02	19.65	20.13	18.14	18.77	18.65	19.28	19.76
	8H	18.82	19.38	19.33	19.87	20.43	18.44	19.00	18.95	19.49	20.05