

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931406

Luminaire Tested: DFN2DS-TR3F0-070DS950-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931406
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-070DS950-RLL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5622.7 lumens
Efficiency: N/A
Efficacy: 75.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 74.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931406

CATALOG NUMBER: DFN2DS-TR3F0-070DS950-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931406

CATALOG NUMBER: DFN2DS-TR3F0-070DS950-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3407	3407	3407
5°	3420	3364	3383
10°	3394	3309	3281
15°	3355	3211	3119
20°	3301	3071	2917
25°	3245	2912	2721
30°	3169	2748	2471
35°	3094	2571	2251
40°	3018	2386	1996
45°	2930	2180	1766
50°	2840	1971	1540
55°	2746	1747	1323
60°	2639	1511	1098
65°	2517	1269	999
70°	2371	1045	919
75°	2192	953	858
80°	1935	852	782
85°	1520	672	672

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2930 cd/sqm

TEST NUMBER: P931406

CATALOG NUMBER: DFN2DS-TR3F0-070DS950-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	256.2	4.6
10°-20°	703.4	12.5
20°-30°	987.6	17.6
30°-40°	1076.5	19.1
40°-50°	989.4	17.6
50°-60°	777.0	13.8
60°-70°	505.8	9.0
70°-80°	260.3	4.6
80°-90°	66.5	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1947.2	34.6
0°-40°	3023.7	53.8
0°-60°	4790.2	85.2
0°-90°	5622.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5622.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2734	2734	2734	2734	2734	
5°	2734	2722	2689	2712	2704	259
15°	2600	2573	2489	2442	2417	733
25°	2360	2281	2118	2016	1979	1086
35°	2034	1908	1690	1534	1480	1273
45°	1663	1497	1237	1061	1002	1284
55°	1264	1071	804	656	609	1130
65°	854	653	430	346	339	846
75°	455	282	198	181	178	481
85°	106	54	47	47	47	127
90°	0	0	0	0	0	

TEST NUMBER: P931406

CATALOG NUMBER: DFN2DS-TR3F0-070DS950-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2734.0	2734.0	2734.0	2734.0	2734.0
2.5°	2746.3	2734.0	2706.7	2731.6	2726.6
5°	2734.0	2721.6	2689.4	2711.7	2704.3
7.5°	2711.7	2696.9	2662.3	2672.0	2659.7
10°	2682.0	2664.7	2615.3	2607.7	2593.0
12.5°	2645.0	2622.7	2555.8	2541.0	2513.7
15°	2600.4	2573.0	2489.0	2442.1	2417.4
17.5°	2548.4	2508.8	2404.8	2350.4	2310.8
20°	2489.0	2439.4	2315.8	2254.1	2199.5
22.5°	2424.8	2367.8	2224.2	2140.1	2103.2
25°	2360.4	2281.1	2117.8	2016.5	1979.3
27.5°	2283.8	2199.5	2018.9	1902.7	1845.7
30°	2202.1	2107.9	1909.9	1784.0	1717.1
32.5°	2122.8	2009.0	1806.3	1657.7	1595.7
35°	2033.8	1907.6	1690.0	1534.1	1479.5
37.5°	1947.3	1811.0	1581.1	1410.1	1348.5
40°	1855.6	1707.3	1467.1	1291.5	1227.2
42.5°	1761.7	1603.4	1353.4	1170.2	1108.6
45°	1662.7	1496.8	1237.2	1061.3	1002.0
47.5°	1568.7	1393.1	1125.9	950.0	895.7
50°	1464.8	1289.2	1016.9	846.1	794.4
52.5°	1363.2	1177.6	913.0	749.7	702.7
55°	1264.2	1071.3	804.0	655.7	608.8
57.5°	1162.9	964.9	707.7	569.1	529.5
60°	1059.0	861.0	606.1	480.2	440.5
62.5°	957.6	759.7	519.5	400.9	381.1
65°	853.6	653.1	430.5	346.5	338.9
67.5°	754.7	554.1	346.5	304.2	296.9
70°	650.7	457.8	286.9	262.2	252.2
72.5°	551.8	368.5	239.9	220.3	215.3
75°	455.2	281.9	197.9	180.6	178.2
77.5°	358.8	200.2	155.9	145.9	141.0
80°	269.6	143.5	118.7	109.0	109.0
82.5°	188.0	96.6	81.6	76.6	76.6
85°	106.3	54.3	47.0	47.0	47.0
87.5°	39.6	19.7	19.7	17.3	17.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931406

CATALOG NUMBER: DFN2DS-TR3F0-070DS950-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.49	17.01	15.86	17.33	17.64	11.45	12.98	11.82	13.29	13.60
	3H	17.26	18.62	17.64	18.95	19.31	12.72	14.08	13.10	14.41	14.77
	4H	17.92	19.21	18.32	19.55	19.93	13.22	14.50	13.62	14.85	15.23
	6H	18.41	19.60	18.83	19.96	20.36	13.60	14.78	14.01	15.15	15.54
	8H	18.58	19.71	19.01	20.10	20.50	13.73	14.85	14.15	15.24	15.64
	12H	18.68	19.76	19.11	20.14	20.57	13.81	14.89	14.24	15.27	15.70
4H	2H	15.60	16.88	16.00	17.23	17.60	12.15	13.43	12.55	13.78	14.16
	3H	17.53	18.59	17.94	18.99	19.39	13.59	14.66	14.00	15.06	15.46
	4H	18.28	19.24	18.71	19.65	20.09	14.19	15.15	14.62	15.56	16.00
	6H	18.87	19.70	19.33	20.15	20.61	14.68	15.51	15.14	15.96	16.41
	8H	19.09	19.86	19.55	20.31	20.77	14.84	15.62	15.31	16.06	16.53
	12H	19.24	19.93	19.72	20.41	20.88	14.96	15.65	15.44	16.13	16.60
8H	4H	18.30	19.08	18.77	19.53	19.99	14.55	15.32	15.01	15.77	16.23
	6H	18.94	19.58	19.44	20.08	20.55	15.13	15.78	15.63	16.27	16.74
	8H	19.19	19.77	19.71	20.28	20.77	15.35	15.93	15.87	16.44	16.93
	12H	19.40	19.91	19.91	20.40	20.96	15.53	16.04	16.04	16.53	17.10
12H	4H	18.29	18.98	18.77	19.46	19.93	14.59	15.28	15.07	15.76	16.23
	6H	18.92	19.50	19.44	20.01	20.50	15.20	15.77	15.71	16.28	16.77
	8H	19.21	19.72	19.72	20.21	20.77	15.47	15.98	15.98	16.47	17.04