

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930835

Luminaire Tested: DFN2DS-SQ2F0-050DS840-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930835
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ2F0-050DS840-FLL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4955.0 lumens
Efficiency: N/A
Efficacy: 103.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.21' x L: 2.21' x H: 0')
CIE Type: Direct

Input Watts (W): 47.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930835

CATALOG NUMBER: DFN2DS-SQ2F0-050DS840-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930835

CATALOG NUMBER: DFN2DS-SQ2F0-050DS840-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90	88	86	84
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80	76	73	71
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63	58	54	51
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57	51	47	45
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52	46	41	39
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47	41	37	35
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44	38	33	31
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40	34	30	28
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37	32	27	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4282	4282	4282
5°	4298	4237	4262
10°	4273	4194	4215
15°	4220	4139	4135
20°	4145	4058	4054
25°	4071	3957	3957
30°	3975	3866	3832
35°	3886	3755	3700
40°	3774	3644	3575
45°	3663	3534	3447
50°	3542	3421	3299
55°	3418	3288	3166
60°	3277	3130	3015
65°	3128	2972	2835
70°	2938	2781	2649
75°	2672	2561	2499
80°	2373	2300	2182
85°	1935	1844	1655

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3663 cd/sqm

TEST NUMBER: P930835

CATALOG NUMBER: DFN2DS-SQ2F0-050DS840-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.3	3.7
10°-20°	515.7	10.4
20°-30°	757.9	15.3
30°-40°	880.3	17.8
40°-50°	879.2	17.7
50°-60°	766.6	15.5
60°-70°	566.7	11.4
70°-80°	320.6	6.5
80°-90°	84.6	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1456.9	29.4
0°-40°	2337.2	47.2
0°-60°	3983.0	80.4
0°-90°	4955.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4955.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1947	1947	1947	1947	1947	
5°	1947	1940	1919	1934	1931	185
15°	1854	1843	1818	1826	1816	522
25°	1678	1663	1631	1635	1631	772
35°	1448	1429	1399	1388	1378	904
45°	1178	1165	1137	1116	1109	909
55°	892	880	858	835	826	797
65°	601	590	571	554	545	594
75°	314	311	301	290	294	336
85°	77	75	73	67	66	90
90°	0	0	0	0	0	

TEST NUMBER: P930835

CATALOG NUMBER: DFN2DS-SQ2F0-050DS840-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1947.4	1947.4	1947.4	1947.4	1947.4
2.5°	1958.8	1949.4	1928.8	1947.4	1943.9
5°	1947.4	1940.1	1919.4	1934.3	1930.8
7.5°	1934.3	1923.2	1902.6	1917.7	1913.9
10°	1913.9	1900.8	1878.4	1893.2	1887.7
12.5°	1885.7	1874.6	1852.2	1861.5	1857.7
15°	1853.9	1842.7	1818.3	1825.9	1816.5
17.5°	1814.5	1803.4	1779.0	1788.3	1779.0
20°	1771.5	1760.4	1734.1	1739.6	1732.3
22.5°	1728.5	1711.6	1687.2	1687.2	1683.4
25°	1677.9	1663.0	1631.1	1634.7	1631.1
27.5°	1621.6	1608.5	1584.3	1578.7	1569.4
30°	1565.6	1550.5	1522.5	1516.9	1509.4
32.5°	1505.6	1494.5	1464.5	1453.2	1445.6
35°	1447.5	1428.9	1398.9	1387.6	1378.3
37.5°	1382.0	1365.2	1335.1	1322.0	1312.7
40°	1314.7	1299.6	1269.6	1252.9	1245.3
42.5°	1249.1	1234.0	1204.2	1185.3	1174.2
45°	1178.0	1164.9	1136.6	1116.2	1108.6
47.5°	1108.6	1095.5	1065.6	1044.8	1033.7
50°	1035.5	1026.2	1000.0	973.8	964.4
52.5°	964.4	951.3	927.0	906.4	893.3
55°	891.5	880.2	857.7	835.2	825.9
57.5°	818.3	809.0	784.6	762.2	754.6
60°	745.2	737.9	711.7	691.0	685.5
62.5°	674.2	661.1	642.3	623.6	616.1
65°	601.2	589.9	571.2	554.4	544.9
67.5°	526.3	516.8	500.1	487.0	479.4
70°	457.0	449.4	432.5	419.4	412.1
72.5°	385.9	378.3	369.0	355.9	350.2
75°	314.5	310.9	301.4	290.3	294.1
77.5°	251.0	243.3	239.6	234.0	228.5
80°	187.4	185.4	181.6	176.1	172.3
82.5°	127.3	127.3	125.5	118.0	118.0
85°	76.7	74.9	73.1	67.4	65.6
87.5°	33.7	30.0	26.2	20.6	18.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930835

CATALOG NUMBER: DFN2DS-SQ2F0-050DS840-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.34	17.95	16.70	18.26	18.57	15.89	17.50	16.26	17.82	18.13
	3H	18.09	19.54	18.46	19.87	20.23	17.60	19.05	17.97	19.38	19.74
	4H	18.73	20.10	19.13	20.45	20.83	18.24	19.61	18.64	19.95	20.33
	6H	19.20	20.47	19.61	20.83	21.23	18.70	19.97	19.11	20.33	20.72
	8H	19.34	20.56	19.77	20.94	21.34	18.84	20.05	19.27	20.44	20.84
	12H	19.43	20.59	19.86	20.98	21.41	18.92	20.08	19.35	20.46	20.89
4H	2H	16.90	18.27	17.29	18.61	18.99	16.54	17.91	16.94	18.26	18.64
	3H	18.87	20.02	19.28	20.42	20.82	18.47	19.61	18.87	20.01	20.41
	4H	19.65	20.68	20.08	21.10	21.53	19.22	20.26	19.66	20.67	21.11
	6H	20.24	21.15	20.70	21.59	22.05	19.81	20.72	20.27	21.16	21.61
	8H	20.43	21.28	20.89	21.72	22.19	20.00	20.84	20.46	21.29	21.75
	12H	20.57	21.33	21.05	21.80	22.27	20.11	20.87	20.59	21.35	21.82
8H	4H	19.92	20.77	20.38	21.21	21.68	19.55	20.39	20.01	20.84	21.30
	6H	20.64	21.34	21.13	21.83	22.30	20.25	20.96	20.75	21.45	21.92
	8H	20.89	21.53	21.40	22.03	22.52	20.50	21.13	21.01	21.64	22.13
	12H	21.09	21.65	21.60	22.14	22.70	20.68	21.24	21.19	21.73	22.29
12H	4H	19.95	20.71	20.43	21.18	21.65	19.58	20.34	20.06	20.82	21.29
	6H	20.68	21.31	21.19	21.82	22.31	20.31	20.94	20.82	21.45	21.94
	8H	20.99	21.55	21.50	22.04	22.60	20.62	21.17	21.12	21.67	22.23