

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931441

Luminaire Tested: DFN2DS-TR3F0-090DS950-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931441
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-090DS950-FLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8420.0 lumens
Efficiency: N/A
Efficacy: 85.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 99.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931441

CATALOG NUMBER: DFN2DS-TR3F0-090DS950-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931441

CATALOG NUMBER: DFN2DS-TR3F0-090DS950-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4124	4124	4124
5°	4139	4080	4104
10°	4115	4039	4059
15°	4064	3986	3982
20°	3992	3908	3904
25°	3920	3811	3811
30°	3828	3723	3691
35°	3742	3616	3563
40°	3634	3509	3442
45°	3528	3404	3320
50°	3411	3294	3177
55°	3291	3166	3049
60°	3156	3014	2903
65°	3012	2862	2731
70°	2829	2678	2551
75°	2573	2466	2406
80°	2285	2214	2101
85°	1863	1777	1593

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3528 cd/sqm

TEST NUMBER: P931441

CATALOG NUMBER: DFN2DS-TR3F0-090DS950-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	311.5	3.7
10°-20°	876.4	10.4
20°-30°	1287.9	15.3
30°-40°	1495.9	17.8
40°-50°	1494.0	17.7
50°-60°	1302.7	15.5
60°-70°	963.0	11.4
70°-80°	544.8	6.5
80°-90°	143.8	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2475.8	29.4
0°-40°	3971.6	47.2
0°-60°	6768.3	80.4
0°-90°	8420.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8420.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3309	3309	3309	3309	3309	
5°	3309	3297	3262	3287	3281	314
15°	3150	3131	3090	3103	3087	887
25°	2851	2826	2772	2778	2772	1312
35°	2460	2428	2377	2358	2342	1536
45°	2002	1980	1932	1897	1884	1545
55°	1515	1496	1458	1419	1404	1354
65°	1022	1002	971	942	926	1010
75°	534	528	512	493	500	571
85°	130	127	124	114	111	153
90°	0	0	0	0	0	

TEST NUMBER: P931441

CATALOG NUMBER: DFN2DS-TR3F0-090DS950-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3309.3	3309.3	3309.3	3309.3	3309.3
2.5°	3328.6	3312.7	3277.6	3309.3	3303.2
5°	3309.3	3296.8	3261.8	3287.1	3280.9
7.5°	3287.1	3268.2	3233.0	3258.7	3252.3
10°	3252.3	3230.0	3191.8	3217.2	3207.7
12.5°	3204.3	3185.4	3147.3	3163.1	3156.8
15°	3150.3	3131.4	3089.9	3102.7	3086.8
17.5°	3083.4	3064.5	3023.1	3038.9	3023.1
20°	3010.2	2991.3	2946.7	2956.1	2943.7
22.5°	2937.2	2908.6	2867.0	2867.0	2860.6
25°	2851.2	2825.8	2771.9	2777.9	2771.9
27.5°	2755.6	2733.3	2692.2	2682.8	2666.9
30°	2660.5	2634.8	2587.1	2577.7	2564.9
32.5°	2558.5	2539.6	2488.6	2469.4	2456.5
35°	2459.9	2428.2	2377.1	2358.0	2342.1
37.5°	2348.5	2319.8	2268.8	2246.5	2230.7
40°	2234.0	2208.4	2157.3	2129.0	2116.2
42.5°	2122.6	2097.0	2046.3	2014.3	1995.4
45°	2001.7	1979.5	1931.5	1896.7	1884.0
47.5°	1884.0	1861.6	1810.6	1775.6	1756.7
50°	1759.7	1743.8	1699.2	1654.7	1638.8
52.5°	1638.8	1616.5	1575.3	1540.3	1518.0
55°	1514.9	1495.7	1457.5	1419.4	1403.5
57.5°	1390.7	1374.8	1333.3	1295.1	1282.3
60°	1266.4	1253.9	1209.3	1174.3	1164.8
62.5°	1145.5	1123.2	1091.5	1059.8	1047.0
65°	1021.6	1002.4	970.6	942.0	926.1
67.5°	894.3	878.2	849.7	827.5	814.7
70°	776.5	763.7	735.0	712.7	700.2
72.5°	655.6	642.8	626.9	604.7	595.3
75°	534.5	528.3	512.2	493.3	499.7
77.5°	426.4	413.6	407.2	397.8	388.3
80°	318.4	315.0	308.5	299.1	292.8
82.5°	216.4	216.4	213.4	200.5	200.5
85°	130.3	127.3	124.3	114.4	111.4
87.5°	57.4	50.9	44.6	35.2	31.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931441

CATALOG NUMBER: DFN2DS-TR3F0-090DS950-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.21	17.82	16.57	18.13	18.44	15.76	17.37	16.13	17.69	18.00
	3H	17.96	19.41	18.33	19.74	20.10	17.46	18.92	17.84	19.25	19.61
	4H	18.60	19.97	19.00	20.32	20.69	18.11	19.48	18.50	19.82	20.20
	6H	19.07	20.34	19.48	20.70	21.09	18.57	19.84	18.98	20.20	20.59
	8H	19.21	20.42	19.64	20.81	21.21	18.71	19.92	19.14	20.31	20.71
	12H	19.30	20.46	19.73	20.85	21.27	18.79	19.95	19.22	20.33	20.76
4H	2H	16.77	18.13	17.16	18.48	18.86	16.41	17.78	16.81	18.13	18.51
	3H	18.74	19.89	19.15	20.28	20.68	18.33	19.48	18.74	19.88	20.28
	4H	19.52	20.55	19.95	20.97	21.40	19.09	20.13	19.52	20.54	20.98
	6H	20.11	21.02	20.57	21.46	21.92	19.68	20.59	20.14	21.03	21.48
	8H	20.30	21.15	20.76	21.59	22.06	19.87	20.71	20.33	21.15	21.62
	12H	20.43	21.19	20.92	21.67	22.14	19.98	20.74	20.46	21.22	21.69
8H	4H	19.79	20.64	20.25	21.08	21.54	19.42	20.26	19.88	20.71	21.17
	6H	20.50	21.21	21.00	21.70	22.17	20.12	20.83	20.62	21.31	21.79
	8H	20.76	21.39	21.27	21.90	22.39	20.37	21.00	20.88	21.51	22.00
	12H	20.96	21.52	21.47	22.01	22.57	20.55	21.11	21.06	21.60	22.16
12H	4H	19.82	20.58	20.30	21.05	21.52	19.45	20.21	19.93	20.69	21.16
	6H	20.55	21.18	21.06	21.69	22.17	20.18	20.81	20.69	21.32	21.81
	8H	20.86	21.42	21.37	21.91	22.47	20.49	21.04	20.99	21.53	22.10

END OF REPORT

FIELD PERFORMANCE MAY DIFFER FROM LABORATORY PERFORMANCE

7 of 7