

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930856

Luminaire Tested: DFN2DS-SQ2F0-060DS850-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930856
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ2F0-060DS850-RLL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5655.9 lumens
Efficiency: N/A
Efficacy: 96.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.21' x L: 2.21' x H: 0')
CIE Type: Direct

Input Watts (W): 58.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930856

CATALOG NUMBER: DFN2DS-SQ2F0-060DS850-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930856

CATALOG NUMBER: DFN2DS-SQ2F0-060DS850-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6047	6047	6047
5°	6070	5971	6004
10°	6024	5874	5824
15°	5955	5700	5535
20°	5859	5451	5177
25°	5761	5169	4831
30°	5624	4878	4385
35°	5492	4563	3995
40°	5358	4236	3543
45°	5201	3870	3134
50°	5040	3499	2733
55°	4875	3101	2347
60°	4685	2681	1948
65°	4468	2253	1774
70°	4208	1855	1631
75°	3890	1692	1523
80°	3434	1511	1388
85°	2697	1191	1191

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5201 cd/sqm

TEST NUMBER: P930856

CATALOG NUMBER: DFN2DS-SQ2F0-060DS850-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	257.7	4.6
10°-20°	707.6	12.5
20°-30°	993.4	17.6
30°-40°	1082.8	19.1
40°-50°	995.2	17.6
50°-60°	781.6	13.8
60°-70°	508.8	9.0
70°-80°	261.9	4.6
80°-90°	66.9	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1958.7	34.6
0°-40°	3041.5	53.8
0°-60°	4818.4	85.2
0°-90°	5655.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5655.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2750	2750	2750	2750	2750	
5°	2750	2738	2705	2728	2720	261
15°	2616	2588	2504	2456	2432	737
25°	2374	2295	2130	2028	1991	1092
35°	2046	1919	1700	1543	1488	1281
45°	1672	1506	1244	1068	1008	1292
55°	1272	1078	809	660	612	1136
65°	859	657	433	349	341	851
75°	458	284	199	182	179	484
85°	107	55	47	47	47	128
90°	0	0	0	0	0	

TEST NUMBER: P930856

CATALOG NUMBER: DFN2DS-SQ2F0-060DS850-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2750.1	2750.1	2750.1	2750.1	2750.1
2.5°	2762.5	2750.1	2722.6	2747.7	2742.7
5°	2750.1	2737.7	2705.2	2727.7	2720.3
7.5°	2727.7	2712.8	2678.0	2687.8	2675.4
10°	2697.8	2680.3	2630.8	2623.1	2608.3
12.5°	2660.6	2638.1	2570.8	2556.0	2528.5
15°	2615.7	2588.2	2503.7	2456.4	2431.6
17.5°	2563.5	2523.5	2419.0	2364.3	2324.5
20°	2503.7	2453.8	2329.5	2267.4	2212.5
22.5°	2439.0	2381.7	2237.3	2152.8	2115.5
25°	2374.4	2294.6	2130.4	2028.5	1991.0
27.5°	2297.3	2212.5	2030.8	1913.8	1856.6
30°	2215.1	2120.3	1921.2	1794.5	1727.2
32.5°	2135.4	2020.8	1817.0	1667.5	1605.2
35°	2045.9	1918.9	1700.0	1543.1	1488.2
37.5°	1958.7	1821.6	1590.4	1418.5	1356.4
40°	1866.6	1717.4	1475.7	1299.1	1234.4
42.5°	1772.1	1612.8	1361.4	1177.1	1115.1
45°	1672.5	1505.6	1244.5	1067.5	1007.9
47.5°	1578.0	1401.3	1132.5	955.6	901.0
50°	1473.4	1296.8	1022.9	851.0	799.0
52.5°	1371.2	1184.5	918.4	754.1	706.9
55°	1271.7	1077.6	808.8	659.6	612.3
57.5°	1169.8	970.6	711.9	572.5	532.5
60°	1065.2	866.1	609.7	483.0	443.0
62.5°	963.3	764.2	522.6	403.2	383.4
65°	858.7	657.0	433.1	348.6	340.9
67.5°	759.1	557.4	348.6	306.1	298.7
70°	654.5	460.5	288.6	263.8	253.7
72.5°	555.1	370.7	241.3	221.6	216.5
75°	457.9	283.6	199.1	181.7	179.3
77.5°	361.0	201.5	156.8	146.8	141.8
80°	271.2	144.4	119.3	109.6	109.6
82.5°	189.1	97.1	82.1	77.1	77.1
85°	106.9	54.7	47.2	47.2	47.2
87.5°	39.9	19.9	19.9	17.4	17.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930856

CATALOG NUMBER: DFN2DS-SQ2F0-060DS850-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.49	19.01	17.85	19.32	19.64	13.45	14.97	13.81	15.28	15.60
	3H	19.25	20.62	19.63	20.95	21.31	14.71	16.08	15.09	16.41	16.77
	4H	19.92	21.20	20.32	21.55	21.93	15.21	16.50	15.61	16.84	17.22
	6H	20.41	21.59	20.82	21.96	22.35	15.60	16.78	16.01	17.15	17.54
	8H	20.57	21.70	21.00	22.09	22.49	15.72	16.85	16.15	17.24	17.64
	12H	20.68	21.75	21.11	22.14	22.57	15.80	16.88	16.23	17.26	17.69
4H	2H	17.59	18.87	17.99	19.22	19.60	14.14	15.42	14.54	15.77	16.15
	3H	19.52	20.59	19.93	20.99	21.39	15.59	16.65	16.00	17.05	17.45
	4H	20.27	21.23	20.71	21.65	22.08	16.19	17.14	16.62	17.56	18.00
	6H	20.87	21.70	21.32	22.14	22.60	16.67	17.51	17.13	17.95	18.41
	8H	21.08	21.86	21.54	22.30	22.77	16.84	17.61	17.30	18.06	18.53
	12H	21.23	21.93	21.72	22.41	22.88	16.95	17.65	17.44	18.13	18.60
8H	4H	20.30	21.08	20.76	21.52	21.99	16.54	17.32	17.00	17.76	18.23
	6H	20.94	21.58	21.43	22.07	22.55	17.13	17.77	17.62	18.26	18.74
	8H	21.19	21.76	21.70	22.27	22.76	17.35	17.92	17.86	18.43	18.92
	12H	21.39	21.90	21.90	22.39	22.96	17.53	18.04	18.04	18.53	19.09
12H	4H	20.28	20.98	20.76	21.46	21.93	16.58	17.28	17.07	17.76	18.23
	6H	20.92	21.49	21.43	22.00	22.49	17.19	17.77	17.70	18.28	18.77
	8H	21.20	21.71	21.71	22.20	22.77	17.46	17.97	17.97	18.46	19.03