

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930225

Luminaire Tested: DFN2DS-HX3F0-080DS850-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930225
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-080DS850-FLL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8783.3 lumens
Efficiency: N/A
Efficacy: 104.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 84.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930225

CATALOG NUMBER: DFN2DS-HX3F0-080DS850-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930225

CATALOG NUMBER: DFN2DS-HX3F0-080DS850-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3999	3999	3999
5°	4014	3956	3980
10°	3991	3916	3936
15°	3941	3865	3862
20°	3871	3789	3785
25°	3801	3696	3696
30°	3712	3610	3579
35°	3629	3507	3455
40°	3524	3403	3338
45°	3421	3301	3219
50°	3308	3194	3081
55°	3191	3070	2957
60°	3060	2923	2815
65°	2921	2775	2648
70°	2743	2597	2474
75°	2495	2391	2333
80°	2215	2147	2037
85°	1808	1722	1544

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3421 cd/sqm

TEST NUMBER: P930225

CATALOG NUMBER: DFN2DS-HX3F0-080DS850-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	324.9	3.7
10°-20°	914.2	10.4
20°-30°	1343.5	15.3
30°-40°	1560.4	17.8
40°-50°	1558.4	17.7
50°-60°	1358.9	15.5
60°-70°	1004.5	11.4
70°-80°	568.4	6.5
80°-90°	150.0	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2582.6	29.4
0°-40°	4143.0	47.2
0°-60°	7060.4	80.4
0°-90°	8783.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8783.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3452	3452	3452	3452	3452	
5°	3452	3439	3402	3429	3423	328
15°	3286	3267	3223	3237	3220	926
25°	2974	2948	2892	2898	2892	1369
35°	2566	2533	2480	2460	2443	1602
45°	2088	2065	2015	1979	1965	1612
55°	1580	1560	1520	1481	1464	1413
65°	1066	1046	1012	983	966	1054
75°	558	551	534	515	521	595
85°	136	133	130	119	116	160
90°	0	0	0	0	0	

TEST NUMBER: P930225

CATALOG NUMBER: DFN2DS-HX3F0-080DS850-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3452.1	3452.1	3452.1	3452.1	3452.1
2.5°	3472.2	3455.6	3419.0	3452.1	3445.8
5°	3452.1	3439.1	3402.5	3428.9	3422.6
7.5°	3428.9	3409.2	3372.6	3399.3	3392.7
10°	3392.7	3369.4	3329.6	3355.9	3346.2
12.5°	3342.6	3322.9	3283.1	3299.6	3293.0
15°	3286.3	3266.6	3223.2	3236.6	3220.1
17.5°	3216.5	3196.8	3153.4	3170.1	3153.4
20°	3140.1	3120.4	3073.9	3083.8	3070.7
22.5°	3064.1	3034.1	2990.8	2990.8	2984.1
25°	2974.2	2947.8	2891.5	2897.8	2891.5
27.5°	2874.5	2851.3	2808.3	2798.5	2781.9
30°	2775.3	2748.4	2698.9	2689.0	2675.6
32.5°	2668.9	2649.2	2595.9	2575.9	2562.6
35°	2566.0	2533.0	2479.7	2459.7	2443.1
37.5°	2449.8	2419.8	2366.7	2343.4	2326.9
40°	2330.5	2303.6	2250.5	2220.9	2207.5
42.5°	2214.2	2187.4	2134.6	2101.1	2081.5
45°	2088.1	2064.8	2014.8	1978.6	1965.3
47.5°	1965.3	1942.0	1888.7	1852.1	1832.4
50°	1835.6	1819.1	1772.5	1726.0	1709.5
52.5°	1709.5	1686.2	1643.3	1606.7	1583.4
55°	1580.2	1560.1	1520.4	1480.6	1464.0
57.5°	1450.7	1434.2	1390.8	1351.0	1337.6
60°	1321.0	1308.1	1261.5	1224.9	1215.0
62.5°	1194.9	1171.8	1138.6	1105.6	1092.1
65°	1065.7	1045.7	1012.5	982.6	966.0
67.5°	932.9	916.0	886.4	863.2	849.8
70°	810.0	796.6	766.8	743.5	730.4
72.5°	683.9	670.6	654.0	630.8	620.9
75°	557.5	551.2	534.3	514.6	521.2
77.5°	444.8	431.4	424.7	414.9	405.0
80°	332.1	328.6	321.9	312.1	305.3
82.5°	225.8	225.8	222.6	209.2	209.2
85°	136.0	132.7	129.6	119.4	116.2
87.5°	59.9	53.2	46.5	36.6	33.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930225

CATALOG NUMBER: DFN2DS-HX3F0-080DS850-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.10	17.71	16.46	18.02	18.34	15.65	17.26	16.02	17.58	17.89
	3H	17.85	19.30	18.23	19.63	19.99	17.36	18.81	17.73	19.14	19.50
	4H	18.49	19.86	18.89	20.21	20.59	18.00	19.37	18.40	19.72	20.09
	6H	18.96	20.23	19.37	20.60	20.99	18.46	19.73	18.87	20.10	20.49
	8H	19.11	20.32	19.53	20.71	21.11	18.60	19.81	19.03	20.20	20.60
	12H	19.20	20.36	19.63	20.74	21.17	18.68	19.84	19.11	20.23	20.66
4H	2H	16.66	18.03	17.06	18.38	18.75	16.31	17.67	16.70	18.02	18.40
	3H	18.63	19.78	19.04	20.18	20.58	18.23	19.37	18.64	19.77	20.17
	4H	19.41	20.45	19.84	20.86	21.30	18.99	20.02	19.42	20.44	20.87
	6H	20.01	20.91	20.46	21.35	21.81	19.57	20.48	20.03	20.92	21.38
	8H	20.20	21.04	20.66	21.49	21.95	19.76	20.60	20.22	21.05	21.51
	12H	20.33	21.09	20.81	21.56	22.03	19.88	20.64	20.36	21.11	21.58
8H	4H	19.68	20.53	20.14	20.97	21.44	19.31	20.16	19.77	20.60	21.06
	6H	20.40	21.10	20.89	21.59	22.06	20.02	20.72	20.51	21.21	21.68
	8H	20.66	21.29	21.17	21.79	22.28	20.27	20.90	20.78	21.40	21.89
	12H	20.86	21.41	21.36	21.91	22.47	20.44	21.00	20.95	21.49	22.05
12H	4H	19.71	20.47	20.19	20.95	21.41	19.34	20.10	19.82	20.58	21.05
	6H	20.44	21.08	20.95	21.58	22.07	20.07	20.71	20.58	21.21	21.70
	8H	20.76	21.31	21.26	21.81	22.37	20.38	20.94	20.89	21.43	21.99