

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930874

Luminaire Tested: DFN2DS-SQ2F0-070DS850-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930874
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ2F0-070DS850-RLL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6598.5 lumens
Efficiency: N/A
Efficacy: 92.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.21' x L: 2.21' x H: 0')
CIE Type: Direct

Input Watts (W): 71.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930874

CATALOG NUMBER: DFN2DS-SQ2F0-070DS850-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930874

CATALOG NUMBER: DFN2DS-SQ2F0-070DS850-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92	90	88	86
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82	79	76	74
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74	69	66	64
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66	62	57	55
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60	55	51	49
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55	50	45	43
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51	45	41	39
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47	41	37	35
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44	38	34	32
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41	35	31	29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7055	7055	7055
5°	7082	6966	7005
10°	7028	6853	6794
15°	6947	6650	6458
20°	6835	6359	6040
25°	6721	6030	5636
30°	6562	5691	5116
35°	6407	5324	4661
40°	6251	4942	4134
45°	6068	4515	3657
50°	5880	4082	3189
55°	5688	3617	2739
60°	5465	3128	2273
65°	5212	2629	2069
70°	4910	2165	1903
75°	4538	1973	1777
80°	4007	1764	1620
85°	3149	1390	1390

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6068 cd/sqm

TEST NUMBER: P930874

CATALOG NUMBER: DFN2DS-SQ2F0-070DS850-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	300.7	4.6
10°-20°	825.5	12.5
20°-30°	1158.9	17.6
30°-40°	1263.3	19.1
40°-50°	1161.1	17.6
50°-60°	911.9	13.8
60°-70°	593.5	9.0
70°-80°	305.5	4.6
80°-90°	78.0	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2285.1	34.6
0°-40°	3548.4	53.8
0°-60°	5621.4	85.2
0°-90°	6598.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6598.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3208	3208	3208	3208	3208	
5°	3208	3194	3156	3182	3174	304
15°	3052	3020	2921	2866	2837	860
25°	2770	2677	2485	2366	2323	1274
35°	2387	2239	1983	1800	1736	1494
45°	1951	1756	1452	1246	1176	1507
55°	1484	1257	944	770	714	1326
65°	1002	766	505	407	398	993
75°	534	331	232	212	209	565
85°	125	64	55	55	55	150
90°	0	0	0	0	0	

TEST NUMBER: P930874

CATALOG NUMBER: DFN2DS-SQ2F0-070DS850-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3208.4	3208.4	3208.4	3208.4	3208.4
2.5°	3222.9	3208.4	3176.4	3205.7	3199.8
5°	3208.4	3193.9	3156.1	3182.3	3173.6
7.5°	3182.3	3165.0	3124.4	3135.7	3121.3
10°	3147.5	3127.2	3069.2	3060.3	3043.0
12.5°	3104.0	3077.8	2999.3	2982.0	2949.9
15°	3051.6	3019.6	2921.0	2865.9	2836.9
17.5°	2990.6	2944.2	2822.2	2758.3	2711.8
20°	2921.0	2862.8	2717.7	2645.3	2581.2
22.5°	2845.6	2778.7	2610.1	2511.6	2468.2
25°	2770.1	2677.0	2485.4	2366.5	2322.8
27.5°	2680.1	2581.2	2369.3	2232.9	2166.0
30°	2584.3	2473.7	2241.4	2093.6	2015.1
32.5°	2491.3	2357.6	2119.7	1945.4	1872.7
35°	2386.8	2238.6	1983.3	1800.4	1736.3
37.5°	2285.2	2125.3	1855.5	1654.8	1582.5
40°	2177.6	2003.6	1721.7	1515.7	1440.1
42.5°	2067.4	1881.6	1588.3	1373.3	1301.0
45°	1951.3	1756.5	1451.9	1245.5	1175.9
47.5°	1840.9	1634.9	1321.3	1114.9	1051.1
50°	1719.0	1512.9	1193.4	992.9	932.2
52.5°	1599.7	1381.9	1071.4	879.8	824.7
55°	1483.6	1257.2	943.5	769.5	714.4
57.5°	1364.7	1132.4	830.5	667.8	621.4
60°	1242.7	1010.4	711.3	563.5	516.9
62.5°	1123.7	891.5	609.6	470.4	447.3
65°	1001.8	766.4	505.3	406.7	397.7
67.5°	885.6	650.3	406.7	357.0	348.4
70°	763.7	537.2	336.7	307.7	296.0
72.5°	647.5	432.5	281.6	258.5	252.6
75°	534.2	330.8	232.2	211.9	209.2
77.5°	421.1	235.0	183.0	171.2	165.5
80°	316.4	168.5	139.3	127.9	127.9
82.5°	220.6	113.3	95.8	89.9	89.9
85°	124.8	63.8	55.1	55.1	55.1
87.5°	46.5	23.1	23.1	20.3	20.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930874

CATALOG NUMBER: DFN2DS-SQ2F0-070DS850-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.02	19.54	18.39	19.86	20.17	13.98	15.50	14.35	15.82	16.13
	3H	19.79	21.15	20.17	21.48	21.84	15.25	16.61	15.63	16.94	17.30
	4H	20.45	21.73	20.85	22.08	22.46	15.75	17.03	16.15	17.38	17.76
	6H	20.94	22.13	21.36	22.49	22.88	16.13	17.31	16.54	17.68	18.07
	8H	21.11	22.23	21.53	22.62	23.03	16.26	17.38	16.68	17.77	18.17
	12H	21.21	22.29	21.64	22.67	23.10	16.34	17.41	16.77	17.80	18.23
4H	2H	18.13	19.41	18.53	19.76	20.13	14.68	15.96	15.08	16.31	16.69
	3H	20.06	21.12	20.47	21.52	21.92	16.12	17.18	16.53	17.58	17.99
	4H	20.81	21.77	21.24	22.18	22.62	16.72	17.68	17.15	18.09	18.53
	6H	21.40	22.23	21.86	22.68	23.14	17.21	18.04	17.67	18.48	18.94
	8H	21.62	22.39	22.08	22.84	23.30	17.37	18.15	17.83	18.59	19.06
	12H	21.77	22.46	22.25	22.94	23.41	17.49	18.18	17.97	18.66	19.13
8H	4H	20.83	21.61	21.30	22.05	22.52	17.07	17.85	17.54	18.30	18.76
	6H	21.47	22.11	21.97	22.60	23.08	17.66	18.30	18.16	18.80	19.27
	8H	21.72	22.30	22.24	22.81	23.30	17.88	18.46	18.40	18.97	19.46
	12H	21.93	22.44	22.43	22.93	23.49	18.06	18.57	18.57	19.06	19.63
12H	4H	20.82	21.51	21.30	21.99	22.46	17.12	17.81	17.60	18.29	18.76
	6H	21.45	22.03	21.97	22.54	23.03	17.72	18.30	18.24	18.81	19.30
	8H	21.74	22.25	22.25	22.74	23.30	18.00	18.51	18.51	19.00	19.56