

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930857

Luminaire Tested: DFN2DS-SQ2F0-060DS927-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930857
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ2F0-060DS927-FLL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4704.5 lumens
Efficiency: N/A
Efficacy: 80.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.21' x L: 2.21' x H: 0')
CIE Type: Direct

Input Watts (W): 58.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930857

CATALOG NUMBER: DFN2DS-SQ2F0-060DS927-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930857

CATALOG NUMBER: DFN2DS-SQ2F0-060DS927-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4066	4066	4066
5°	4081	4023	4046
10°	4057	3982	4002
15°	4007	3930	3926
20°	3936	3853	3849
25°	3865	3757	3757
30°	3774	3670	3638
35°	3689	3565	3512
40°	3583	3460	3394
45°	3478	3356	3273
50°	3363	3248	3132
55°	3245	3122	3006
60°	3112	2972	2862
65°	2970	2822	2692
70°	2790	2640	2515
75°	2537	2431	2372
80°	2253	2183	2070
85°	1837	1751	1572

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3478 cd/sqm

TEST NUMBER: P930857

CATALOG NUMBER: DFN2DS-SQ2F0-060DS927-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	174.0	3.7
10°-20°	489.7	10.4
20°-30°	719.6	15.3
30°-40°	835.8	17.8
40°-50°	834.7	17.7
50°-60°	727.9	15.5
60°-70°	538.1	11.4
70°-80°	304.4	6.5
80°-90°	80.3	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1383.3	29.4
0°-40°	2219.1	47.2
0°-60°	3781.7	80.4
0°-90°	4704.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4704.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1849	1849	1849	1849	1849	
5°	1849	1842	1822	1837	1833	176
15°	1760	1750	1726	1734	1725	496
25°	1593	1579	1549	1552	1549	733
35°	1374	1357	1328	1317	1308	858
45°	1118	1106	1079	1060	1053	863
55°	846	836	814	793	784	757
65°	571	560	542	526	517	564
75°	299	295	286	276	279	319
85°	73	71	69	64	62	86
90°	0	0	0	0	0	

TEST NUMBER: P930857

CATALOG NUMBER: DFN2DS-SQ2F0-060DS927-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1849.0	1849.0	1849.0	1849.0	1849.0
2.5°	1859.8	1850.9	1831.3	1849.0	1845.6
5°	1849.0	1842.0	1822.4	1836.6	1833.2
7.5°	1836.6	1826.0	1806.4	1820.7	1817.2
10°	1817.2	1804.7	1783.3	1797.5	1792.2
12.5°	1790.4	1779.8	1758.5	1767.3	1763.8
15°	1760.1	1749.6	1726.4	1733.6	1724.7
17.5°	1722.8	1712.3	1689.1	1697.9	1689.1
20°	1681.9	1671.4	1646.4	1651.7	1644.7
22.5°	1641.2	1625.1	1601.9	1601.9	1598.3
25°	1593.0	1578.9	1548.7	1552.1	1548.7
27.5°	1539.6	1527.2	1504.2	1498.9	1490.1
30°	1486.5	1472.1	1445.6	1440.3	1433.0
32.5°	1429.5	1418.9	1390.4	1379.7	1372.5
35°	1374.4	1356.7	1328.2	1317.4	1308.5
37.5°	1312.2	1296.1	1267.7	1255.2	1246.3
40°	1248.2	1233.9	1205.4	1189.6	1182.4
42.5°	1185.9	1171.6	1143.3	1125.4	1114.8
45°	1118.5	1105.9	1079.2	1059.8	1052.6
47.5°	1052.6	1040.1	1011.7	992.1	981.4
50°	983.2	974.3	949.4	924.5	915.6
52.5°	915.6	903.2	880.1	860.6	848.2
55°	846.4	835.6	814.3	793.0	784.2
57.5°	777.0	768.2	745.0	723.7	716.4
60°	707.6	700.6	675.7	656.1	650.8
62.5°	640.0	627.6	609.8	592.1	585.0
65°	570.8	560.1	542.4	526.3	517.4
67.5°	499.7	490.6	474.8	462.4	455.2
70°	433.9	426.7	410.7	398.2	391.2
72.5°	366.3	359.2	350.3	337.9	332.6
75°	298.6	295.3	286.1	275.6	279.2
77.5°	238.2	231.1	227.5	222.2	216.9
80°	177.9	176.0	172.4	167.1	163.5
82.5°	120.9	120.9	119.2	112.1	112.1
85°	72.8	71.1	69.4	63.9	62.3
87.5°	32.1	28.5	24.9	19.6	17.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930857

CATALOG NUMBER: DFN2DS-SQ2F0-060DS927-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.16	17.77	16.52	18.08	18.40	15.71	17.32	16.08	17.64	17.95
	3H	17.91	19.36	18.28	19.69	20.05	17.42	18.87	17.79	19.20	19.56
	4H	18.55	19.92	18.95	20.27	20.65	18.06	19.43	18.46	19.77	20.15
	6H	19.02	20.29	19.43	20.65	21.05	18.52	19.79	18.93	20.15	20.54
	8H	19.16	20.38	19.59	20.76	21.16	18.66	19.87	19.09	20.26	20.66
	12H	19.25	20.41	19.68	20.80	21.23	18.74	19.90	19.17	20.28	20.71
4H	2H	16.72	18.09	17.12	18.43	18.81	16.36	17.73	16.76	18.08	18.46
	3H	18.69	19.84	19.10	20.24	20.64	18.28	19.43	18.69	19.83	20.23
	4H	19.47	20.50	19.90	20.92	21.35	19.04	20.08	19.48	20.49	20.93
	6H	20.06	20.97	20.52	21.41	21.87	19.63	20.54	20.09	20.98	21.43
	8H	20.25	21.10	20.71	21.54	22.01	19.82	20.66	20.28	21.10	21.57
	12H	20.39	21.15	20.87	21.62	22.09	19.93	20.69	20.41	21.17	21.64
8H	4H	19.74	20.59	20.20	21.03	21.50	19.37	20.21	19.83	20.66	21.12
	6H	20.46	21.16	20.95	21.65	22.12	20.07	20.78	20.57	21.27	21.74
	8H	20.71	21.35	21.22	21.85	22.34	20.32	20.95	20.83	21.46	21.95
	12H	20.91	21.47	21.42	21.96	22.52	20.50	21.06	21.01	21.55	22.11
12H	4H	19.77	20.53	20.25	21.00	21.47	19.40	20.16	19.88	20.64	21.11
	6H	20.50	21.13	21.01	21.64	22.13	20.13	20.76	20.64	21.27	21.76
	8H	20.81	21.37	21.32	21.86	22.42	20.44	20.99	20.94	21.49	22.05